# CCU6 Capture Compare Unit 6


AURIX<sup>™</sup> TC3xx Microcontroller Training V1.0 2020-06



Please read the Important Notice and Warnings at the end of this document

## CCU6 Capture Compare Unit 6






### Highlights

- The CCU6 unit is used to control AC and DC drives
- Special operating modes support the control of Brushless DC-motors using Hall sensors or Back-EMF detection

Key Features	Customer Benefits	
Center aligned / edge aligned PWM	<ul> <li>Fits perfectly to most of all eMotor applications</li> </ul>	
Block commutation for brushless DC	<ul> <li>The CPU load is reduced due to optimized module implementation</li> </ul>	
Fast emergency stop (/CTRAP)	> Easy to configure for block commutation	


## CCU6 Center aligned/edge aligned PWM





#### > Center aligned PWM


- Space Vector Modulation fits perfectly to Permanent Magnetic Synchronous Motor applications
- > Benefits:
  - EMC is reduced by center aligned PWM
  - Shadow transfer on Period match/zero match
  - The length of the dead time can be programmed individually in order to deal with transient behavior of the MOSFETs



- > Edge aligned PWM
- > Brushless DC (Block commutation)
- > Benefits:
  - Fits perfectly to block commutation
  - Easy to implement



- At every correct Hall event, a new Hall pattern with its corresponding output pattern can be loaded
- The sampling of the Hall pattern is done with T12 input clock
- A noise filter can be realized by using the dead time counter DTC0 (6 bit wide)
- The Hall pattern inputs are sampled and compared with the current Hall pattern and the expected next Hall pattern in order to determine the movement direction of the motor. If the values match, no further action is needed





- > Fast emergency stop without CPU load via external signal (/CTRAP)
  - Switch output channel to a defined state
- > TRAP control
  - passive state select bit for each channel
  - initialization bit for each channel
- > In TRAP state, all outputs can be switched to selected passive state
- > TRAP state can be triggered by SW or HW via a bit field

## CCU6 System integration



Motor Current ADC• Sample Rate < 1 μs• ADC is triggered by CCU6• Delay generation to avoid spikes• Interrupt generation is possible• Independent ADC modules are available	Motor Pattern CCU6 • 6 PWM outputs • Center/Edge aligned PWM • Dead time generation • Interrupt generation • Generation of trigger events for ADC	Position Sensor Hall Sensors Processed by CCU6 Encoder Processed by GPT12 (Timer Incremental Mode) Resolver Processed by DSADC
--	---	---

### **Overview**


- Capture/Compare Unit CCU6 generates ADC conversion to measure current
- Position recognition can be realized by Hall sensors (CCU6), encoder (GPT12) and resolver (DSADC)

### **Advantages**

- No external resources are needed for motor control (all modules are integrated in AURIX<sup>™</sup>)
- Synchronous triggering of ADC is done by CCU6
- All modules for controlling a PMSM/BLDC are on-chip (AURIX<sup>™</sup>)

## Application example Brushless DC drive application





### **Overview**

- Capture/Compare Unit CCU6 generates
   PWM pattern to turn the motor
- With the position, provided by the Hall sensors, the next comutation pattern is generated automatically

#### **Advantages**

- Generating different PWM patterns with less CPU interaction
- Synchronous triggering of ADC conversions
- Handling of sensor(less) brushless DC motor applications

#### Trademarks

All referenced product or service names and trademarks are the property of their respective owners.



Edition 2020-06 Published by Infineon Technologies AG 81726 Munich, Germany

© 2020 Infineon Technologies AG. All Rights Reserved.

Do you have a question about this document? Email: <u>erratum@infineon.com</u>

Document reference AURIX\_Training\_2\_ Capture\_Compare\_Unit\_6

#### **IMPORTANT NOTICE**

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application. For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

#### WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.