UART_DMA_Transfer_1 UART data transfer via DMA

AURIX[™] TC2xx Microcontroller Training V1.0.0



Please read the Important Notice and Warnings at the end of this document




The DMA module is used to transfer data received from the UART to LMURAM.

The CPU sends a message via UART in loopback mode. When it receives the message back, it triggers an interrupt which starts the data transfer via DMA.



Introduction

- The Direct Memory Access (DMA) transfers data from data source locations to data destination locations without intervention of the CPU or other on-chip devices.
- A DMA channel performs transactions. One transaction is made of transfers. One transfer is made of up to 16 moves. This structure divides the data into several parts and increases the application's efficiency.



- A transaction can be interrupted, however once a transfer is started, it cannot be interrupted.
- Any DMA move engine can service a DMA request from any of the 128 DMA channels. Channel 127 has the highest priority.
- > DMA requests can be triggered by Hardware or Software.



Introduction


- The Asynchronous/Synchronous Interface (ASCLIN) module provides asynchronous serial communication with external devices, using data-in and data-out signals only.
- For test purposes in this example, the transmit pin (TX) and receive pin (RX) can be shorted internally on-chip (loopback mode).



Hardware setup

This code example has been developed for the board KIT_AURIX_TC297_TFT_BC-Step.

		X102	
	P14.5	40 39	P14.4
	P20.10	38 37	P20.9
	P15.7	36 35	P15.6
	P15.5	34 33	P15.4
TX/RX UART	P15.3	32 31	P15.2
	P22.3	30 29	P22.2
	P22.1	28 27	P22.0
	P33.11	26 25	P23.4
	P23.3	24 23	P23.2
	P23.1	22 21	P23.0
	P33.6	20 19	P33.8
	P33.12	18 17	P33.1
	P33.2	16 15	P33.3
	P33.4	14 13	P33.5
	AN0	12 11	AN8
	AN2	10 9	AN3
	AN32	8 7	AN33
	AN20	6 5	AN21
Ground	GND	4 3	GND
	V_UC(+5V)	2 1	VCC_IN





The UART_DMA_Transfer_1 example works as follows:


- 1. The CPU sends a character string (12-bytes) on the UART Tx: "Hello World!"
- 2. Via to the loopback (Tx-Rx shorted internally), the **Asclin Rx interrupt** is triggered.
- 3. The interruption enables the reception of the data and therefore calls the DMA to transfer it to the LMURAM.



Configuration of the DMA

In this example, a **12-byte message**, which is a **sequence of twelve 8-bit characters**, needs to be transferred.

Twelve transactions composed of **one transfer** made of one **8-bit word move** is then a possible solution. All this can be achieved with a **single DMA channel**, here channel 12.





Configuration of the DMA

The needed iLLD functions for DMA configuration are called from *init_dma()*:

- 1. IfxDma_Dma_initModuleConfig() generates the default module configuration
- IfxDma_Dma_initModule() initializes the DMA module with the defined parameters
- **3.** *IfxDma_Dma_initChannelConfig()* generates the default channel configuration The following parameters can be then defined at this point:
 - channelld: 12
 - transferCount (number of transfer per transaction): 1
 - moveSize: 8-bit
 - **blockMode** (number of move per transfer): 1
 - requestMode: Complete a full transaction on request
 - source/destinationAddress: Set the source and destination memory locations
 - source/destinationCircularBufferEnabled: Define if the address is fixed or should be incremented

For more detailed information, please check the source code.

4. IfxDma_Dma_initChannel() initializes the channel with the defined parameters



Configuration of the UART

The initialization of the UART communication is done via the function *init_uart()*, which contains:

- 1. The iLLD function *lfxAsclin_Asc_initModuleConfig()* generates the default configuration. This configuration is then modified with the needed parameters:
 - The priority levels of the Rx and Tx interrupts are defined through the *interrupt.txPriority* and *interrupt.rxPriority* parameters
 - The Rx and Tx pins are defined in this function
 - The Interrupt Service Provider is defined by the *interrupt.typeOfService* parameter. The defined ISR is CPU0 for both Tx and Rx since the iLLD only has one parameter
- 2. The *lfxAsclin_Asc_init_Module()* function is called to initialize the module with the defined parameters
- 3. The Service Provider is therefore manually modified for the Rx interrupt, in order to assign it to the DMA.

The transmission of data is triggered by the function **send_data()**:

Calls the iLLD function *lfxAsclin_Asc_write()* which sends the data, specified in the parameters, over the UART Tx.

Note: The **IfxAsclin_Asc_read()** iLLD function is not used, because there is no need to copy the received data in a global variable. As soon as received, the data is directly transferred to the LMURAM via DMA.



Run and Test

After code compilation and flashing the device, perform the following steps:

- > Connect the board to the PC
- > Run the code
- > Add the LMURAM address (0x9000000) to the memory window
- > Check using the debugger:
 - The message has been properly copied in the LMURAM

Memory ⋈ Inc C/C++ Projects											
N	Aonitors 🛛 🝦 🗶 🔆	0x90000000 : 0x90000000	<ascii< th=""><th>> 🛛 🗌</th><th>🔶 New</th><th>Render</th><th>ings</th><th></th><th></th><th></th><th></th></ascii<>	> 🛛 🗌	🔶 New	Render	ings				
	Ox90000000	Address	0	1	2	3	4	5	6	7	
		0000000090000000	н	e	1	1	o		W	o	
	LMURAM	000000000000008	n	1	d	1	0	۵	0	0	
		0000000090000010	0	0	٥	0	0	0	0	0	
		000000090000018	0	0	۵	0	0	0	0	0	
		000000090000020	0	0	0	0	0	0	0	0	

- As expected, 12 transactions were needed to transfer the message

(x)= Variables 🛛	● Breakpoints	
Name		Value
(×)= 'UART_DN	A_Transfer.c'::g_correctTransaction	ons 12

References





- → AURIX[™] Development Studio is available online:
- https://www.infineon.com/aurixdevelopmentstudio
- > Use the *"Import…"* function to get access to more code examples.
- > More code examples can be found on the GIT repository:
- https://github.com/Infineon/AURIX code examples
- > For additional trainings, visit our webpage:
- https://www.infineon.com/aurix-expert-training
- → For questions and support, use the AURIX[™] Forum:
- https://www.infineonforums.com/forums/13-Aurix-Forum

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.



Edition 2019-10 Published by Infineon Technologies AG 81726 Munich, Germany

© 2019 Infineon Technologies AG. All Rights Reserved.

Do you have a question about this document? Email: <u>erratum@infineon.com</u>

Document reference UART_DMA_Transfer_1

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application. For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.