

18dB High Gain Low Noise Amplifier for LTE Midband

Features

Operating frequencies: 1805 - 2200 MHz

• Insertion power gain: 19.3 dB

Insertion Loss in bypass mode: 4.7 dB

Low noise figure: 0.65 dB


· Low current consumption: 9.5 mA

Multi-state control: Bypass- and high gain-Mode

Ultra small TSNP-6-2 and TSNP-6-10 leadless package

· RF output internally matched to 50 Ohm

· Low external component count



Application


The LTE data rate can be significantly improved by using the Low Noise Amplifier. The integrated bypass function increases the overall system dynamic range and leads to more flexibility in the RF front-end.

In high gain mode the LNA offers best Noise Figure to ensure high data rates even on the LTE cell edge. Closer to the basestation the bypass mode can be activated reducing current consumption.

Product Validation

Qualified for industrial applications according to the relevant tests of JEDEC47/20/22

Block diagram



Data Sheet www.infineon.com

18dB High Gain Low Noise Amplifier for LTE Midband



Table of Contents

Table of Contents

	Table of Contents	2
1	Features	3
2	Maximum Ratings	5
3	Electrical Characteristics	6
4	Application Information	8
5	Package Information	9

2



Features

1 Features

• Insertion power gain: 19.3 dB

• Insertion Loss in bypass mode: 4.7 dB

• Low noise figure: 0.65 dB

· Low current consumption: 9.5 mA

Operating frequencies: 1805 - 2200 MHz

• Multi-state control: Bypass- and High gain-Mode

Supply voltage: 1.5 V to 3.6 V

Ultra small TSNP-6-2 and TSNP-6-10 leadless package (footprint: 0.7 x 1.1 mm²)

B9HF Silicon Germanium technology

• RF output internally matched to 50 Ohm

· Low external component count

• 2kV HBM ESD protection (including AI-pin)

• Pb-free (RoHS compliant) package








Figure 1 Block Diagram

Product Name	Marking	Package			
BGA5M1BN6	5	TSNP-6-2/TSNP-6-10			

18dB High Gain Low Noise Amplifier for LTE Midband



Features

Description

The BGA5M1BN6 is a front-end low noise amplifier for LTE which covers a wide frequency range from 1805 MHz to 2200 MHz. The LNA provides 19.3 dB gain and 0.65 dB noise figure at a current consumption of 9.5 mA in the application configuration described in **Chapter 4**. In bypass mode the LNA provides an insertion loss of 4.7 dB. The BGA5M1BN6 is based upon Infineon Technologies' B9HF Silicon Germanium technology. It operates from 1.5 V to 3.6 V supply voltage. The device features a single-line two-state control (Bypass- and High gain-Mode). OFF-state can be enabled by powering down VCC.

Pin Definition and Function

Table 1 Pin Definition and Function

Pin No.	Name	Function
1	GND	Ground
2	VCC	DC supply
3	AO	LNA output
4	GND	Ground
5	Al	LNA input
6	С	Control



Maximum Ratings

2 Maximum Ratings

Table 2 Maximum Ratings

Parameter	Symbol		Value	Unit	Note or		
		Min.	Тур.	Max.		Test Condition	
Voltage at pin VCC	$V_{\rm CC}$	-0.3	_	3.6	V	1)	
Voltage at pin Al	V_{AI}	-0.3	_	0.9	V	_	
Voltage at pin AO	V_{AO}	-0.3	_	V _{CC} + 0.3	V	_	
Voltage at pin C	V _C	-0.3	_	V _{CC} + 0.3	V	_	
Voltage at pin GND	V_{GND}	-0.3	-	0.3	V	_	
Current into pin VCC	I _{CC}	_	-	16	mA	_	
RF input power	P _{IN}	_	-	+25	dBm	_	
Total power dissipation, $T_S < 148 ^{\circ}C^{2)}$	P _{tot}	-	-	60	mW	-	
Junction temperature	T_{J}	_	-	150	°C	_	
Ambient temperature range	T_{A}	-40	-	85	°C	_	
Storage temperature range	$T_{\rm STG}$	-55	-	150	°C	_	
ESD capability all pins	V _{ESD_HBM}	-2000	-	+2000	V	according to JS-001	

¹⁾ All voltages refer to GND-Node unless otherwise noted

Attention: Stresses above the max. values listed here may cause permanent damage to the device.

Maximum ratings are absolute ratings; exceeding only one of these values may cause irreversible damage to the integrated circuit. Exposure to conditions at or below absolute maximum rating but above the specified maximum operation conditions may affect device reliability and life time. Functionality of the device might not be given under these conditions.

²⁾ T_S is measured on the ground lead at the soldering point



Electrical Characteristics

3 Electrical Characteristics

Table 3 Electrical Characteristics V_{cc} = 1.8V¹⁾

 $T_{\rm A}$ = 25 °C, $V_{\rm CC}$ = 1.8 V, $V_{\rm C,BP}$ = 1.8 V, $V_{\rm C,OFF}$ = 0 V, f = 1805 - 2200 MHz

Parameter	Symbol		Value	S	Unit	Note or Test Condition		
		Min.	Тур.	Max.				
Supply voltage	$V_{\rm CC}$	1.5	1.8	3.6	٧	_		
Control voltages	V _C	1.0	_	V_{CC}	٧	High gain mode		
		0	_	0.4	٧	Bypass mode		
Supply current	I _{cc}	-	9.5	11.0	mA	High gain mode		
		-	85	120	μΑ	Bypass mode		
Insertion power gain	$ S_{21} ^2$	17.8	19.3	20.8	dB	High gain mode		
f= 2000 MHz		-5.9	-4.7	-3.5	dB	Bypass mode		
Noise figure ²⁾	NF	-	0.65	1.15	dB	High gain mode		
$f = 2000 \text{ MHz}, Z_{S} = 50 \Omega$		-	4.7	5.9	dB	Bypass mode		
nput return loss ³⁾	RL _{IN}	9	12	_	dB	High gain mode		
f= 2000 MHz		5	8	_	dB	Bypass mode		
Output return loss³)	RL _{OUT}	10	18	_	dB	High gain mode		
f= 2000 MHz		3	5	_	dB	Bypass mode		
Reverse isolation ³⁾	$1/ S_{12} ^2$	25	37	_	dB	High gain mode		
f = 2000 MHz		3.5	4.7	_	dB	Bypass mode		
Power on time ⁴⁾⁶⁾	t_{S}	_	3	7	μs	OFF to High gain mode		
nbandinput 1dB-compression	IP _{1dB}	-21	-17	_	dBm	High gain mode		
point, f = 2000 MHz ³⁾		-6	-2	_	dBm	Bypass mode		
nband input 3 rd -order	IIP ₃	-12	-7	_	dBm	High gain mode		
ntercept point ³⁾⁵⁾ $f_1 = 2000 \text{ MHz}, f_2 = f_1 + / -1 \text{ MHz}$		1	6	-	dBm	Bypass mode		
Stability ⁶⁾	k	> 1	_	_		f = 20 MHz 10 GHz		

- 1) Based on the application described in **Chapter 4**
- 2) PCB losses are subtracted
- 3) Verification based on AQL; not 100% tested in production
- 4) Gain changed to >90% of gain difference (in dB)
- 5) Input power HG = -30 dBm for each tone; input power BP = -10 dBm for each tone
- 6) Guaranteed by device design; not tested in production

18dB High Gain Low Noise Amplifier for LTE Midband



Electrical Characteristics

Table 4 Electrical Characteristics V_{cc} = 2.8V¹⁾

 $T_{\rm A}$ = 25 °C, $V_{\rm CC}$ = 2.8 V, $V_{\rm C,BP}$ = 2.8 V, $V_{\rm C,OFF}$ = 0 V, f = 1805 - 2200 MHz

Parameter	Symbol		Value	5	Unit	Note or Test Condition		
		Min.	Тур.	Max.				
Supply voltage	$V_{\rm cc}$	1.5	2.8	3.6	٧			
Control voltages	V _C	1.0	_	$V_{\rm CC}$	٧	High gain mode		
		0	_	0.4	٧	Bypass mode		
Supply current	I _{CC}	-	10.3	11.8	mA	High gain mode		
		_	87	120	μΑ	Bypass mode		
Insertion power gain	$ S_{21} ^2$	17.9	19.4	20.9	dB	High gain mode		
f = 2000 MHz		-5.9	-4.7	-3.5	dB	Bypass mode		
Noise figure ²⁾	NF	-	0.65	1.15	dB	High gain mode		
$f = 2000 \text{ MHz}, Z_S = 50 \Omega$		-	4.7	5.9	dB	Bypass mode		
Input return loss ³⁾	RL _{IN}	9	12	_	dB	High gain mode		
f = 2000 MHz		5	8	_	dB	Bypass mode		
Output return loss ³⁾	RL _{OUT}	10	17	_	dB	High gain mode		
f = 2000 MHz		3	5	_	dB	Bypass mode		
Reverse isolation ³⁾	$1/ S_{12} ^2$	25	37	_	dB	High gain mode		
f = 2000 MHz		3.5	4.7	_	dB	Bypass mode		
Power on time ⁴⁾⁶⁾	t_{S}	_	3	7	μs	OFF to High gain mode		
Inband input 1dB-compression	IP _{1dB}	-20	-16	_	dBm	High gain mode		
point, <i>f</i> = 2000 MHz ³⁾		-6	-2	_	dBm	Bypass mode		
Inband input 3 rd -order	IIP ₃	-12	-7	_	dBm	High gain mode		
intercept point ³⁾⁵⁾ $f_1 = 2000 \text{ MHz}, f_2 = f_1 + / -1 \text{ MHz}$		1	6	_	dBm	Bypass mode		
Stability ⁶⁾	k	> 1	_	-		f = 20 MHz 10 GHz		

- 1) Based on the application described in Chapter 4
- 2) PCB losses are subtracted
- 3) Verification based on AQL; not 100% tested in production
- 4) Gain changed to >90% of gain difference (in dB)
- 5) Input power HG = -30 dBm for each tone; input power BP = -10 dBm for each tone
- 6) Guaranteed by device design; not tested in production



Application Information

4 Application Information

Application Board Configuration




Figure 2 Application Schematic BGA5M1BN6

Table 5 Bill of Materials

Name	Value	Package	Manufacturer	Function
C1	1nF	0402	Various	Input matching
C2 (optional)	≥ 1nF	0402	Various	RF bypass 1)
L1	5.2nH	0402	Murata LQW15 type	Input matching
N1	BGA5M1BN6	TSNP-6-2 and TSNP-6-10	Infineon	SiGe LNA

¹⁾ RF bypass recommended to mitigate power supply noise

A list of all application notes is available at http://www.infineon.com/ltelna



Package Information




Figure 3 TSNP-6-2 Package Outline (top, side and bottom views)




Figure 4 TSNP-6-10 Package Outline (top, side and bottom views)






Figure 5 Footprint Recommendation TSNP-6-2 and TSNP-6-10




Figure 6 Marking Layout TSNP-6-2 (top view)




Figure 7 Marking Layout TSNP-6-10 (top view)



Month	2015	2016	2017	2018	2019	2020	2021	2022	2023	2024	2025	2026
01	а	Р	А	Р	а	Р	А	Р	а	Р	Α	Р
02	Ь	q	В	Q	Ь	q	В	Q	Ь	q	В	Q
03	С	Г	C	R	С	Г	C	R	C	Г	C	R
04	d	S	D	S	d	s	D	S	В	S	D	S
05	e	t	Е	Т	е	t	E	T	e	t	E	T
06	f	и	F	U	f	u	F	U	f	u	F	U
07	g	V	G	V	g	V	G	V	g	V	G	V
08	h	×	Н	X	h	×	Н	X	h	×	Н	X
09	j	у	J	Υ	j	у	J	Y	j	у	J	Y
10	k	Z	K	Z	k	Z	K	Z	k	Z	K	Z
11	l	2	L	4	l	2	L	4	l	2	L	4
12	n	3	Ν	5	n	3	N	5	n	3	Ν	5

Figure 8 Date Code Marking TSNP-6-2 and TSNP-6-10




Figure 9 Tape & Reel Dimensions TSNP-6-2 (reel diameter 180 mm, pieces/reel 15000)

18dB High Gain Low Noise Amplifier for LTE Midband






Figure 10 Tape & Reel Dimensions TSNP-6-10 (reel diameter 180 mm, pieces/reel 12000)

18dB High Gain Low Noise Amplifier for LTE Midband



Revision History								
Page or Item	Subjects (major changes since previous revision)							
Revision 2.0, 2	018-02-01							
11	Update Data Code Marking Table							
all Change to Final Status								
-								

Other Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2018-02-01 Published by Infineon Technologies AG 81726 Munich, Germany

© 2018 Infineon Technologies AG. All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.