

## Pre-Driver for Wireless Infrastructure Applications

#### 1 Features

• Operation frequency range: 2300 to 2700MHz

• Gain: 34.8dB

• Output P1dB: 28.9dBm

•  $50\Omega$  single-ended input and output

• 5V supply voltage

• TSNP-16 leadless package (3.0 x 3.0 mm<sup>2</sup>)

• BiCMOS Technology

#### 2 Potential Applications

• 4G/5G

- · Cellular Infrastructure
  - Massive MIMO systems
  - Small cells





 $3.0 \times 3.0 \, \text{mm}^2$ 

Qualified for industrial applications according to the relevant tests of JEDEC47/20/22.

### 4 Description

The product is a stand-alone pre-driver in package. The pre-driver is a two-stage amplifier designed to be used in the 5G Tx line-up for base station applications as the pre-driver for the Doherty power amplifier. It has been designed in the INFINEON BiCMOS technology. Input and outputs are  $50\Omega$  single-ended.

The device configuration is shown in Fig. 1.




Figure 1: BGAP2S20A Block diagram

| Product Name | Marking                       | Package       |
|--------------|-------------------------------|---------------|
| BGAP2S20A    | BP2S2A YYWW(YY=year, WW=week) | PG-TSNP-16-12 |

# **Pre-Driver for Wireless Infrastructure Applications**



#### **Table of Contents**

# **Table of Contents**

| 1 | Features                   | 1 |
|---|----------------------------|---|
| 2 | Potential Applications     | 1 |
| 3 | Product Validation         | 1 |
| 4 | Description                | 1 |
| 5 | Absolute Maximum Ratings   | 3 |
| 6 | Electrical Characteristics | 4 |
| 7 | Application Information    | 5 |
| 8 | Package Information        | 7 |

2

#### **Pre-Driver for Wireless Infrastructure Applications**



**Absolute Maximum Ratings** 

### **5 Absolute Maximum Ratings**

**Table 1: Absolute Maximum Ratings** 

| Parameter                           | Symbol               | Values |      |      | Unit | Note / Test Condition |
|-------------------------------------|----------------------|--------|------|------|------|-----------------------|
|                                     |                      | Min.   | Тур. | Max. |      |                       |
| Supply Voltage                      | V <sub>cc</sub>      | -0.5   | _    | 5.5  | V    | 1                     |
| Enable Voltage                      | V <sub>EN</sub>      | -0.4   | -    | 4.0  | V    | -                     |
| Storage Temperature                 | $T_{STG}$            | -45    | _    | 150  | °C   | -                     |
| Junction Temperature                | TJ                   | -40    | _    | 170  | °C   | -                     |
| DC voltage on RF Ports              | $V_{\rm RF,DC}$      | 0      | -    | 0    | V    | 1                     |
| RF Input Power CW                   | P <sub>IN,CW</sub>   | _      | -    | 6    | dBm  | -                     |
| ESD Robustness, HBM BM <sup>2</sup> | V <sub>ESD,H</sub>   | _      | _    | 1000 | V    | -                     |
| ESD Robustness, CDM <sup>3</sup>    | V <sub>ESD,CDM</sub> | _      | _    | 250  | V    | -                     |

<sup>&</sup>lt;sup>1</sup>All voltages refer to GND-Nodes unless otherwise noted

Warning: Stresses above the max. values listed here may cause permanent damage to the device. Maximum ratings are absolute ratings; exceeding only one of these values may cause irreversible damage to the integrated circuit. Exposure to conditions at or below absolute maximum rating but above the specified maximum operation conditions may affect device reliability and life time. Functionality of the device might not be given under these conditions.

**Table 2: Thermal Resistance** 

| Parameter                                      | Symbol      | Value | Unit |
|--|-------------|-------|------|
| Thermal Resistance - Junction - Solder (@25°C) | $R_{th,JS}$ | 19.6  | °K/W |

**Table 3: Recommended Operating Conditions** 

| Parameter             | Symbol              | Values |      |      | Unit | Note / Test Condition    |  |
|-----------------------|---------------------|--------|------|------|------|--------------------------|--|
|                       |                     | Min.   | Тур. | Max. |      |                          |  |
| Supply Voltage        | V <sub>cc</sub>     | 4.75   | _    | 5.25 | V    | -                        |  |
| Enable Voltage OFF    | V <sub>EN,OFF</sub> | 0      | _    | 0.63 | V    | -                        |  |
| Enable Voltage ON     | V <sub>EN,ON</sub>  | 1.17   | _    | 3.6  | V    | -                        |  |
| Operating Temperature | T <sub>A</sub>      | -40    | _    | 115  | °C   | Solder joint temperature |  |

#### Power-up and power-down sequences

The following sequences are required to be respected during power-up/down of the device.

Power-up sequence: 1. VCC1 and VCC2 -> on; 2. EN -> on.

Power-down sequence: 1. EN -> off; 2. VCC1 and VCC2 -> off.

Deviating from these sequences may cause permanent damage.

<sup>&</sup>lt;sup>2</sup>Human Body Model ANSI/ESDA/JEDECJS-001 (R =  $1.5k\Omega$ , C = 100pF)

<sup>&</sup>lt;sup>3</sup>Field-Induced Charged-Device Model ANSI/ESDA/JEDECJS-002. Simulates charging/discharging events that occur in production equipment and processes. Potential for CDM ESD events occurs whenever there is metal-to-metal contact in manufacturing.

### **Pre-Driver for Wireless Infrastructure Applications**



**Electrical Characteristics** 

### **6 Electrical Characteristics**

Table 4: Electrical Characteristics. Test conditions (unless otherwise noted): T=25°C,  $V_{\rm CC}$ =5V,  $f_{\rm RF}$ =2.5GHz

| Parameter                      | Symbol Values       |           |       | Unit | Note / Test Condition |  |
|--------------------------------|---------------------|-----------|-------|------|-----------------------|--|
|                                |                     | Min. Typ. |       | Max. |                       |  |
| RF Frequency                   | $f_{RF}$            | 2300      | _     | 2700 | MHz                   | -  |
| Current Consumption OFF        | I <sub>CC,OFF</sub> | _         | 1.2   | _    | mA                    | -  |
| Current Consumption ON         | I <sub>CC,ON</sub>  | _         | 121   | _    | mA                    | No RF input signal                         |
| Input Return Loss              | RL <sub>IN</sub>    | 19        | 30    | _    | dB                    | -  |
| Output Return Loss             | RL <sub>OUT</sub>   | 12        | 17    | _    | dB                    | -  |
| Gain                           | G                   | 34.3      | 34.8  | _    | dB                    | -  |
| Gain Flatness                  | G <sub>FLAT</sub>   | -         | -     | 0.22 | dB                    | Defined in any 100MHz within               |
|                                |                     |           |       |      |                       | band                                       |
| Output P1dB                    | OP <sub>1dB</sub>   | 28        | 28.9  | _    | dBm                   | -  |
| Output IP3                     | OIP <sub>3</sub>    | 32.6      | 34.2  | _    | dBm                   | $P_{IN1}=P_{IN2}=-25dBm$ , $\Delta f=1MHz$ |
| Adjacent Channel Leakage Ratio | ACLR                | _         | -47.1 | -44  | dBc                   | 20MHz E-TM1.1 with 9.8 dB                  |
|                                |                     |           |       |      |                       | PAPR @Pout=15 dBm                          |
| Noise Figure                   | NF                  | _         | 3.8   | 4.3  | dB                    | -  |
| Switching ON Time              | T <sub>ON</sub>     | _         | 0.45  | 0.5  | $\mu$ s               | P <sub>OUT</sub> to 90% of final value     |
| Switching OFF Time             | T <sub>OFF</sub>    | _         | _     | 0.3  | $\mu$ s               | Gain within <5% and power dis-             |
|                                |                     |           |       |      |                       | sipation <10% than in ON state             |



**Application Information** 

# 7 Application Information

### **Pin Configuration and Function**




Figure 2: BGAP2S20A Pin Configuration - Top View

**Table 5: Pin Definition and Function** 

| Pin No.                    | Name  | Function   |
|----------------------------|-------|--|
| 1,9                        | GND   | Ground   |
| 2                          | RFIN  | RF Input   |
| 4                          | VCC2  | 2 <sup>nd</sup> stage DC voltage supply  |
| 3, 5, 6, 7, 8, 11, 12, 14, | NC    | Not connected internally. It can be either left floating or connected to ground. |
| 15                         |       |  |
| 10                         | RFOUT | RF Output  |
| 13                         | VCC1  | 1 <sup>st</sup> stage DC voltage supply  |
| 16                         | EN    | Chip enable  |
| Backside Paddle            | GND   | Ground connection  |
|                            |       |  |

### **Pre-Driver for Wireless Infrastructure Applications**



**Application Information** 

### **Application Board Configuration**




Figure 3: BGAP2S20A Application Schematic

#### **Table 6: Bill of Materials Table**

|      |                           | 1  | I .   |
|------|---------------------------|--|---|
| 10nF | Capacitor, X7R, 0402      | -  | Various                                     |
| 1uF  | Capacitor, X7R, 0402      | -  | Various                                     |
| -    | Connector, SMA            | -  | Various                                     |
| _    | Pre-driver, PG-TSNP-16-12 | BGAP2S20A                                  | Infineon                                    |
|      | 1uF                       | 1uF Capacitor, X7R, 0402  - Connector, SMA | 1uF Capacitor, X7R, 0402 – Connector, SMA – |



Package Information

# **8 Package Information**




Figure 4: PG-TSNP-16-12 Package Outline (3.0mm x 3.0mm x 0.73mm)




Figure 5: PG-TSNP-16-12 Carrier Tape





| <b>Revision History</b> |  |
|-------------------------|--|
| Page or Item            | Subjects (major changes since previous revision)                 |
| all                     | Preliminary, Revision v1.0 - 2023-06-29                          |
| all                     | Preliminary, Revision v1.1 - 2023-08-03 Package changed to 16-12 |
|                         |  |

#### Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2023-08-03 Published by Infineon Technologies AG 81726 Munich, Germany

© 2023 Infineon Technologies AG. All Rights Reserved.

Do you have a question about any aspect of this document?
Email: erratum@infineon.com

Document reference Doc\_Number

#### IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie"). With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party. In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications. The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

#### WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.