SIPMOS ® Power Transistor

BUZ 30A H

- N channel
- Enhancement mode
- Avalanche-rated
- Pb-free lead plating; RoHS compliant
. Halogen-free according to IEC61249-2--21



Pin 1	Pin 2	Pin 3
G	D	S

Type	V_{DS}	I_D	$R_{DS(on)}$	Package	Pb-free
BUZ 30A H	200 V	21 A	0.13 Ω	PG-TO-220-3	Yes

Maximum Ratings

Parameter	Symbol	Values	Unit
Continuous drain current T_C = 26 ˚C	I_D	21	A
Pulsed drain current T_C = 25 ˚C	I_{Dpuls}	84	
Avalanche current,limited by T_{jmax}	I_{AR}	21	
Avalanche energy,periodic limited by T_{jmax}	E_{AR}	12	mJ
Avalanche energy, single pulse I_D = 21 A, V_{DD} = 50 V, R_{GS} = 25 Ω L = 1.53 mH, T_j = 25 ˚C	E_{AS}	450	
Gate source voltage	V_{GS}	± 20	V
Power dissipation T_C = 25 ˚C	P_{tot}	125	W
Operating temperature	T_j	-55 ... + 150	˚C
Storage temperature	T_{stg}	-55 ... + 150	
Thermal resistance, chip case	R_{thJC}	≤ 1	K/W
Thermal resistance, chip to ambient	R_{thJA}	75	
DIN humidity category, DIN 40 040		E	
IEC climatic category, DIN IEC 68-1		55 / 150 / 56	

Electrical Characteristics, at T_j = 25˚C, unless otherwise specified

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
Static Characteristics					
Drain- source breakdown voltage V_{GS} = 0 V, I_D = 0.25 mA, T_j = 25 ˚C	$V_{(BR)DSS}$	200	-	-	V
Gate threshold voltage V_{GS}=V_{DS}, I_D = 1 mA	$V_{GS(th)}$	2.1	3	4	
Zero gate voltage drain current V_{DS} = 200 V, V_{GS} = 0 V, T_j = 25 ˚C V_{DS} = 200 V, V_{GS} = 0 V, T_j = 125 ˚C	I_{DSS}	- -	0.1 10	1 100	µA
Gate-source leakage current V_{GS} = 20 V, V_{DS} = 0 V	I_{GSS}	-	10	100	nA
Drain-Source on-resistance V_{GS} = 10 V, I_D = 13.5 A	$R_{DS(on)}$	-	0.1	0.13	Ω

Electrical Characteristics, at T_j = 25°C, unless otherwise specified

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
Dynamic Characteristics					
Transconductance $V_{DS} \geq 2 * I_D * R_{DS(on)max}$, I_D = 13.5 A	g_{fs}	6	15	-	S
Input capacitance V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz	C_{iss}	-	1400	1900	pF
Output capacitance V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz	C_{oss}	-	280	400	
Reverse transfer capacitance V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz	C_{rss}	-	130	200	
Turn-on delay time V_{DD} = 30 V, V_{GS} = 10 V, I_D = 3 A R_{GS} = 50 Ω	$t_{d(on)}$	-	30	45	ns
Rise time V_{DD} = 30 V, V_{GS} = 10 V, I_D = 3 A R_{GS} = 50 Ω	t_r	-	70	110	
Turn-off delay time V_{DD} = 30 V, V_{GS} = 10 V, I_D = 3 A R_{GS} = 50 Ω	$t_{d(off)}$	-	250	320	
Fall time V_{DD} = 30 V, V_{GS} = 10 V, I_D = 3 A R_{GS} = 50 Ω	t_f	-	90	120	

Electrical Characteristics, at T_j = 25°C, unless otherwise specified

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
Reverse Diode					
Inverse diode continuous forward current T_C = 25 °C	I_S	-	-	21	A
Inverse diode direct current,pulsed T_C = 25 °C	I_{SM}	-	-	84	
Inverse diode forward voltage V_{GS} = 0 V, I_F = 42 A	V_{SD}	-	1.2	1.6	V
Reverse recovery time V_R = 100 V, I_F=I_S, di_F/dt = 100 A/µs	t_{rr}	-	180	-	ns
Reverse recovery charge V_R = 100 V, I_F=I_S, di_F/dt = 100 A/µs	Q_{rr}	-	1.2	-	µC

Power dissipation

$P_{tot} = f(T_C)$



Drain current

$I_D = f(T_C)$

parameter: $V_{GS} \geq 10$ V



Safe operating area

$I_D = f(V_{DS})$

parameter: $D = 0.01$, $T_C = 25$°C



Transient thermal impedance

$Z_{th\,JC} = f(t_p)$

parameter: $D = t_p / T$



Typ. output characteristics

$I_D = f(V_{DS})$

parameter: t_p = 80 µs



Typ. drain-source on-resistance

$R_{DS\ (on)} = f(I_D)$

parameter: V_{GS}



Typ. transfer characteristics $I_D = f(V_{GS})$

parameter: t_p = 80 µs

$V_{DS} \geq 2 \times I_D \times R_{DS(on)max}$



Typ. forward transconductance $g_{fs} = f(I_D)$

parameter: t_p = 80 µs,

$V_{DS} \geq 2 \times I_D \times R_{DS(on)max}$



Drain-source on-resistance

$R_{DS\ (on)} = f(T_j)$

parameter: I_D = 13.5 A, V_{GS} = 10 V



Gate threshold voltage

$V_{GS\ (th)} = f(T_j)$

parameter: $V_{GS} = V_{DS}$, I_D = 1 mA



Typ. capacitances

$C = f(V_{DS})$

parameter: V_{GS} = 0V, f = 1MHz



Forward characteristics of reverse diode

$I_F = f(V_{SD})$

parameter: T_j, t_p = 80 µs



Avalanche energy $E_{AS} = f(T_j)$
parameter: I_D = 21 A, V_{DD} = 50 V
R_{GS} = 25 Ω, L = 1.53 mH



Typ. gate charge
$V_{GS} = f(Q_{Gate})$
parameter: $I_{D\ puls}$ = 32 A



Drain-source breakdown voltage
$V_{(BR)DSS} = f(T_j)$



Package Drawing: TO220-3



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.30	4.57	0.169	0.180
A1	1.17	1.40	0.046	0.055
A2	2.15	2.72	0.085	0.107
b	0.65	0.86	0.026	0.034
b1	0.95	1.40	0.037	0.055
b2	0.95	1.15	0.037	0.045
b3	0.65	1.15	0.026	0.045
c	0.33	0.60	0.013	0.024
D	14.81	15.95	0.583	0.628
D1	8.51	9.45	0.335	0.372
D2	12.19	13.10	0.480	0.516
E	9.70	10.36	0.382	0.408
E1	6.50	8.60	0.256	0.339
e	2.54		0.100	
e1	5.08		0.200	
N	3		3	
H1	5.90	6.90	0.232	0.272
L	13.00	14.00	0.512	0.551
L1	-	4.80	-	0.189
øP	3.60	3.89	0.142	0.153
Q	2.60	3.00	0.102	0.118

DOCUMENT NO.
Z8B00003318

SCALE 0 2.5 0 2.5 5mm

EUROPEAN PROJECTION

ISSUE DATE
30-07-2009

REVISION
06

Published by
Infineon Technologies AG
81726 Munich, Germany

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.
Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.