

Please note that Cypress is an Infineon Technologies Company.

The document following this cover page is marked as “Cypress” document as this is the company that originally developed the product. Please note that Infineon will continue to offer the product to new and existing customers as part of the Infineon product portfolio.

Continuity of document content

The fact that Infineon offers the following product as part of the Infineon product portfolio does not lead to any changes to this document. Future revisions will occur when appropriate, and any changes will be set out on the document history page.

Continuity of ordering part numbers

Infineon continues to support existing part numbers. Please continue to use the ordering part numbers listed in the datasheet for ordering.

Objective

This code example demonstrates the use of the current digital-to-analog converter (IDAC).

Overview

This code example shows the capability of the [Current Digital-to-Analog Converter](#) (IDAC) to change its current output with firmware. The current increases when a switch is pressed. Once the output reaches its maximum value, it resets to zero and starts to increase the value again. If switch is not pressed, the last value is maintained.

Requirements

Tool: PSoC Creator™ 4.2 or higher

Programming Language: C (ARM® GCC 5.4)


Associated Parts: PSoC® 4

Hardware: [CY8CKIT-042](#), [CY8CKIT-042-BLE](#), [CY8CKIT-044](#), [CY8CKIT-046](#)

Design

The example demonstrates one way of using the IDAC Component. It is configured as an 8-bit IDAC with a range of 0–612 μA (2.4 $\mu\text{A}/\text{count}$). Firmware detects when the switch (SW2) is pressed and slowly increases the IDAC output with the `IDAC8_SetValue()` function, until the switch is released. See [Figure 1](#) below for schematic.

Figure 1. Top Design Schematic



Kit Configuration and Pin Assignments

1. Select the appropriate device for the kit you are using according to [Table 1](#). By default the project is configured for the CY8CKIT-042. To select the correct device, click on the “Project” menu and select the “Device Selector” sub-menu.

Table 1. Development Kits and Associated Devices

Development Kit	Device
CY8CKIT-042	CY8C4245AXI-483
CY8CKIT-042-BLE	CY8C4247LQI-BL483
CY8CKIT-044	CY8C4247AZI-M485
CY8CKIT-046	CY8C4248BZI-L489

- You can change the pins used by selecting the “Pins” tab in the “Design Wide Resources” view to match [Table 2](#). As mentioned above, the project is initially configured for the CY8CKIT-042 kit, so all references to GPIO pins used will be for the CY8CKIT-042 kit.

Table 2. Pin Assignments

Pin Name	Development Kit			
	CY8CKIT-042	CY8CKIT-042-BLE	CY8CKIT-044	CY8CKIT-046
Iout	P0[0]	P0[0]	P0[0]	P1[2]
SW2	P0[7]	P2[7]	P0[7]	P0[7]

Components


[Table 3](#) lists the PSoC Creator Components used in this example (CY8CKIT-042), as well as the hardware resources used by each.

Table 3. PSoC Creator Components

Component	Usage	Hardware Resources
IDAC	Current DAC	CSIDAC0/1
Pin	IDAC output	GPIO (pin P0[0])
Pin	SW2 Input	GPIO (pin P0[7])

The IDAC is configured for positive polarity (source), 8-bit resolution and the 612 uA range, as shown in [Figure 2](#). Initial value doesn't matter since it will be over written by the firmware to 0 uA.

Figure 2. IDAC Configuration



Operation

This example project requires a multi-meter to measure the output current. Follow these steps below to exercise the project.

- Make sure that the kit has been configured as instructed in the [Kit Configuration and Pin Assignments](#) section.
- Connect the USB cable between the PC and the kit.
- Build the project and program the PSoC 4 device.

4. Measure the current between pin lout (P0[0]) and Vss. This can be done in two ways:
 - a. Use a sensitive amp meter that can resolve down to a couple uAmps and connect it across pin lout (P0[0]) and Vss. (Remove the 1K resistor shown in the schematic.)
 - b. Leave the 1K resistor in the circuit as shown and use a voltmeter to measure the voltage across the resistor. The conversion between amps and volts is just ohms law, $I = V/R$. With a 1K shunt resistor, the voltage output will be between 0 and 612mV instead of 0 to 612uA.
5. Press and hold the switch (SW2) to observe the current (or voltage) increase until it exceeds 612uA (or 612mV) then starts back at 0.

Related Documents

Table 4 lists the relevant application notes, code examples, Component datasheets, and device and DVK documentation.

Table 4. Related Documents

Application Notes		
AN79953	Getting Started with PSoC 4	Describes PSoC 4 and shows how to build the attached code example
AN60590	PSoC 3, PSoC 4, and PSoC 5LP – Temperature Measurement with a Diode	Explains the use of a diode and an IDAC as a temperature sensor
Code Examples		
CE204022	PSoC 4 IDAC7 Sawtooth Waveform Generator	Shows the basics of using the IDAC7 available in some PSoC 4 devices. A simple sawtooth or voltage ramp waveform is generated using the IDAC7 current output digital-to-analog converter.
PSoC Creator Component Datasheets		
Current Digital to Analog Converter	Supports the IDAC Component	
Pins	Supports the connection of hardware resources to physical pins	
Device Documentation		
PSoC 4 Datasheets		
PSoC 4 Technical Reference Manuals		
Development Kit (DVK) Documentation		
PSoC 4 Kits		

Document History

Document Title: CE95327 – PSoC® 4 Current Digital-to-Analog Converter

Document Number: 001-95327

Revision	ECN	Orig. of Change	Submission Date	Description of Change
**	5526019	WESL	11/23/2016	New code example
*A	6097931	MEH	04/20/2017	Changed project operation and fixed errors in document and firmware listing. Updated example to PSoC Creator 4.2. Updated template

Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at [Cypress Locations](#).

Products

ARM® Cortex® Microcontrollers	cypress.com/arm
Automotive	cypress.com/automotive
Clocks & Buffers	cypress.com/clocks
Interface	cypress.com/interface
Internet of Things	cypress.com/iot
Memory	cypress.com/memory
Microcontrollers	cypress.com/mcu
PSoC	cypress.com/psoc
Power Management ICs	cypress.com/pmic
Touch Sensing	cypress.com/touch
USB Controllers	cypress.com/usb
Wireless Connectivity	cypress.com/wireless

PSoC® Solutions

[PSoC 1](#) | [PSoC 3](#) | [PSoC 4](#) | [PSoC 5LP](#) | [PSoC 6](#)

Cypress Developer Community

[Forums](#) | [WICED IOT Forums](#) | [Projects](#) | [Videos](#) | [Blogs](#) | [Training](#) | [Components](#)

Technical Support

[cypress.com/support](#)

All other trademarks or registered trademarks referenced herein are the property of their respective owners.



Cypress Semiconductor
198 Champion Court
San Jose, CA 95134-1709

© Cypress Semiconductor Corporation, 2016-2018. This document is the property of Cypress Semiconductor Corporation and its subsidiaries, including Spansion LLC ("Cypress"). This document, including any software or firmware included or referenced in this document ("Software"), is owned by Cypress under the intellectual property laws and treaties of the United States and other countries worldwide. Cypress reserves all rights under such laws and treaties and does not, except as specifically stated in this paragraph, grant any license under its patents, copyrights, trademarks, or other intellectual property rights. If the Software is not accompanied by a license agreement and you do not otherwise have a written agreement with Cypress governing the use of the Software, then Cypress hereby grants you a personal, non-exclusive, nontransferable license (without the right to sublicense) (1) under its copyright rights in the Software (a) for Software provided in source code form, to modify and reproduce the Software solely for use with Cypress hardware products, only internally within your organization, and (b) to distribute the Software in binary code form externally to end users (either directly or indirectly through resellers and distributors), solely for use on Cypress hardware product units, and (2) under those claims of Cypress's patents that are infringed by the Software (as provided by Cypress, unmodified) to make, use, distribute, and import the Software solely for use with Cypress hardware products. Any other use, reproduction, modification, translation, or compilation of the Software is prohibited.

TO THE EXTENT PERMITTED BY APPLICABLE LAW, CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS DOCUMENT OR ANY SOFTWARE OR ACCOMPANYING HARDWARE, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. To the extent permitted by applicable law, Cypress reserves the right to make changes to this document without further notice. Cypress does not assume any liability arising out of the application or use of any product or circuit described in this document. Any information provided in this document, including any sample design information or programming code, is provided only for reference purposes. It is the responsibility of the user of this document to properly design, program, and test the functionality and safety of any application made of this information and any resulting product. Cypress products are not designed, intended, or authorized for use as critical components in systems designed or intended for the operation of weapons, weapons systems, nuclear installations, life-support devices or systems, other medical devices or systems (including resuscitation equipment and surgical implants), pollution control or hazardous substances management, or other uses where the failure of the device or system could cause personal injury, death, or property damage ("Unintended Uses"). A critical component is any component of a device or system whose failure to perform can be reasonably expected to cause the failure of the device or system, or to affect its safety or effectiveness. Cypress is not liable, in whole or in part, and you shall and hereby do release Cypress from any claim, damage, or other liability arising from or related to all Unintended Uses of Cypress products. You shall indemnify and hold Cypress harmless from and against all claims, costs, damages, and other liabilities, including claims for personal injury or death, arising from or related to any Unintended Uses of Cypress products.

Cypress, the Cypress logo, Spansion, the Spansion logo, and combinations thereof, WICED, PSoC, CapSense, EZ-USB, F-RAM, and Traveo are trademarks or registered trademarks of Cypress in the United States and other countries. For a more complete list of Cypress trademarks, visit [cypress.com](#). Other names and brands may be claimed as property of their respective owners.