



Please note that Cypress is an Infineon Technologies Company.

The document following this cover page is marked as “Cypress” document as this is the company that originally developed the product. Please note that Infineon will continue to offer the product to new and existing customers as part of the Infineon product portfolio.

Continuity of document content

The fact that Infineon offers the following product as part of the Infineon product portfolio does not lead to any changes to this document. Future revisions will occur when appropriate, and any changes will be set out on the document history page.

Continuity of ordering part numbers

Infineon continues to support existing part numbers. Please continue to use the ordering part numbers listed in the datasheet for ordering.



THIS SPEC IS OBSOLETE.

Spec No: 001-91027

Spec Title: CY8CTMG240, TRUETOUCH(R) MULTI-TOUCH GESTURE TOUCHSCREEN CONTROLLER - SUMMARY

Replaced by: None

TrueTouch[®] Multi-Touch Gesture Touchscreen Controller

Features

- TrueTouch[®] capacitive touchscreen controller
 - Two finger positions reported
 - Second finger used for gesture detection
 - Screen sizes up to 3.6" diagonal
 - Up to 32 sense pins
 - Fat finger detection and tracking
 - Large-object detection
 - Self-calibrating to environmental changes
 - Resistant to LCD noise
 - Robust operation in noisy RF environments
 - 1.71 V to 5.5 V input supply range
 - Single supply voltage
 - Compatible with 1.8 V I2C signaling
 - Integrated voltage regulators – no need for dedicated voltage regulators
- Performance
 - Noise-free resolution: 0.1 mm
 - Accuracy with 1 finger on the touchscreen: 0.8 mm
 - Finger separation: 3.5 mm
 - >110 Hz refresh rate with one finger on the touchscreen
 - Best in class active power of 3.6 mW
 - Best in class low-power state current: 0.7 mA
 - Best in class deep sleep state current: 100 nA
- Extended feature set
 - Water rejection – no false touches
 - Capacitive buttons supported
 - On-chip gesture detection
 - Single-click, double-click, and two-finger clicks
 - One-finger and two-finger pan gestures
 - Zoom-in and zoom-out
- Sensor and system design
 - Supports chip-on-flex and chip-on-board
 - Supports plastic film and glass touch sensors
 - Supports a variety of touchscreen sensors and stickups
- Communication interface
 - I2C slave up to 400 kHz
 - SPI slave with 2 Mbps sustained data throughput
 - Field upgrades through integrated bootloader
- Host development kit (HDK)
 - Android driver support
 - Supports custom driver development
 - TrueTouch host emulator – acts as host for early prototyping
- Package options
 - 32-pin 5 × 5 × 0.55 mm QFN
 - 48-pin 7 × 7 × 1.0 mm QFN
 - 30-ball 2.2 × 2.32 × 0.4 mm WLCSP

Ordering Information


The following table lists the TrueTouch Standard Product Multi-Touch Gesture Touchscreen Controllers. For information on other TrueTouch families, please visit <http://www.cypress.com/truetouch>.

Table 1. Device Ordering Information

Part Number	TrueTouch					Sensor		Minimum Interface Voltage	Supply Voltage Operating Range	Bootloader	I2C	SPI	UART	Package
	Typical Screen Size (in.) (4:3 Aspect Ratio)	Maximum Nodes	Maximum Fingers	On-chip Gesture Decoding	Large Object Detection	Glass	Film							
CY8CTMG240-LQI-01(T)	3.3	24	2	✓	✓	✓	✓	1.8	1.71-5.5	✓	✓	✓	✓	32-pin QFN
CY8CTMG240-LTI-01(T)	3.6	32	2	✓	✓	✓	✓	1.8	1.71-5.5	✓	✓	✓	✓	48-pin QFN
CP8CTMG240-FNC-01	3.3	24	2	✓	✓	✓	✓	1.8	1.71-5.5	✓	✓	✓	✓	30-ball WLCSP

Ordering Code Definitions

CY8 C TMG 240 - xxx xx(T)



Document History Page

Document Title: CY8CTMG240, TrueTouch® Multi-Touch Gesture Touchscreen Controller Document Number: 001-91027				
Rev.	ECN No.	Orig. of Change	Submission Date	Description of Change
**	4278978	SWU	02/12/2014	New summary datasheet.

Sales, Solutions, and Legal Information

Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer’s representatives, and distributors. To find the office closest to you, visit us at [Cypress Locations](#).

Products

- Automotive cypress.com/go/automotive
- Clocks & Buffers cypress.com/go/clocks
- Interface cypress.com/go/interface
- Lighting & Power Control cypress.com/go/powerpsoc
cypress.com/go/plc
- Memory cypress.com/go/memory
- PSoC cypress.com/go/psoc
- Touch Sensing cypress.com/go/touch
- USB Controllers cypress.com/go/USB
- Wireless/RF cypress.com/go/wireless

PSoC® Solutions

- psoc.cypress.com/solutions
- PSoC 1 | PSoC 3 | PSoC 4 | PSoC 5LP

Cypress Developer Community

- [Community](#) | [Forums](#) | [Blogs](#) | [Video](#) | [Training](#)

Technical Support

- cypress.com/go/support

© Cypress Semiconductor Corporation, 2014. The information contained herein is subject to change without notice. Cypress Semiconductor Corporation assumes no responsibility for the use of any circuitry other than circuitry embodied in a Cypress product. Nor does it convey or imply any license under patent or other rights. Cypress products are not warranted nor intended to be used for medical, life support, life saving, critical control or safety applications, unless pursuant to an express written agreement with Cypress. Furthermore, Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress products in life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

Any Source Code (software and/or firmware) is owned by Cypress Semiconductor Corporation (Cypress) and is protected by and subject to worldwide patent protection (United States and foreign), United States copyright laws and international treaty provisions. Cypress hereby grants to licensee a personal, non-exclusive, non-transferable license to copy, use, modify, create derivative works of, and compile the Cypress Source Code and derivative works for the sole purpose of creating custom software and or firmware in support of licensee product to be used only in conjunction with a Cypress integrated circuit as specified in the applicable agreement. Any reproduction, modification, translation, compilation, or representation of this Source Code except as specified above is prohibited without the express written permission of Cypress.

Disclaimer: CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS MATERIAL, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Cypress reserves the right to make changes without further notice to the materials described herein. Cypress does not assume any liability arising out of the application or use of any product or circuit described herein. Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress’ product in a life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

Use may be limited by and subject to the applicable Cypress software license agreement.