







SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	4.47
A1	1.02	1.27	1.52
A2	2.43	-	2.95
b	0.41	0.46	0.51
b2	1.22	-	1.32
c	0.23	0.25	0.3
D	40.26	40.64	41.02
E	7.62	7.87	8.13
E1	7.24	7.49	7.75
e	2.54 BSC		
eA	7.62 REF		
L	3.18	-	4.32

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []