

Preliminary datasheet

EasyBRIDGE module with chopper configuration and PressFIT / pre-applied Thermal Interface Material

Features

- Electrical features
 - $V_{CES} = 1200\text{ V}$
 - $I_{C\text{ nom}} = 50\text{ A} / I_{CRM} = 100\text{ A}$
 - TRENCHSTOP™ IGBT7
- Mechanical features
 - Al_2O_3 substrate with low thermal resistance
 - Compact design
 - PressFIT contact technology
 - Pre-applied Thermal Interface Material
 - Rugged mounting due to integrated mounting clamps



Typical appearance

Potential applications

- Auxiliary inverters
- Air conditioning
- Motor drives
- Servo drives

Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068

Description




Table of contents

	Description	1
	Features	1
	Potential applications	1
	Product validation	1
	Table of contents	2
1	Package	3
2	IGBT-Chopper	3
3	Diode, Chopper	5
4	Diode, Rectifier	6
5	Characteristics diagrams	8
6	Circuit diagram	11
7	Package outlines	12
	Revision history	13
	Disclaimer	14

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, $f = 50 \text{ Hz}$, $t = 1 \text{ min}$	2.5	kV
Internal Isolation		basic insulation (class 1, IEC 61140)	Al_2O_3	
Creepage distance	d_{Creep}	terminal to heatsink	11.5	mm
Creepage distance	d_{Creep}	terminal to terminal	6.3	mm
Clearance	d_{Clear}	terminal to heatsink	10.0	mm
Clearance	d_{Clear}	terminal to terminal	5.0	mm
Comparative tracking index	CTI		> 200	
RTI Elec.	RTI	housing	140	°C

Table 2 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Stray inductance module	L_{SCE}			30		nH
Module lead resistance, terminals - chip	$R_{AA'+CC'}$	$T_H = 25^\circ\text{C}$, per switch		4		mΩ
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	$T_H = 25^\circ\text{C}$, per switch		6		mΩ
Storage temperature	T_{stg}		-40		125	°C
Maximum baseplate operation temperature	T_{BPmax}				125	°C
Mounting force per clamp	F		20		50	N
Weight	G			24		g

Note: The current under continuous operation is limited to 25A rms per connector pin.
Storage and shipment of modules with TIM => see AN 2012-07

2 IGBT-Chopper

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Collector-emitter voltage	V_{CES}		$T_{vj} = 25^\circ\text{C}$	1200	V
Continuous DC collector current	I_{CDC}	$T_{vj \max} = 175^\circ\text{C}$	$T_H = 85^\circ\text{C}$	50	A
Repetitive peak collector current	I_{CRM}	$t_p = 1 \text{ ms}$		100	A

Table 3 Maximum rated values (continued)

Parameter	Symbol	Note or test condition	Values	Unit
Gate-emitter peak voltage	V_{GES}		± 20	V

Table 4 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CE\ sat}$	$I_C = 50\text{ A}$, $V_{GE} = 15\text{ V}$	$T_{vj} = 25\text{ °C}$	1.50	TBD	V
			$T_{vj} = 125\text{ °C}$	1.64		
			$T_{vj} = 175\text{ °C}$	1.72		
Gate threshold voltage	V_{GEth}	$I_C = 1.28\text{ mA}$, $V_{CE} = V_{GE}$, $T_{vj} = 25\text{ °C}$	5.15	5.80	6.45	V
Gate charge	Q_G	$V_{GE} = \pm 15\text{ V}$, $V_{CE} = 600\text{ V}$		0.92		μC
Internal gate resistor	R_{Gint}	$T_{vj} = 25\text{ °C}$		0		Ω
Input capacitance	C_{ies}	$f = 100\text{ kHz}$, $T_{vj} = 25\text{ °C}$, $V_{CE} = 25\text{ V}$, $V_{GE} = 0\text{ V}$		11.1		nF
Reverse transfer capacitance	C_{res}	$f = 100\text{ kHz}$, $T_{vj} = 25\text{ °C}$, $V_{CE} = 25\text{ V}$, $V_{GE} = 0\text{ V}$		0.039		nF
Collector-emitter cut-off current	I_{CES}	$V_{CE} = 1200\text{ V}$, $V_{GE} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$		0.0062	mA
Gate-emitter leakage current	I_{GES}	$V_{CE} = 0\text{ V}$, $V_{GE} = 20\text{ V}$, $T_{vj} = 25\text{ °C}$			100	nA
Turn-on delay time (inductive load)	t_{don}	$I_C = 50\text{ A}$, $V_{CE} = 600\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $R_{Gon} = 5.1\text{ }\Omega$	$T_{vj} = 25\text{ °C}$	0.042		μs
			$T_{vj} = 125\text{ °C}$	0.045		
			$T_{vj} = 175\text{ °C}$	0.046		
Rise time (inductive load)	t_r	$I_C = 50\text{ A}$, $V_{CE} = 600\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $R_{Gon} = 5.1\text{ }\Omega$	$T_{vj} = 25\text{ °C}$	0.036		μs
			$T_{vj} = 125\text{ °C}$	0.040		
			$T_{vj} = 175\text{ °C}$	0.043		
Turn-off delay time (inductive load)	t_{doff}	$I_C = 50\text{ A}$, $V_{CE} = 600\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $R_{Goff} = 5.1\text{ }\Omega$	$T_{vj} = 25\text{ °C}$	0.270		μs
			$T_{vj} = 125\text{ °C}$	0.350		
			$T_{vj} = 175\text{ °C}$	0.370		
Fall time (inductive load)	t_f	$I_C = 50\text{ A}$, $V_{CE} = 600\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $R_{Goff} = 5.1\text{ }\Omega$	$T_{vj} = 25\text{ °C}$	0.110		μs
			$T_{vj} = 125\text{ °C}$	0.200		
			$T_{vj} = 175\text{ °C}$	0.270		
Turn-on energy loss per pulse	E_{on}	$I_C = 50\text{ A}$, $V_{CE} = 600\text{ V}$, $L_\sigma = 35\text{ nH}$, $V_{GE} = \pm 15\text{ V}$, $R_{Gon} = 5.1\text{ }\Omega$, $di/dt = 850\text{ A}/\mu\text{s}$ ($T_{vj} = 175\text{ °C}$)	$T_{vj} = 25\text{ °C}$	4.47		mJ
			$T_{vj} = 125\text{ °C}$	5.2		
			$T_{vj} = 175\text{ °C}$	5.67		
Turn-off energy loss per pulse	E_{off}	$I_C = 50\text{ A}$, $V_{CE} = 600\text{ V}$, $L_\sigma = 35\text{ nH}$, $V_{GE} = \pm 15\text{ V}$, $R_{Goff} = 5.1\text{ }\Omega$, $dv/dt = 2900\text{ V}/\mu\text{s}$ ($T_{vj} = 175\text{ °C}$)	$T_{vj} = 25\text{ °C}$	3.36		mJ
			$T_{vj} = 125\text{ °C}$	5.25		
			$T_{vj} = 175\text{ °C}$	6.45		

Table 4 Characteristic values (continued)

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
SC data	I_{SC}	$V_{GE} \leq 15 \text{ V}, V_{CC} = 800 \text{ V}, V_{CEmax} = V_{CES} - L_{sCE} \cdot di/dt$	$t_P \leq 8 \mu\text{s}, T_{vj} = 150^\circ\text{C}$	190		A
			$t_P \leq 7 \mu\text{s}, T_{vj} = 175^\circ\text{C}$	180		
Thermal resistance, junction to heatsink	R_{thJH}	per IGBT, Valid with IFX pre-applied Thermal Interface Material			0.840	K/W
Temperature under switching conditions	$T_{vj op}$		-40		175	$^\circ\text{C}$

Note: $T_{vj op} > 150^\circ\text{C}$ is allowed for operation at overload conditions. For detailed specifications, please refer to AN 2018-14.

3 Diode, Chopper

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Repetitive peak reverse voltage	V_{RRM}		$T_{vj} = 25^\circ\text{C}$	1200	V
Continuous DC forward current	I_F			25	A
Repetitive peak forward current	I_{FRM}	$t_P = 1 \text{ ms}$		50	A
I^2t - value	I^2t	$V_R = 0 \text{ V}, t_P = 10 \text{ ms}$	$T_{vj} = 125^\circ\text{C}$	72.5	A^2s
			$T_{vj} = 175^\circ\text{C}$	63	

Table 6 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 25 \text{ A}, V_{GE} = 0 \text{ V}$	$T_{vj} = 25^\circ\text{C}$	1.83		V
			$T_{vj} = 125^\circ\text{C}$	1.70		
			$T_{vj} = 175^\circ\text{C}$	1.63		
Peak reverse recovery current	I_{RM}	$I_F = 25 \text{ A}, V_R = 600 \text{ V}, V_{GE} = -15 \text{ V}, -di_F/dt = 960 \text{ A}/\mu\text{s} (T_{vj} = 175^\circ\text{C})$	$T_{vj} = 25^\circ\text{C}$	21.6		A
			$T_{vj} = 125^\circ\text{C}$	25.3		
			$T_{vj} = 175^\circ\text{C}$	27.6		

Table 6 Characteristic values (continued)

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Recovered charge	Q_r	$I_F = 25\text{ A}$, $V_R = 600\text{ V}$, $V_{GE} = -15\text{ V}$, $-di_F/dt = 960\text{ A}/\mu\text{s}$ ($T_{vj} = 175\text{ }^\circ\text{C}$)	$T_{vj} = 25\text{ }^\circ\text{C}$	1.89		μC
			$T_{vj} = 125\text{ }^\circ\text{C}$	3.53		
			$T_{vj} = 175\text{ }^\circ\text{C}$	4.62		
Reverse recovery energy	E_{rec}	$I_F = 25\text{ A}$, $V_R = 600\text{ V}$, $V_{GE} = -15\text{ V}$, $-di_F/dt = 960\text{ A}/\mu\text{s}$ ($T_{vj} = 175\text{ }^\circ\text{C}$)	$T_{vj} = 25\text{ }^\circ\text{C}$	0.62		mJ
			$T_{vj} = 125\text{ }^\circ\text{C}$	1.3		
			$T_{vj} = 175\text{ }^\circ\text{C}$	1.74		
Thermal resistance, junction to heatsink	R_{thJH}	per diode, Valid with IFX pre-applied Thermal Interface Material			1.90	K/W
Temperature under switching conditions	$T_{vj\text{ op}}$		-40		175	$^\circ\text{C}$

Note: $T_{vj\text{ op}} > 150\text{ }^\circ\text{C}$ is allowed for operation at overload conditions. For detailed specifications, please refer to AN 2018-14.

4 Diode, Rectifier

Table 7 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Repetitive peak reverse voltage	V_{RRM}	$T_{vj} = 25\text{ }^\circ\text{C}$	1600	V
Maximum RMS forward current per chip	I_{FRMSM}	$T_H = 100\text{ }^\circ\text{C}$	50	A
Maximum RMS current at rectifier output	I_{RMSM}	$T_H = 100\text{ }^\circ\text{C}$	85	A
Surge forward current	I_{FSM}	$t_p = 10\text{ ms}$	$T_{vj} = 25\text{ }^\circ\text{C}$	A
			$T_{vj} = 150\text{ }^\circ\text{C}$	
I^2t - value	I^2t	$t_p = 10\text{ ms}$	$T_{vj} = 25\text{ }^\circ\text{C}$	A^2s
			$T_{vj} = 150\text{ }^\circ\text{C}$	

Table 8 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 50\text{ A}$, $T_{vj} = 150\text{ }^\circ\text{C}$		0.96		V
Reverse current	I_r	$T_{vj} = 150\text{ }^\circ\text{C}$, $V_R = 1600\text{ V}$		1		mA
Thermal resistance, junction to heatsink	R_{thJH}	per diode, Valid with IFX pre-applied Thermal Interface Material			1.11	K/W


Table 8 **Characteristic values (continued)**

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Temperature under switching conditions	$T_{vj, op}$		-40		150	°C

5 Characteristics diagrams


reverse bias safe operating area (RBSOA), IGBT-Chopper

$I_C = f(V_{CE})$
 $R_{Goff} = 5.1 \Omega$, $V_{GE} = \pm 15 \text{ V}$, $T_{vj} = 175 \text{ }^\circ\text{C}$




transfer characteristic (typical), IGBT-Chopper

$I_C = f(V_{GE})$
 $V_{CE} = 20 \text{ V}$




output characteristic (typical), IGBT-Chopper

$I_C = f(V_{CE})$
 $V_{GE} = 15 \text{ V}$



output characteristic (typical), IGBT-Chopper


$I_C = f(V_{CE})$
 $T_{vj} = 175 \text{ }^\circ\text{C}$



5 Characteristics diagrams


transient thermal impedance , IGBT-Chopper

$Z_{th} = f(t)$




transient thermal impedance , Diode, Chopper

$Z_{th} = f(t)$




forward characteristic of (typical), Diode, Chopper

$I_F = f(V_F)$



transient thermal impedance , Diode, Rectifier


$Z_{th} = f(t)$



5 Characteristics diagrams

forward characteristic of (typical), Diode, Rectifier

$I_F = f(V_F)$



6 Circuit diagram




Figure 2

7 Package outlines




Figure 3

Revision history

Revision history

Document revision	Date of release	Description of changes
0.10	2021-08-27	Initial version

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2021-08-27

Published by

Infineon Technologies AG
81726 Munich, Germany

© 2021 Infineon Technologies AG
All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-AAJ547-002

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.