

CY4533 BCR Evaluation Kit

CONTENTS	
PAGE	DESCRIPTION
01	Title, Table of Contents & Drawing Numbers
02	Block Diagram
03	BCR Connections
04	Power Selectors and LEDs
05	Type-C Connector and Load Switch
06	Revision History

Drawing Numbers	
PCBA	121-60538-01
PCB	600-60538-01
FAB DRW	610-60538-01
ASSY DRW	620-60538-01
SCH DRW	630-60538-01



CYPRESS SEMICONDUCTOR
198 CHAMPION COURT
SAN JOSE, CA 95134
(408) 943-2600

CYPRESS SEMICONDUCTOR © 2018

SCH Title : CY4533 BCR Evaluation Kit

Page Title : Title Page

Size A4	Document Number 630-60538-01	Drawn By KUMR	Approved By PDS	Rev 02
Date: Friday, December 07, 2018		Sheet 1 of 6		

D




A


A

Size A4	Document Number 630-60538-01	Drawn By KUMR	Approved By PDS	Rev 02
Date: Friday, December 07, 2018			Sheet 2 of 6	


SUPPLY DECOUPLING CAPS



BCR Connections



GPIO HEADER, HPI INTERFACE AND FLIP



HPI pins (I2C Slave at address 0x08) can be connected to an SoC/MCU

FLIP pin can be connected to a MUX
 FLIP = 0 when Type-C Plug is upside-up
 FLIP = 1 when Type-C Plug is upside-down
 (Output is open drain: 0 or High-Z)



CYPRESS
 EMBEDDED IN TOMORROW™

CYPRESS SEMICONDUCTOR
 198 CHAMPION COURT
 SAN JOSE, CA 95134
 (408) 943-2600

CYPRESS SEMICONDUCTOR © 2018

SCH Title : CY4533 BCR Evaluation Kit

Page Title : BCR Connections


Size	Document Number	Drawn By	Approved By	Rev
A4	630-60538-01	KUMR	PDS	02
Date:	Tuesday, December 11, 2018		Sheet	3 of 6

VBUS VOLTAGE SELECTORS: VBUS_MAX and VBUS_MIN


Requested voltage = (VBUS_MIN -> VBUS_MAX)
= between 5V ~ rotary_sw_option

VBUS_MAX Rotary Switch Options


Position 1 = 5V
Position 2 = 9V
Position 3 = 12V
Position 4 = 15V
Position 5 = 20V



Part Number = SS-10-15SPE
Manufacturer = Nidec Copal Electronics



VBUS_MAX is decided by the rotary switch




VBUS_MIN is set to 5V

VBUS_MIN and VBUS_MAX Resistor Options Table

V3P3 RATIO	0/6	1/6	2/6	3/6	4/6	5/6	6/6
VBUS_MAX, VBUS_MIN	5V	9V	12V	15V	19V	20V	
PULLUP (R3, R11)	none	5k	5k	5k	5k	0*	
PULLDOWN (R5, R14)	0*	1k	2.4k	5k	10k	none	


FAULT LED




FAULT pin goes HIGH when
(a) Power adapter does not advertise compatible PDOs
(b) VBUS is out of (vbus_min, vbus_max) range

VBUS CURRENT SELECTORS: ISNK_COARSE and ISNK_FINE

Requested (RDO) current = ISNK_COARSE + ISNK_FINE = 900mA



ISNK_COARSE is set to 0A




ISNK_FINE is set to +900mA

ISNK_COARSE and ISNK_FINE Resistor Options Table

V3P3 RATIO	0/6	1/6	2/6	3/6	4/6	>=5/6
ISNK_COARSE	0A	1A	2A	3A	4A	5A
ISNK_FINE	0mA	250mA	500mA	750mA	900mA	
PULLUP (R10, R13)	none	5k	5k	5k	5k	0*
PULLDOWN (R12, R4)	0*	1k	2.4k	5k	10k	none

* When pullup-pulldown combination is 0-none or none-0, use any resistor instead of 0-ohm

LED AND TEST POINTS



CYPRESS SEMICONDUCTOR
198 CHAMPION COURT
SAN JOSE, CA 95134
(408) 943-2600

CYPRESS SEMICONDUCTOR © 2018

SCH Title : CY4533 BCR Evaluation Kit

Page Title : Power Selectors and LEDs

Size	Document Number	Drawn By	Approved By	Rev
A4	630-60538-01	KUMR	PDS	02
Date:	Friday, December 07, 2018	Sheet	4 of 6	

[illegible]

SCH Title : CY4533 BCR Evaluation Kit
--

Size A4	Document Number 630-60538-01	Drawn By KUMR	Approved By PDS	Rev 02
------------	--	-------------------------	---------------------------	------------------

Date:	Friday, December 07, 2018	Sheet	6	of	6
-------	---------------------------	-------	---	----	---