



The following document contains information on Cypress products. Although the document is marked with the name "Spansion" and "Fujitsu", the company that originally developed the specification, Cypress will continue to offer these products to new and existing customers.

Continuity of Specifications

There is no change to this document as a result of offering the device as a Cypress product. Any changes that have been made are the result of normal document improvements and are noted in the document history page, where supported. Future revisions will occur when appropriate, and changes will be noted in a document history page.

Continuity of Ordering Part Numbers

Cypress continues to support existing part numbers. To order these products, please use only the Ordering Part Numbers listed in this document.

For More Information

Please contact your local sales office for additional information about Cypress products and solutions.

About Cypress

Cypress (NASDAQ: CY) delivers high-performance, high-quality solutions at the heart of today's most advanced embedded systems, from automotive, industrial and networking platforms to highly interactive consumer and mobile devices. With a broad, differentiated product portfolio that includes NOR flash memories, F-RAM™ and SRAM, Traveo™ microcontrollers, the industry's only PSoC® programmable system-on-chip solutions, analog and PMIC Power Management ICs, CapSense® capacitive touch-sensing controllers, and Wireless BLE Bluetooth® Low-Energy and USB connectivity solutions, Cypress is committed to providing its customers worldwide with consistent innovation, best-in-class support and exceptional system value.

Errata

This errata sheet is for MB96340 Series Data Sheet Rev. 3 (DS07-13802-3E).

F²MC-16FX
16-BIT MICROCONTROLLER
MB96340 Series
Data Sheet

2010.11.29

Date	Page	Item	Description
2010/ 11/29	14	I/O CIRCUIT TYPE Remarks of Type B	<p>Programmable feedback resistor was corrected as corrected by the shading below.</p> <p>(Error)</p> <p>approx. 2 * 5 MΩ</p> <p>(Correct)</p> <p>approx. 2 0 MΩ (X 1 A : 1 9. 5 MΩ、X 0 A : 0. 5 MΩ)</p>

[mcu_doc1093]