


Final datasheet

EconoDUAL™3 module with Trench/Fieldstop IGBT4 and emitter controlled 3 diode

Features

- Electrical features
 - $V_{CES} = 1700\text{ V}$
 - $I_{C\text{ nom}} = 150\text{ A} / I_{CRM} = 300\text{ A}$
 - High DC stability
 - High short-circuit capability
 - Low $V_{CE,sat}$
 - $T_{vj,op} = 150^{\circ}\text{C}$
 - Trench IGBT 4
 - $V_{CE,sat}$ with positive temperature coefficient
 - Suitable Infineon gate drivers can be found under <https://www.infineon.com/gdfinder>
- Mechanical features
 - Al_2O_3 substrate with low thermal resistance
 - High power density
 - Isolated base plate
 - PressFIT contact technology



Potential applications

- High-power converters
- Medium-voltage converters
- Wind turbines

Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068

Description




Table of contents

	Description	1
	Features	1
	Potential applications	1
	Product validation	1
	Table of contents	2
1	Package	3
2	IGBT, Inverter	4
3	Diode, Inverter	5
4	Characteristics diagrams	7
5	Circuit diagram	10
6	Package outlines	11
7	Module label code	12
	Revision history	13
	Disclaimer	14

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, $f = 50 \text{ Hz}$, $t = 1 \text{ min}$	3.4	kV
Isolation test voltage NTC	$V_{ISOL(NTC)}$	RMS, $f = 50 \text{ Hz}$, $t = 1 \text{ min}$	3.4	kV
Material of module baseplate			Cu	
Internal isolation		basic insulation (class 1, IEC 61140)	Al_2O_3	
Creepage distance	$d_{\text{Creep nom}}$	terminal to baseplate, nom.	> 15	mm
Creepage distance	$d_{\text{Creep min}}$	terminal to baseplate, min.	14.7	mm
Creepage distance	$d_{\text{Creep nom}}$	terminal to terminal, nom.	> 19.3	mm
Creepage distance	$d_{\text{Creep min}}$	terminal to terminal, min.	19.3	mm
Clearance	$d_{\text{Clear nom}}$	terminal to baseplate, nom.	> 12.5	mm
Clearance	$d_{\text{Clear min}}$	terminal to baseplate, min.	12.5	mm
Clearance	$d_{\text{Clear nom}}$	terminal to terminal, nom.	> 10	mm
Clearance	$d_{\text{Clear min}}$	terminal to terminal, min.	9.6	mm
Comparative tracking index	CTI		> 200	
Relative thermal index (electrical)	RTI	housing	140	°C

Table 2 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Stray inductance module	L_{sCE}				26		nH
Storage temperature	T_{stg}			-40		125	°C
Mounting torque for module mounting	M	- Mounting according to valid application note	M5, Screw	3		6	Nm
Terminal connection torque	M	- Mounting according to valid application note	M6, Screw	3		6	Nm
Weight	G				345		g

Note: The labels AC and DC on the housing do not have relevance.

2 IGBT, Inverter

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Collector-emitter voltage	V_{CES}		$T_{vj} = 25\text{ °C}$	1700	V
Continuous DC collector current	I_{CDC}	$T_{vj\text{ max}} = 175\text{ °C}$	$T_C = 100\text{ °C}$	150	A
Repetitive peak collector current	I_{CRM}	t_p limited by $T_{vj\text{ op}}$		300	A
Gate-emitter peak voltage	V_{GES}			± 20	V

Table 4 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CE\text{ sat}}$	$I_C = 150\text{ A}$, $V_{GE} = 15\text{ V}$	$T_{vj} = 25\text{ °C}$		1.95	2.30	V
			$T_{vj} = 125\text{ °C}$		2.35		
			$T_{vj} = 150\text{ °C}$		2.45		
Gate threshold voltage	V_{GETh}	$I_C = 6\text{ mA}$, $V_{CE} = V_{GE}$, $T_{vj} = 25\text{ °C}$		5.20	5.80	6.40	V
Gate charge	Q_G	$V_{GE} = \pm 15\text{ V}$, $V_{CC} = 900\text{ V}$, $T_{vj} = 25\text{ °C}$			1.55		μC
Internal gate resistor	R_{Gint}	$T_{vj} = 25\text{ °C}$			5		Ω
Input capacitance	C_{ies}	$f = 1000\text{ kHz}$, $T_{vj} = 25\text{ °C}$, $V_{CE} = 25\text{ V}$, $V_{GE} = 0\text{ V}$			12		nF
Reverse transfer capacitance	C_{res}	$f = 1000\text{ kHz}$, $T_{vj} = 25\text{ °C}$, $V_{CE} = 25\text{ V}$, $V_{GE} = 0\text{ V}$			0.39		nF
Collector-emitter cut-off current	I_{CES}	$V_{CE} = 1700\text{ V}$, $V_{GE} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$			3	mA
Gate-emitter leakage current	I_{GES}	$V_{CE} = 0\text{ V}$, $V_{GE} = 20\text{ V}$, $T_{vj} = 25\text{ °C}$				400	nA
Turn-on delay time (inductive load)	t_{don}	$I_C = 150\text{ A}$, $V_{CC} = 900\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $R_{Gon} = 0.51\text{ }\Omega$	$T_{vj} = 25\text{ °C}$		0.190		μs
			$T_{vj} = 125\text{ °C}$		0.210		
			$T_{vj} = 150\text{ °C}$		0.220		
Rise time (inductive load)	t_r	$I_C = 150\text{ A}$, $V_{CC} = 900\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $R_{Gon} = 0.51\text{ }\Omega$	$T_{vj} = 25\text{ °C}$		0.040		μs
			$T_{vj} = 125\text{ °C}$		0.050		
			$T_{vj} = 150\text{ °C}$		0.050		
Turn-off delay time (inductive load)	t_{doff}	$I_C = 150\text{ A}$, $V_{CC} = 900\text{ V}$, $V_{GE} = \pm 15\text{ V}$, $R_{Goff} = 0.51\text{ }\Omega$	$T_{vj} = 25\text{ °C}$		0.410		μs
			$T_{vj} = 125\text{ °C}$		0.570		
			$T_{vj} = 150\text{ °C}$		0.610		

(table continues...)

Table 4 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Fall time (inductive load)	t_f	$I_C = 150 \text{ A}$, $V_{CC} = 900 \text{ V}$, $V_{GE} = \pm 15 \text{ V}$, $R_{Goff} = 0.51 \Omega$	$T_{vj} = 25 \text{ °C}$	0.090		μs
			$T_{vj} = 125 \text{ °C}$	0.160		
			$T_{vj} = 150 \text{ °C}$	0.170		
Turn-on energy loss per pulse	E_{on}	$I_C = 150 \text{ A}$, $V_{CC} = 900 \text{ V}$, $L_\sigma = 35 \text{ nH}$, $V_{GE} = \pm 15 \text{ V}$, $R_{Gon} = 0.51 \Omega$, $di/dt = 2900 \text{ A}/\mu\text{s}$ ($T_{vj} = 150 \text{ °C}$)	$T_{vj} = 25 \text{ °C}$	39.5		mJ
			$T_{vj} = 125 \text{ °C}$	52.5		
			$T_{vj} = 150 \text{ °C}$	56.5		
Turn-off energy loss per pulse	E_{off}	$I_C = 150 \text{ A}$, $V_{CC} = 900 \text{ V}$, $L_\sigma = 35 \text{ nH}$, $V_{GE} = \pm 15 \text{ V}$, $R_{Goff} = 0.51 \Omega$, $dv/dt = 3000 \text{ V}/\mu\text{s}$ ($T_{vj} = 150 \text{ °C}$)	$T_{vj} = 25 \text{ °C}$	29		mJ
			$T_{vj} = 125 \text{ °C}$	45.5		
			$T_{vj} = 150 \text{ °C}$	53		
SC data	I_{SC}	$V_{GE} \leq 15 \text{ V}$, $V_{CC} = 1000 \text{ V}$, $V_{CEmax} = V_{CES} - L_{sCE} \cdot di/dt$	$t_p \leq 10 \mu\text{s}$, $T_{vj} = 150 \text{ °C}$	630		A
Thermal resistance, junction to case	R_{thJC}	per IGBT			0.158	K/W
Thermal resistance, case to heat sink	R_{thCH}	per IGBT, $\lambda_{grease} = 1 \text{ W}/(\text{m} \cdot \text{K})$		0.093		K/W
Temperature under switching conditions	$T_{vj op}$		-40		150	°C

3 Diode, Inverter

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Repetitive peak reverse voltage	V_{RRM}		$T_{vj} = 25 \text{ °C}$	1700	V
Continuous DC forward current	I_F			150	A
Repetitive peak forward current	I_{FRM}	$t_p = 1 \text{ ms}$		300	A
I^2t - value	I^2t	$t_p = 10 \text{ ms}$, $V_R = 0 \text{ V}$	$T_{vj} = 125 \text{ °C}$	4250	A^2s
			$T_{vj} = 150 \text{ °C}$	6150	

Table 6 **Characteristic values**


Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 150 \text{ A}$, $V_{GE} = 0 \text{ V}$	$T_{vj} = 25 \text{ °C}$		1.80	2.20	V
			$T_{vj} = 125 \text{ °C}$		1.90		
			$T_{vj} = 150 \text{ °C}$		1.95		
Peak reverse recovery current	I_{RM}	$V_{CC} = 900 \text{ V}$, $I_F = 150 \text{ A}$, $V_{GE} = -15 \text{ V}$, $-di_F/dt = 2900 \text{ A}/\mu\text{s}$ ($T_{vj} = 150 \text{ °C}$)	$T_{vj} = 25 \text{ °C}$		160		A
			$T_{vj} = 125 \text{ °C}$		170		
			$T_{vj} = 150 \text{ °C}$		175		
Recovered charge	Q_r	$V_{CC} = 900 \text{ V}$, $I_F = 150 \text{ A}$, $V_{GE} = -15 \text{ V}$, $-di_F/dt = 2900 \text{ A}/\mu\text{s}$ ($T_{vj} = 150 \text{ °C}$)	$T_{vj} = 25 \text{ °C}$		35.5		μC
			$T_{vj} = 125 \text{ °C}$		64.5		
			$T_{vj} = 150 \text{ °C}$		72		
Reverse recovery energy	E_{rec}	$V_{CC} = 900 \text{ V}$, $I_F = 150 \text{ A}$, $V_{GE} = -15 \text{ V}$, $-di_F/dt = 2900 \text{ A}/\mu\text{s}$ ($T_{vj} = 150 \text{ °C}$)	$T_{vj} = 25 \text{ °C}$		16.5		mJ
			$T_{vj} = 125 \text{ °C}$		35.5		
			$T_{vj} = 150 \text{ °C}$		40.5		
Thermal resistance, junction to case	R_{thJC}	per diode				0.332	K/W
Thermal resistance, case to heat sink	R_{thCH}	per diode, $\lambda_{grease} = 1 \text{ W}/(\text{m}\cdot\text{K})$			0.11		K/W
Temperature under switching conditions	$T_{vj op}$			-40		150	°C

4 Characteristics diagrams

Output characteristic (typical), IGBT, Inverter

$I_C = f(V_{CE})$


$V_{GE} = 15\text{ V}$



Output characteristic field (typical), IGBT, Inverter

$I_C = f(V_{CE})$


$T_{vj} = 150\text{ °C}$



Transfer characteristic (typical), IGBT, Inverter

$I_C = f(V_{GE})$


$V_{CE} = 20\text{ V}$



Switching losses (typical), IGBT, Inverter

$E = f(I_C)$


$R_{Goff} = 0.51\text{ }\Omega$, $R_{Gon} = 0.51\text{ }\Omega$, $V_{GE} = \pm 15\text{ V}$, $V_{CC} = 900\text{ V}$



4 Characteristics diagrams


Switching losses (typical), IGBT, Inverter

$E = f(R_G)$
 $V_{GE} = \pm 15\text{ V}$, $I_C = 150\text{ A}$, $V_{CC} = 900\text{ V}$




Reverse bias safe operating area (RBSOA), IGBT, Inverter

$I_C = f(V_{CE})$
 $R_{Goff} = 0.51\ \Omega$, $V_{GE} = \pm 15\text{ V}$, $T_{vj} = 150\text{ °C}$




Transient thermal impedance, IGBT, Inverter

$Z_{th} = f(t)$



Forward characteristic (typical), Diode, Inverter


$I_F = f(V_F)$



4 Characteristics diagrams


Switching losses (typical), Diode, Inverter

$E_{rec} = f(I_F)$
 $V_{CE} = 900\text{ V}, R_G = 0.51\ \Omega$




Switching losses (typical), Diode, Inverter

$E_{rec} = f(R_G)$
 $V_{CE} = 900\text{ V}, I_F = 150\text{ A}$



Transient thermal impedance, Diode, Inverter

$Z_{th} = f(t)$



5 Circuit diagram




Figure 1

6 Package outlines




Figure 2

7 Module label code

Module label code			
Code format	Data Matrix		Barcode Code128
Encoding	ASCII text		Code Set A
Symbol size	16x16		23 digits
Standard	IEC24720 and IEC16022		IEC8859-1
Code content	<i>Content</i>	<i>Digit</i>	<i>Example</i>
	Module serial number	1 – 5	71549
	Module material number	6 - 11	142846
	Production order number	12 - 19	55054991
	Date code (production year)	20 – 21	15
	Date code (production week)	22 – 23	30
Example			
			
71549142846550549911530		71549142846550549911530	

Figure 3

Revision history

Document revision	Date of release	Description of changes
V1.0	2012-10-17	Target datasheet
V1.1	2013-01-07	Target datasheet
V1.2	2014-08-07	Target datasheet
V1.3	2015-03-12	Target datasheet
V1.4	2015-12-02	Target datasheet
V3.0	2016-04-18	Final datasheet
V3.1	2017-09-07	Final datasheet
V3.2	2017-09-18	Final datasheet
n/a	2020-09-01	Datasheet migrated to a new system with a new layout and new revision number schema: target or preliminary datasheet = 0.xy; final datasheet = 1.xy
1.10	2024-03-12	Package outlines drawing updated
1.20	2025-07-31	Package outlines drawing updated

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2025-07-31

Published by

Infineon Technologies AG
81726 Munich, Germany

© 2025 Infineon Technologies AG
All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-AAX183-010

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.