

**IHM-B module with Trench/Fieldstop IGBT4 and emitter controlled 4 diode****Features**

- Electrical features
  - $V_{CES} = 3300\text{ V}$
  - $I_{C\text{ nom}} = 1600\text{ A} / I_{CRM} = 3200\text{ A}$
  - High DC stability
  - High short-circuit capability
  - Low switching losses
  - Low  $V_{CE,sat}$
  - $T_{vj,op} = 150^{\circ}\text{C}$
  - Trench IGBT 4
  - Unbeatable robustness
  - $V_{CE,sat}$  with positive temperature coefficient
  - High current density
  - Low  $Q_g$  and  $C_{res}$
- Mechanical features
  - ALSiC base plate for increased thermal cycling capability
  - High power density
  - Isolated base plate
  - Package with CTI > 600
  - RoHS compliant

**Potential applications**

- High-power converters
- Medium-voltage converters
- Motor drives
- Traction drives
- UPS systems
- Active frontend (energy recovery)
- Commercial agriculture vehicles

**Product validation**

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068


**Description**

Table of contents

	Description .....	1
	Features .....	1
	Potential applications .....	1
	Product validation .....	1
	Table of contents .....	2
1	Package .....	3
2	IGBT, Inverter .....	3
3	Diode, Inverter .....	5
4	Characteristics diagrams .....	7
5	Circuit diagram .....	11
6	Package outlines .....	11
7	Module label code .....	12
	Revision history .....	13
	Disclaimer .....	14

## 1 Package

**Table 1** Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	$V_{ISOL}$	RMS, $f = 50 \text{ Hz}$ , $t = 60 \text{ s}$	6.0	kV
Partial discharge extinction voltage	$V_{isol}$	RMS, $f = 50 \text{ Hz}$ , $Q_{PD} \leq 10 \text{ pC}$	2.6	kV
DC stability	$V_{CE(D)}$	$T_{vj}=25^{\circ}\text{C}$ , 100 Fit	2100	V
Material of module baseplate			AlSiC	
Creepage distance	$d_{Creep}$	terminal to heatsink	32.2	mm
Clearance	$d_{Clear}$	terminal to heatsink	19.1	mm
Comparative tracking index	$CTI$		>600	

**Table 2** Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Stray inductance module	$L_{sCE}$			9		nH
Module lead resistance, terminals - chip	$R_{AA'+CC'}$	$T_C=25^{\circ}\text{C}$ , per switch		0.12		mΩ
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	$T_C=25^{\circ}\text{C}$ , per switch		0.14		mΩ
Storage temperature	$T_{stg}$		-40		150	°C
Mounting torque for module mounting	$M$	- Mounting according to valid application note	M6, Screw	4.25	5.75	Nm
Terminal connection torque	$M$	- Mounting according to valid application note	M4, Screw	1.8	2.1	Nm
			M8, Screw	8	10	
Weight	$G$			800		g

## 2 IGBT, Inverter

**Table 3** Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Collector-emitter voltage	$V_{CES}$		$T_{vj} = -40^{\circ}\text{C}$	3300	V
			$T_{vj} = 150^{\circ}\text{C}$	3300	
Continuous DC collector current	$I_{CDC}$	$T_{vj \text{ max}} = 150^{\circ}\text{C}$	$T_C = 100^{\circ}\text{C}$	1600	A
Repetitive peak collector current	$I_{CRM}$	$t_p = 1 \text{ ms}$		3200	A
Gate-emitter peak voltage	$V_{GES}$			±20	V

**Table 4**                      **Characteristic values**

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CE\ sat}$	$I_C = 1600\ A, V_{GE} = 15\ V$	$T_{vj} = 25\ ^\circ C$		2.40	2.65	V
			$T_{vj} = 125\ ^\circ C$		2.95		
			$T_{vj} = 150\ ^\circ C$		3.10	3.25	
Gate threshold voltage	$V_{GEth}$	$I_C = 62\ mA, V_{CE} = V_{GE}, T_{vj} = 25\ ^\circ C$		5.20	5.80	6.40	V
Gate charge	$Q_G$	$V_{GE} = \pm 15\ V, V_{CE} = 1800\ V$			28		$\mu C$
Internal gate resistor	$R_{Gint}$	$T_{vj} = 25\ ^\circ C$			0.75		$\Omega$
Input capacitance	$C_{ies}$	$f = 1000\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$			187		nF
Reverse transfer capacitance	$C_{res}$	$f = 1000\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$			5.33		nF
Collector-emitter cut-off current	$I_{CES}$	$V_{CE} = 3300\ V, V_{GE} = 0\ V$	$T_{vj} = 25\ ^\circ C$			5	mA
Gate-emitter leakage current	$I_{GES}$	$V_{CE} = 0\ V, V_{GE} = 20\ V, T_{vj} = 25\ ^\circ C$				400	nA
Turn-on delay time (inductive load)	$t_{don}$	$I_C = 1600\ A, V_{CE} = 1800\ V, V_{GE} = \pm 15\ V, R_{Gon} = 0.8\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.600		$\mu s$
			$T_{vj} = 125\ ^\circ C$		0.710		
			$T_{vj} = 150\ ^\circ C$		0.760		
Rise time (inductive load)	$t_r$	$I_C = 1600\ A, V_{CE} = 1800\ V, V_{GE} = \pm 15\ V, R_{Gon} = 0.8\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.220		$\mu s$
			$T_{vj} = 125\ ^\circ C$		0.240		
			$T_{vj} = 150\ ^\circ C$		0.250		
Turn-off delay time (inductive load)	$t_{doff}$	$I_C = 1600\ A, V_{CE} = 1800\ V, V_{GE} = \pm 15\ V, R_{Goff} = 3.9\ \Omega$	$T_{vj} = 25\ ^\circ C$		3.420		$\mu s$
			$T_{vj} = 125\ ^\circ C$		3.670		
			$T_{vj} = 150\ ^\circ C$		3.740		
Fall time (inductive load)	$t_f$	$I_C = 1600\ A, V_{CE} = 1800\ V, V_{GE} = \pm 15\ V, R_{Goff} = 3.9\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.690		$\mu s$
			$T_{vj} = 125\ ^\circ C$		1.290		
			$T_{vj} = 150\ ^\circ C$		1.470		
Turn-on time (resistive load)	$t_{on\_R}$	$I_C = 500\ A, V_{CE} = 2000\ V, V_{GE} = \pm 15\ V, R_{Gon} = 0.8\ \Omega$	$T_{vj} = 25\ ^\circ C$	1.18			$\mu s$
Turn-on energy loss per pulse	$E_{on}$	$I_C = 1600\ A, V_{CE} = 1800\ V, L_\sigma = 85\ nH, V_{GE} = \pm 15\ V, R_{Gon} = 0.8\ \Omega, di/dt = 5300\ A/\mu s (T_{vj} = 150\ ^\circ C)$	$T_{vj} = 25\ ^\circ C$		1850		mJ
			$T_{vj} = 125\ ^\circ C$		2850		
			$T_{vj} = 150\ ^\circ C$		3200		
Turn-off energy loss per pulse	$E_{off}$	$I_C = 1600\ A, V_{CE} = 1800\ V, L_\sigma = 85\ nH, V_{GE} = \pm 15\ V, R_{Goff} = 3.9\ \Omega, dv/dt = 1700\ V/\mu s (T_{vj} = 150\ ^\circ C)$	$T_{vj} = 25\ ^\circ C$		2280		mJ
			$T_{vj} = 125\ ^\circ C$		2980		
			$T_{vj} = 150\ ^\circ C$		3140		
SC data	$I_{SC}$	$V_{GE} \leq 15\ V, V_{CC} = 2400\ V, V_{CEmax} = V_{CES} - L_{SCE} \cdot di/dt$	$t_P \leq 10\ \mu s, T_{vj} \leq 150\ ^\circ C$		6400		A

**(table continues...)**

**Table 4** (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Thermal resistance, junction to case	$R_{thJC}$	per IGBT			9.30	K/kW
Thermal resistance, case to heat sink	$R_{thCH}$	per IGBT, $\lambda_{grease} = 1 \text{ W/(m}^2\text{K)}$		5.60		K/kW
Temperature under switching conditions	$T_{vj\text{ op}}$		-40		150	°C

### 3 Diode, Inverter

**Table 5** Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Repetitive peak reverse voltage	$V_{RRM}$		$T_{vj} = -40 \text{ °C}$	3300	V
			$T_{vj} = 150 \text{ °C}$	3300	
Continuous DC forward current	$I_F$			1600	A
Repetitive peak forward current	$I_{FRM}$	$t_P = 1 \text{ ms}$		3200	A
$I^2t$ - value	$I^2t$	$t_P = 10 \text{ ms}, V_R = 0 \text{ V}$	$T_{vj} = 125 \text{ °C}$	630	kA <sup>2</sup> s
			$T_{vj} = 150 \text{ °C}$	570	
Maximum power dissipation	$P_{RQM}$	$T_{vj} = 150 \text{ °C}$		3600	kW
Minimum turn-on time	$t_{onmin}$			10	μs

**Table 6** Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	$V_F$	$I_F = 1600 \text{ A}, V_{GE} = 0 \text{ V}$	$T_{vj} = 25 \text{ °C}$		3.30	V
			$T_{vj} = 125 \text{ °C}$	2.60		
			$T_{vj} = 150 \text{ °C}$	2.50	2.80	
Peak reverse recovery current	$I_{RM}$	$V_R = 1800 \text{ V}, I_F = 1600 \text{ A}, V_{GE} = -15 \text{ V}, -di_F/dt = 5300 \text{ A/μs} (T_{vj} = 150 \text{ °C})$	$T_{vj} = 25 \text{ °C}$	1470		A
			$T_{vj} = 125 \text{ °C}$	1650		
			$T_{vj} = 150 \text{ °C}$	1700		
Recovered charge	$Q_r$	$V_R = 1800 \text{ V}, I_F = 1600 \text{ A}, V_{GE} = -15 \text{ V}, -di_F/dt = 5300 \text{ A/μs} (T_{vj} = 150 \text{ °C})$	$T_{vj} = 25 \text{ °C}$	685		μC
			$T_{vj} = 125 \text{ °C}$	1360		
			$T_{vj} = 150 \text{ °C}$	2000		

(table continues...)


**Table 6** (continued) Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Reverse recovery energy	$E_{rec}$	$V_R = 1800\text{ V}$ , $I_F = 1600\text{ A}$ , $V_{GE} = -15\text{ V}$ , $-di_F/dt =$ $5300\text{ A}/\mu\text{s}$ ( $T_{vj} = 150\text{ }^\circ\text{C}$ )	$T_{vj} = 25\text{ }^\circ\text{C}$		730		mJ
			$T_{vj} = 125\text{ }^\circ\text{C}$		1450		
			$T_{vj} = 150\text{ }^\circ\text{C}$		1750		
Thermal resistance, junction to case	$R_{thJC}$	per diode				17.5	K/kW
Thermal resistance, case to heat sink	$R_{thCH}$	per diode, $\lambda_{grease} = 1\text{ W}/(\text{m}^*\text{K})$			8.50		K/kW
Temperature under switching conditions	$T_{vj\text{ op}}$			-40		150	$^\circ\text{C}$

4 Characteristics diagrams


output characteristic (typical), IGBT, Inverter

$I_C = f(V_{CE})$   
 $V_{GE} = 15\text{ V}$




output characteristic (typical), IGBT, Inverter

$I_C = f(V_{CE})$   
 $T_{vj} = 150\text{ °C}$




transfer characteristic (typical), IGBT, Inverter

$I_C = f(V_{GE})$   
 $V_{CE} = 20\text{ V}$



switching losses (typical), IGBT, Inverter


$E = f(I_C)$   
 $R_{Goff} = 3.9\text{ }\Omega$ ,  $R_{Gon} = 0.8\text{ }\Omega$ ,  $V_{CE} = 1800\text{ V}$ ,  $V_{GE} = \pm 15\text{ V}$



4 Characteristics diagrams


switching losses (typical), IGBT, Inverter

$E = f(R_G)$   
 $I_C = 1600\text{ A}$ ,  $V_{CE} = 1800\text{ V}$ ,  $V_{GE} = \pm 15\text{ V}$




switching times (typical), IGBT, Inverter

$t = f(I_C)$   
 $R_{Goff} = 3.9\text{ }\Omega$ ,  $R_{Gon} = 0.8\text{ }\Omega$ ,  $V_{CE} = 1800\text{ V}$ ,  $V_{GE} = \pm 15\text{ V}$ ,  $T_{vj} = 125\text{ }^\circ\text{C}$




switching times (typical), IGBT, Inverter

$t = f(R_G)$   
 $I_C = 1600\text{ A}$ ,  $V_{CE} = 1800\text{ V}$ ,  $V_{GE} = \pm 15\text{ V}$ ,  $T_{vj} = 125\text{ }^\circ\text{C}$



transient thermal impedance , IGBT, Inverter


$Z_{th} = f(t)$



**reverse bias safe operating area (RBSOA), IGBT, Inverter**


$$I_C = f(V_{CE})$$

$$R_{Goff} = 3.9 \, \Omega, V_{GE} = \pm 15 \, V, T_{vj} = 150 \, ^\circ C$$

**capacity characteristic (typical), IGBT, Inverter**


$$C = f(V_{CE})$$

$$f = 100 \, kHz, V_{GE} = 0 \, V, T_{vj} = 25 \, ^\circ C$$


**gate charge characteristic (typical), IGBT, Inverter**

$$V_{GE} = f(Q_G)$$

$$I_C = 1600 \, A, T_{vj} = 25 \, ^\circ C$$

**forward characteristic of (typical), Diode, Inverter**


$$I_F = f(V_F)$$



4 Characteristics diagrams


switching losses (typical), Diode, Inverter

$E_{rec} = f(I_F)$   
 $V_{CE} = 1800\text{ V}, R_{Gon} = R_{Gon}(IGBT)$




switching losses (typical), Diode, Inverter

$E_{rec} = f(R_G)$   
 $V_{CE} = 1800\text{ V}, I_F = 1600\text{ A}$




transient thermal impedance , Diode, Inverter

$Z_{th} = f(t)$




safe operation area (SOA), Diode, Inverter

$I_R = f(V_R)$   
 $T_{vj} = 150\text{ °C}$



### Figure 1



### Figure 2

7 Module label code



Module label code			
Code format	Data Matrix		Barcode Code128
Encoding	ASCII text		Code Set A
Symbol size	16x16		23 digits
Standard	IEC24720 and IEC16022		IEC8859-1
Code content	<i>Content</i>	<i>Digit</i>	<i>Example</i>
	Module serial number	1 – 5	71549
	Module material number	6 - 11	142846
	Production order number	12 - 19	55054991
	Date code (production year)	20 – 21	15
	Date code (production week)	22 – 23	30
Example	<div> 71549142846550549911530</div> <div> 71549142846550549911530</div>		

Figure 3

## Revision history

Document revision	Date of release	Description of changes
1.00	2021-03-02	
1.10	2021-04-13	Final
1.20	2021-10-28	Final datasheet

## Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

**Edition 2021-10-28**

**Published by**

**Infineon Technologies AG**  
**81726 Munich, Germany**

**© 2021 Infineon Technologies AG**  
**All Rights Reserved.**

**Do you have a question about any aspect of this document?**

**Email: [erratum@infineon.com](mailto:erratum@infineon.com)**

**Document reference**  
**IFX-AAO543-003**

## IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

## WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.