GTM_TOM_Interrupt_1 for KIT_AURIX_TC397_TFT GTM TOM interrupt

AURIX™ TC3xx Microcontroller Training V1.0.1





Scope of work

The GTM TOM is configured to trigger an interrupt every 500 ms. The interrupt toggles an LED.

The Generic Timer Module triggers an interrupt every 500 ms. The state of the port pin, where the LED is connected, is toggled inside the Interrupt Service Routine (ISR).



Introduction


- The Generic Timer Module (GTM) is a modular timer unit designed to accommodate many timer applications
- It has an in-built Timer Output Module (TOM) that offers up to 16 independent channels to generate output signals
- The Clock Management Unit (CMU) is responsible for clock generation of the GTM. The Fixed Clock Generation (FXU) is one of its subunits and it provides five predefined non-configurable clocks for GTM modules, including the TOM



Hardware setup

This code example has been developed for the board KIT_A2G_TC397_5V_TFT.

LED D107 (1) is used for this example.



infineon

Implementation

Configuring the TOM

The configuration of the TOM is done once in the setup phase by calling the initialization function *initGtmTom()* with the following steps:

- Enable the GTM by calling the function IfxGtm_enable()
- The function IfxGtm_Tom_Timer_initConfig() initializes an instance of the structure IfxGtm_Tom_Timer_Config with its default values
- The IfxGtm_Tom_Timer_Config structure allows to set the following parameters to initialize the module:
 - tom Set TOM 1
 - timerChannel Set channel 0 of TOM 1
 - clock Select CMU clock 3
 - base.frequency Set timer frequency to 2 Hz (Interrupt every 500 ms)
 - base.isrPriority Interrupt Service Routine priority
 - base.isrProvider Interrupt Service Routine provider



Implementation

Configuring the TOM

- Select the FXU clock 3 to divide the clock source by 4096 (*timerConfig.clock* = *IfxGtm_Tom_Ch_ClkSrc_cmuFxclk3*)
- Enable the FXU clocks by calling the function IfxGtm_Cmu_enableClocks()
- The function IfxGtm_Tom_Timer_init() initializes and activates the TOM with the given configuration

All the functions used for the configuration of the TOM are provided by the iLLD header *IfxGtm Tom Timer.h*.



Implementation

Configuring the LED

The LED configuration is done once in the function *initGtmTom()* by setting the port pin mode to output and push-pull by calling the function *IfxPort_setPinModeOutput()*, provided by iLLD header *IfxPort.h*.

Interrupt Service Routine (ISR)

The ISR implemented in this example contains the following steps:


- Clear the timer event with the function IfxGtm_Tom_Timer_acknowledgeTimerIrq() (iLLD header IfxGtm_Tom_Timer.h)
- Change the LED state by calling the function IfxPort_togglePin() (iLLD header IfxPort.h)



Run and Test

After code compilation and flashing the device, observe the LED D107 (1),

which should be blinking.



References





- > AURIX™ Development Studio is available online:
- https://www.infineon.com/aurixdevelopmentstudio
- Use the "Import…" function to get access to more code examples.



- More code examples can be found on the GIT repository:
- https://github.com/Infineon/AURIX code examples



- For additional trainings, visit our webpage:
- https://www.infineon.com/aurix-expert-training



- For questions and support, use the AURIX™ Forum:
- https://www.infineonforums.com/forums/13-Aurix-Forum



Revision history

| Revision | Description of change |
|----------|--|
| V1.0.1 | Fixed number of CMU clock used in implementation slide |
| V1.0.0 | Initial version |
| | |
| | |
| | |

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.



Edition 2021-06 Published by Infineon Technologies AG 81726 Munich, Germany

© 2021 Infineon Technologies AG. All Rights Reserved.

Do you have a question about this document?
Email: erratum@infineon.com

Document reference GTM_TOM_Interrupt_1_KIT_TC397_TFT

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.