Automotive MOSFET

OptiMOS™-5 Power-Transistor

RoHS

Infineon Automotive Quality

AEC Qualified

PG-HSOF-5-4





Features

- OptiMOS™ power MOSFET for automotive applications
- N-channel – Enhancement mode – Normal Level
- Extended qualification beyond AEC-Q101
- Enhanced electrical testing
- Robust design
- MSL3 up to 260°C peak reflow
- 175°C operating temperature
- Green product (RoHS compliant)
- 100% Avalanche tested

Potential applications

General automotive applications.

Product Summary

V_{DS}	80	V
$R_{DS(on)}$	1.8	mΩ
I_D (Chip limited)	250	A

Type	Package	Marking
IAUA250N08S5N018	PG-HSOF-5-4	5N08018

Table of Contents

Maximum ratings

at Tj=25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Value	Unit
Continuous drain current	I_D	V_{GS}=10 V, Chip limitation[1)]	250	A
		V_{GS}=10V, DC current	250	
		T_a=85 °C, V_{GS}=10 V, R_{thJA} on 2s2p[2,3)]	35	
Pulsed drain current[2)]	$I_{D,pulse}$	T_C=25 °C, t_p= 100 µs	813	
Avalanche energy, single pulse[2)]	E_{AS}	I_D=125 A	340	mJ
Avalanche current, single pulse	I_{AS}	-	250	A
Gate source voltage	V_{GS}	-	±20	V
Power dissipation	P_{tot}	T_C=25 °C	238	W
Operating and storage temperature	T_j, T_{stg}	-	-55 ... +175	°C
IEC climatic category; DIN IEC 68-1	-	-	55/175/56	

Thermal characteristics[2)]

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Thermal resistance, junction - case	R_{thJC}	–	-	-	0.63	K/W
Thermal resistance, junction - ambient[3)]	R_{thJA}	–	-	22.6	-	

Electrical characteristics

at Tj=25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Static characteristics						
Drain-source breakdown voltage	$V_{(BR)DSS}$	V_{GS}=0 V, I_D=1 mA	80	-	-	V
Gate threshold voltage	$V_{GS(th)}$	V_{DS}=V_{GS}, I_D=150 µA	2.2	3	3.8	
Zero gate voltage drain current	I_{DSS}	V_{DS}=80 V, V_{GS}=0 V, T_j=25 °C	-	0.1	1	µA
		V_{DS}=80 V, V_{GS}=0 V, T_j=100 °C[2)]	-	1	100	
Gate-source leakage current	I_{GSS}	V_{GS}=20 V, V_{DS}=0 V	-	-	100	nA
Drain-source on-state resistance	$R_{DS(on)}$	V_{GS}=6 V, I_D=60 A	-	2.1	2.5	mΩ
		V_{GS}=10 V, I_D=100 A	-	1.5	1.8	
Gate resistance[2)]	R_G	-	-	1.4	-	Ω

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Dynamic characteristics[2]						
Input capacitance	C_{iss}	V_{GS}=0 V, V_{DS}=40 V, f=1 MHz	-	6704	8715	pF
Output capacitance	C_{oss}		-	1156	1502	
Reverse transfer capacitance	C_{rss}		-	47	70	
Turn-on delay time	$t_{d(on)}$	V_{DD}=40 V, V_{GS}=10 V, I_D=100 A, R_G=3.5 Ω	-	16	-	ns
Rise time	t_r		-	11	-	
Turn-off delay time	$t_{d(off)}$		-	32	-	
Fall time	t_f		-	23	-	
Gate Charge Characteristics[2]						
Gate to source charge	Q_{gs}	V_{DD}=40 V, I_D=100 A, V_{GS}=0 to 10 V	-	32	41	nC
Gate to drain charge	Q_{gd}		-	21	32	
Gate charge total	Q_g		-	96	125	
Gate plateau voltage	$V_{plateau}$		-	4.7	-	V
Reverse Diode						
Diode continous forward current[2]	I_S	T_C=25 °C	-	-	256	A
Diode pulse current[2]	$I_{S,pulse}$	T_C=25 °C, t_p= 100 µs	-	-	813	
Diode forward voltage	V_{SD}	V_{GS}=0 V, I_F=100 A, T_j=25 °C	-	0.9	1.2	V
Reverse recovery time[2]	t_{rr}	V_R=40 V, I_F=50A, di_F/dt=100 A/µs	-	60	-	ns
Reverse recovery charge[2]	Q_{rr}		-	84	-	nC

[1] Practically the current is limited by the overall system design including the customer-specific PCB.

[2] The parameter is not subject to production testing – specified by design.

[3] Device on 2s2p FR4 PCB defined in accordance with JEDEC standards (JESD51-5, -7). PCB is vertical in still air.

Electrical characteristics diagrams

1 Power dissipation

$P_{tot} = f(T_C)$; $V_{GS} \geq 6$ V



2 Drain current

$I_D = f(T_C)$; $V_{GS} \geq 6$ V



3 Safe operating area

$I_D = f(V_{DS})$; $T_C = 25$ °C; $D = 0$; parameter: t_p



4 Max. transient thermal impedance

$Z_{thJC} = f(t_p)$; parameter: $D = t_p/T$



5 Typ. output characteristics

$I_D = f(V_{DS})$; $T_j = 25$ °C; parameter: V_{GS}



6 Typ. drain-source on-state resistance

$R_{DS(on)} = f(I_D)$; $T_j = 25$ °C; parameter: V_{GS}



7 Typ. transfer characteristics

$I_D = f(V_{GS})$; $V_{DS} = 6$V: parameter: T_j



8 Typ. drain-source on-state resistance

$R_{DS(on)} = f(T_j)$; parameter: I_D, V_{GS}



9 Typ. gate threshold voltage

$V_{GS(th)} = f(T_j)$; $V_{GS} = V_{DS}$; parameter: I_D



10 Typ. capacitances

$C = f(V_{DS})$; $V_{GS} = 0$ V; $f = 1$ MHz



11 Typical forward diode characteristics

$I_F = f(V_{SD})$; parameter: T_j



12 Typ. avalanche characteristics

$I_{AS} = f(t_{AV})$; parameter: $T_{j(start)}$



13 Typical avalanche energy

$E_{AS} = f(T_j)$; parameter: ID



14 Drain-source breakdown voltage

$V_{BR(DSS)} = f(T_j)$; $I_{D\_typ} = 1$ mA



15 Typ. gate charge

$V_{GS} = f(Q_{gate})$; $I_D = 100$ A pulsed; parameter: V_{DD}



16 Gate charge waveforms



Package Outline



1) Lead length up to anti flash profile; mold flashes excluded
2) Excluding burr
All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1

Footprint



All dimensions are in units mm

Packaging



All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1

Revision History

Revision	Date	Changes
Revision 1.0	17.03.2021	Final Datasheet

Trademarks
All referenced product or service names and trademarks are the property of their respective owners.

Edition 2021-03-17

Published by

Infineon Technologies AG

81726 Munich, Germany

Do you have any questions about any aspect of this document?

Email: erratum@infineon.com