

High reliability microwave & RF components for space

Selection guide





High reliability RF components for space

As a key supplier of discrete semiconductor devices for the high-reliability community, Infineon Technologies has built an excellent reputation in space community for over 40 years. From silicon to backend and screening, Infineon's RF capabilities include space-qualified silicon microwave transistors and foundry services.

Unlike the high-volume markets where low-cost plastic packages are used, the semi-conductor dies for Infineon's space components are assembled in hermetically sealed packages to create HiRel standard products for professional applications. It should be stressed, however, that these HiRel components take full advantage of the stabilized mass production of wafers for the consumer and commercial markets.

All HiRel devices, are also available as qualified chip (bare die) from specially released wafers. Infineon HiRel components are supplied in different quality levels:

- "P" for prototype level used in Engineering Modules (EM)
- "ES" for ESA space level for Flight Modules (FM)

Key features

- Transition frequency from 8 GHz up to 42 GHz
- Output power from 20 mA to 100 mA
- Ideal for high frequency applications like LNA or oscillator circuits
- TID and SEE radiation hardened

HiRel silicon diodes

Product type	Package	V _{BR} (min) [V]	I _F (max) [mA]	RF (typ) [mΩ]	τ(typ) [ns]	CT (typ) [pF]	ESA QPL number
BAS40-05 (ql)	T1	40	120	10.0	-	3.10	5512 020 05
BAS70-04 (ql)	T1	70	70	20.0	-	1.50	5512 020 04
BXY42-03 (ql)	T1	50	5000	1.2	50	0.26	5513 017 03
BXY43-09 (ql)	T1	150	400	1.2	950	0.30	5513 030 09
BXY44-10 (ql)	T1	200	400	2.2	1100	0.20	5513 030 10
chip D0337E (ql)	die (BAS40-05)	-	-	-	-	-	N.A.
chip D0336E (ql)	die (BAS70-04)	-	-	-	-	-	N.A.
chip D0310G (ql)	die (BXY42-03)	-	-	-	-	_	N.A.
chip D0309G (ql)	die (BXY43-09)	_	-	-	-	_	N.A.
chip D0360C (ql)	die (BXY44-10)	_	-	_	_	-	N.A.

HiRel silicon bipolar transistors

Product type	Package	V _{CEO} (min) [V]	I _c (max) [mA]	P _{tot} (max) [mW]	f _T [GHz]	NF (typ) [dB]	ESA QPL number
BFY181 (ql)	Micro-X1	12.0	20	175	8.0	2.5 @ 2.0 GHz	5611 006 03
BFY182 (ql)	Micro-X1	12.0	35	250	8.0	2.5 @ 2.0 GHz	5611 006 04
BFY183 (ql)	Micro-X1	12.0	65	450	8.0	2.5 @ 2.0 GHz	5611 006 05
BFY193F (ql)	Micro-X1	12.0	80	580	8.0	1.75 @ 2.0 GHz	5611 006 09
BFY196 (ql)	Micro-X1	12.0	100	700	6.5	3.2 @ 2.0 GHz	5611 006 07
BFY405 (ql)	Micro-X1	4.5	12	55	22.0	1.2 @ 1.8 Ghz	5611 008 01
BFY420 (ql)	Micro-X1	4.5	35	160	22.0	1.2 @ 1.8 Ghz	5611 008 02
BFY450 (ql)	Micro-X1	4.5	100	450	22.0	1.4 @ 1.8 Ghz	5611 008 03
BFY650B-12 (ql)	Micro-X1	4.0	150	600	40.0	0.7 @ 1.8 Ghz	5611 010 05
BFY740B-02 (ql)	Micro-X1	4.0	30	120	45.0	1.05 @ 6.0 Ghz	5611 011 02
chip T0349B (ql)	die (BFY181)	-	-	-	-	_	N.A.
chip T0341 (ql)	die (BFY182)	-	-	-	-	_	N.A.
chip T0351 (ql)	die (BFY183)	-	-	-	-	_	N.A.
chip T0359E (ql)	die (BFY193F)	-	-	-	-	_	N.A.
chip T0395 (ql)	die (BFY196)	-	-	-	-	_	N.A.
chip T0501 (ql)	die (BFY405)	-	-	-	-	_	N.A.
chip T0502 (ql)	die (BFY420)	-	-	-	_	-	N.A.
chip T0503 (ql)	die (BFY450)	-	-	-	-	_	N.A.
chip T1581C (ql)	die (BFY650B-12)	-	-	-	_	-	N.A.
chip T1592D (ql)	die (BFY740B-02)	-	-	-	-	-	N.A.

RF silicon foundry services

Infineon is a market leader in radar technology, especially leading in automotive applications and offers its high volume production radar technology with stable process for foundry business. With a low power consumption, a superior low noise performance, a high integration layout due to 130 nm SiGe BiCMOS technology and a high RF amplification output, the Infineon B11HFC technology sets a benchmark.

Infineon's RF foundry service enables the customer to use this superior, mature radar technology for customized designs, developing markets or low-volume applications. Services include wafer and mask set production of the customer designed IC. Infineon can also recommend experienced partners for design and test of B11HFC silicon.

Typical applications include phased array antennas, (RF-) test equipment, satellite ground equipment or any other RF based application. For further information, please contact the RF foundry team: rf-foundry@infineon.com

Key features

- Frequency up to $f_T = 250 \text{ GHz}$ and $f_{\text{max}} = 390 \text{ GHz}$
- 130 nm SiGe BiCMOS

RF foundry services includes

- Engineering mask set production
- Engineering wafer run



1) Cooperation with design and test house partner possible

Other services

Infineon also offers the possibility to order Infineon standard components (COTS) with full traceability of wafer lot and production lot. This service is available for packaged components as well as bare die. For further information, please contact the RF foundry team: rf-foundry@infineon.com

Services include

- COTS parts with traceability
- COTS chips in small quantity

Where to buy

Infine on distribution partners and sales offices: www.infineon.com/WhereToBuy

Service hotline

Infineon offers its toll-free 0800/4001 service hotline as one central number, available 24/7 in English, Mandarin and German.

- > Germany 0800 951 951 951 (German/English)
- > China, mainland 4001 200 951 (Mandarin/English)
- > India 000 800 4402 951 (English)
- > USA 1-866 951 9519 (English/German)
- > Other countries 00* 800 951 951 951 (English/German)
- > Direct access+49 89 234-0 (interconnection fee, German/English)

Published by Infineon Technologies AG Am Campeon 1-15, 85579 Neubiberg Germany

© 2023 Infineon Technologies AG. All rights reserved.

Public

Document number: B155-I1204-V2-7600-EU-EC-P Date: 10/2023

Please note!

This Document is for information purposes only and any information given herein shall in no event be regarded as a warranty, guarantee or description of any functionality, conditions and/or quality of our products or any suitability for a particular purpose. With regard to the technical specifications of our products, we kindly ask you to refer to the relevant product data sheets provided by us. Our customers and their technical departments are required to evaluate the suitability of our products for the intended application.

We reserve the right to change this document and/ or the information given herein at any time.

Additional information

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office (www.infineon.com).

Warnings

Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Infineon Technologies Components may only be used in life-support devices or systems with the expressed written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety of effectiveness of that device or system.

Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.



Scan QR code and explore offering www.infineon.com/hirelrf

^{*} Please note: Some countries may require you to dial a code other than "00" to access this international number. Please visit www.infineon.com/service for your country!