


**OptiMOS™ -5 Power-Transistor**

**Features**

- OptiMOS™ - power MOSFET for automotive applications
- N-channel - Enhancement mode - Normal Level
- AEC Q101 qualified
- MSL3 up to 260°C peak reflow
- 175°C operating temperature
- Green Product (RoHS compliant)
- 100% Avalanche tested

**Product Summary**

$V_{DS}$	40	V
$R_{DS(on),max}$	1	mΩ
$I_D$	200	A

**PG-HSOF-5**


Type	Package	Marking
IAUA200N04S5N010	PG-HSOF-5	5N04N010

**Maximum ratings, at  $T_j=25\text{ °C}$ , unless otherwise specified**

Parameter	Symbol	Conditions	Value	Unit
Continuous drain current	$I_D$	$T_C=25\text{ °C}, V_{GS}=10\text{V}^{1)}$	200	A
		$T_C=100\text{ °C}, V_{GS}=10\text{V}^{2)}$	200	
Pulsed drain current <sup>2)</sup>	$I_{D,pulse}$	$T_C=25\text{ °C}$	800	
Avalanche energy, single pulse <sup>2)</sup>	$E_{AS}$	$I_D=100\text{A}$	280	mJ
Avalanche current, single pulse	$I_{AS}$	-	200	A
Gate source voltage	$V_{GS}$	-	±20	V
Power dissipation	$P_{tot}$	$T_C=25\text{ °C}$	167	W
Operating and storage temperature	$T_j, T_{stg}$	-	-55 ... +175	°C

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
<b>Thermal characteristics<sup>2)</sup></b>						
Thermal resistance, junction - case	$R_{thJC}$	-	-	-	0.9	K/W
Thermal resistance, junction - ambient	$R_{thJA}$	6 cm <sup>2</sup> cooling area <sup>3)</sup>	-	-	60	

**Electrical characteristics**, at  $T_j=25\text{ }^\circ\text{C}$ , unless otherwise specified

**Static characteristics**

Drain-source breakdown voltage	$V_{(BR)DSS}$	$V_{GS}=0V, I_D=1mA$	40	-	-	V
Gate threshold voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=100\mu A$	2.2	2.8	3.4	
Zero gate voltage drain current	$I_{DSS}$	$V_{DS}=40V, V_{GS}=0V, T_j=25^\circ C$	-	-	1	$\mu A$
		$V_{DS}=40V, V_{GS}=0V, T_j=125^\circ C^{2)}$	-	-	100	
Gate-source leakage current	$I_{GSS}$	$V_{GS}=20V, V_{DS}=0V$	-	-	100	nA
Drain-source on-state resistance	$R_{DS(on)}$	$V_{GS}=7V, I_D=100A$	-	0.9	1.2	m $\Omega$
		$V_{GS}=10V, I_D=100A$	-	0.8	1.0	

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	

**Dynamic characteristics<sup>2)</sup>**

Input capacitance	$C_{iss}$	$V_{GS}=0V, V_{DS}=25V,$ $f=1MHz$	-	5750	7650	pF
Output capacitance	$C_{oss}$		-	1600	2130	
Reverse transfer capacitance	$C_{rss}$		-	80	120	
Turn-on delay time	$t_{d(on)}$	$V_{DD}=20V, V_{GS}=10V,$ $I_D=200A, R_G=3.5\Omega$	-	11	-	ns
Rise time	$t_r$		-	6	-	
Turn-off delay time	$t_{d(off)}$		-	23	-	
Fall time	$t_f$		-	12	-	

**Gate Charge Characteristics<sup>2)</sup>**

Gate to source charge	$Q_{gs}$	$V_{DD}=32V, I_D=200A,$ $V_{GS}=0$ to 10V	-	28	37	nC
Gate to drain charge	$Q_{gd}$		-	21	32	
Gate charge total	$Q_g$		-	99	132	
Gate plateau voltage	$V_{plateau}$		-	4.7	-	V

**Reverse Diode**

Diode continuous forward current <sup>2)</sup>	$I_S$	$T_C=25^\circ C$	-	-	200	A
Diode pulse current <sup>2)</sup>	$I_{S,pulse}$		-	-	800	
Diode forward voltage	$V_{SD}$	$V_{GS}=0V, I_F=100A,$ $T_j=25^\circ C$	-	0.8	1.1	V
Reverse recovery time <sup>2)</sup>	$t_{rr}$	$V_R=20V, I_F=50A,$ $di_F/dt=100A/\mu s$	-	65	-	ns
Reverse recovery charge <sup>2)</sup>	$Q_{rr}$		-	80	-	


<sup>1)</sup> Current is limited by package; with an  $R_{thJC} = 0.9K/W$  the chip is able to carry 300A at 25°C.

<sup>2)</sup> The parameter is not subject to production test- verified by design/characterization.

<sup>3)</sup> Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm<sup>2</sup> (one layer, 70 μm thick) copper area for drain connection. PCB is vertical in still air.


**1 Power dissipation**

$P_{tot} = f(T_C); V_{GS} = 10\text{ V}$



**2 Drain current**


$I_D = f(T_C); V_{GS} = 10\text{ V}$



**3 Safe operating area**

$I_D = f(V_{DS}); T_C = 25\text{ °C}; D = 0$


parameter:  $t_p$



**4 Max. transient thermal impedance**

$Z_{thJC} = f(t_p)$


parameter:  $D = t_p/T$



**5 Typ. output characteristics**

$I_D = f(V_{DS}); T_j = 25\text{ }^\circ\text{C}$


parameter:  $V_{GS}$



**6 Typ. drain-source on-state resistance**

$R_{DS(on)} = f(I_D); T_j = 25\text{ }^\circ\text{C}$


parameter:  $V_{GS}$



**7 Typ. transfer characteristics**


$I_D = f(V_{GS}); V_{DS} = 6\text{ V}$

parameter:  $T_j$



**8 Typ. drain-source on-state resistance**


$R_{DS(on)} = f(T_j); I_D = 100\text{ A}; V_{GS} = 10\text{ V}$



**9 Typ. gate threshold voltage**


$V_{GS(th)} = f(T_j); V_{GS} = V_{DS}$

parameter:  $I_D$



**10 Typ. capacitances**


$C = f(V_{DS}); V_{GS} = 0 V; f = 1 MHz$



**11 Typical forward diode characteristics**

$I_F = f(V_{SD})$


parameter:  $T_j$



**12 Avalanche characteristics**


$I_{AS} = f(t_{AV})$

parameter:  $T_{j(start)}$




**13 Avalanche energy**

$$E_{AS} = f(T_j)$$



**14 Drain-source breakdown voltage**


$$V_{BR(DSS)} = f(T_j); I_D = 1 \text{ mA}$$




**15 Typ. gate charge**

$$V_{GS} = f(Q_{gate}); I_D = 200 \text{ A pulsed}$$

parameter:  $V_{DD}$



**16 Gate charge waveforms**



**Published by**  
**Infineon Technologies AG**  
**81726 Munich, Germany**

**© Infineon Technologies AG 2017**  
**All Rights Reserved.**

#### **Legal Disclaimer**

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

#### **Information**

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office ([www.infineon.com](http://www.infineon.com)).

#### **Warnings**

Due to technical requirements, components may contain dangerous substances.  
For information on the types in question, please contact the nearest Infineon Technologies Office.  
Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life.  
If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.



## Revision History

Version	Date	Changes
Revision 1.0	07.12.2017	Final Data Sheet
Revision 1.1	10.07.2018	package name, SOA 10µs curve