Automotive MOSFET

OptiMOS™ 6 Power-Transistor

RoHS Infineon Automotive Quality AEC Qualified

PG-LHDSO-10-2



Features

- OptiMOS™ power MOSFET for automotive applications
- N-channel – Enhancement mode – Normal Level
- Extended qualification beyond AEC-Q101
- Enhanced electrical testing
- Robust design
- MSL1 up to 260°C peak reflow
- 175°C operating temperature
- RoHS compliant
- 100% Avalanche tested
- Top Side Cooling



Pins 10 - 6 & Tab on Drain

Potential applications

General automotive applications.

Product validation

Qualified for automotive applications. Product validation according to AEC-Q101.

Product Summary

V_{DS}	40	V
$R_{DS(on)}$	0.89	mΩ
I_D (chip limited)	330	A

Type	Package	Marking
IAUCN04S6N009T	PG-LHDSO-10-2	6B4

Table of Contents

Maximum ratings

at Tj=25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Value	Unit
Continuous drain current	I_D	V_{GS}=10 V, Chip limitation[1,2)]	330	A
		V_{GS}=10V, DC current	120	
		T_a=85 °C, V_{GS}=10 V, R_{thJA} on 2s2p[2,4)]	70	
Pulsed drain current[2)]	$I_{D,pulse}$	T_C=25 °C, t_p= 100 µs	1000	
Avalanche energy, single pulse[2)]	E_{AS}	I_D=60 A	380	mJ
Avalanche current, single pulse	I_{AS}	–	95	A
Gate source voltage	V_{GS}	–	±20	V
Power dissipation	P_{tot}	T_C=25 °C	178	W
Operating and storage temperature	T_j, T_{stg}	–	-55 ... +175	°C

Thermal characteristics[2)]

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Thermal resistance, junction - case	R_{thJC}	–	–	0.42	0.84	K/W
Thermal characterization parameter, source pin[5)]	Ψ_{source}		–	5.3	–	
Thermal characterization parameter, drain pin[6)]	Ψ_{drain}		–	5.3	–	
Thermal resistance, junction - heatsink[4)]	R_{thJH}		–	6.9	–	
Thermal resistance, junction - ambient[3)]	R_{thJA}	–	–	49	–	

Electrical characteristics

at T_j=25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Static characteristics						
Drain-source breakdown voltage	$V_{(Br)DSS}$	V_{GS}=0 V, I_D=1 mA	40	–	–	V
Gate threshold voltage	$V_{GS(th)}$	V_{DS}=V_{GS}, I_D=90 µA	2.2	2.6	3.0	
Zero gate voltage drain current	I_{DSS}	V_{DS}=40 V, V_{GS}=0 V, T_j=25 °C	–	–	1	µA
		V_{DS}=40 V, V_{GS}=0 V, T_j=125 °C[2)]	–	–	25	
Gate-source leakage current	I_{GSS}	V_{GS}=20 V, V_{DS}=0 V	–	–	100	nA
Drain-source on-state resistance	$R_{DS(on)}$	V_{GS}=7 V, I_D=60 A	–	0.95	1.1	mΩ
		V_{GS}=10 V, I_D=60 A	–	0.79	0.89	
Gate resistance[2)]	R_G	–	–	0.9	–	Ω

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Dynamic characteristics[2]						
Input capacitance	C_{iss}	V_{GS}=0 V, V_{DS}=25 V, f=1 MHz	–	5650	7345	pF
Output capacitance	C_{oss}		–	1700	2210	
Reverse transfer capacitance	C_{rss}		–	80	120	
Turn-on delay time	$t_{d(on)}$	V_{DD}=20 V, V_{GS}=10 V, I_D=120 A, R_G=3.5 Ω	–	10	–	ns
Rise time	t_r		–	6	–	
Turn-off delay time	$t_{d(off)}$		–	25	–	
Fall time	t_f		–	12	–	
Gate Charge Characteristics[2]						
Gate to source charge	Q_{gs}	V_{DD}=32 V, I_D=120 A, V_{GS}=0 to 10 V	–	23	30	nC
Gate to drain charge	Q_{gd}		–	17	26	
Gate charge total	Q_g		–	80	104	
Gate plateau voltage	$V_{plateau}$		–	4.1	–	V
Reverse Diode						
Diode continous forward current[2]	I_S	T_C=25 °C	–	–	120	A
Diode pulse current[2]	$I_{S,pulse}$	T_C=25 °C, t_p= 100 µs	–	–	1000	
Diode forward voltage	V_{SD}	V_{GS}=0 V, I_F=60 A, T_j=25 °C	–	0.8	1.1	V
Reverse recovery time[2]	t_{rr}	V_R=20 V, I_F=50 A, di_F/dt =100 A/µs	–	41	–	ns
Reverse recovery charge[2]	Q_{rr}		–	38	–	nC

[1] Practically the current is limited by the overall system design including the customer-specific PCB.

[2] The parameter is not subject to production testing – specified by design.

[3] Device on 2s2p FR4 PCB defined in accordance with JEDEC standards (JESD51-5, -7). PCB is vertical in still air.

[4] Device on 2s2p FR4 PCB defined in accordance with JEDEC standards (JESD51-5, -7) without thermal vias, heatsink of 71x110x2 mm is attached through 3 W/(m*K) 400µm to top side pad. Heatsink fixed to 85°C ambient temperature.

[5] Thermal characterization parameter, calculated as $\psi_{source} = (T_{source} - T_{ambient})/P_{dis}$ in condition of 4). Used to determine PCB temperature at source pins for given power.

[6] Thermal characterization parameter, calculated as $\psi_{drain} = (T_{drain} - T_{ambient})/P_{dis}$ in condition of 4). Used to determine PCB temperature at drain pins for given power.

Electrical characteristics diagrams

1 Power dissipation

$P_{tot} = f(T_C)$; $V_{GS} \geq 6$ V



2 Drain current

$I_D = f(T_C)$; $V_{GS} \geq 6$ V



3 Safe operating area

$I_D = f(V_{DS})$; $T_C = 25$ °C; $D = 0$; parameter: t_p



4 Max. transient thermal impedance

$Z_{thJC} = f(t_p)$; parameter: $D=t_p/T$



5 Typ. output characteristics

$I_D = f(V_{DS})$; $T_j = 25$ °C; parameter: V_{GS}



6 Typ. drain-source on-state resistance

$R_{DS(on)} = f(I_D)$; $T_j = 25$ °C; parameter: V_{GS}



7 Typ. transfer characteristics

$I_D = f(V_{GS})$; $V_{DS} = 6$ V: parameter: T_j



8 Typ. drain-source on-state resistance

$R_{DS(on)} = f(T_j)$; parameter: I_D, V_{GS}



9 Typ. gate threshold voltage



10 Typ. capacitances



11 Typical forward diode characteristics



12 Typ. avalanche characteristics



13 Typical avalanche energy

$E_{AS} = f(T_j)$; parameter: ID



14 Drain-source breakdown voltage

$V_{(Br)DSS} = f(T_j)$; I_{D_typ} = 1 mA



15 Typ. gate charge

$V_{GS} = f(Q_{gate})$; I_D = 120 A pulsed; parameter: V_{DD}



16 Gate charge waveforms



Package Outline



https://www.infineon.com/cms/en/product/packages/PG-LHDSO/PG-LHDSO-10-2

Footprint



Packaging



all dimensions in mm

Revision History

Revision	Date	Changes
Revision 1.1	21.08.2023	Final Data Sheet
Revision 1.2	31.07.2024	updated package drawing with harmonized & standardized tolerance writing methodology

Trademarks
All referenced product or service names and trademarks are the property of their respective owners.

Edition 2024-07-31

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2024 Infineon Technologies AG

All Rights Reserved.

Do you have any questions about any aspect of this document?

Email: erratum@infineon.com

Document reference
IAUCN04S6N009T-Data-Sheet-12-Infineon

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications. The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (**www.infineon.com**).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact the nearest Infineon Technologies Office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.