Automotive MOSFET

OptiMOS™ 5 Power-Transistor

RoHS Infineon Automotive Quality AEC Qualified

PG-HSOG-4-1



Features

- OptiMOS™ power MOSFET for automotive applications
- N-channel – Enhancement mode – Normal Level
- Extended qualification beyond AEC-Q101
- Enhanced electrical testing
- Robust design
- MSL2 up to 260°C peak reflow
- 175°C operating temperature
- RoHS compliant
- 100% Avalanche tested

Potential applications

General automotive applications.

Product validation

Qualified for automotive applications. Product validation according to AEC-Q101.

Product Summary

V_{DS}	100	V
$R_{DS(on)}$	1.6	mΩ
I_D (chip limited)	310	A

Type	Package	Marking
IAUMN10S5N016G	PG-HSOG-4-1	5N10N016

Table of Contents

Maximum ratings

at T_j=25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Value	Unit
Continuous drain current	I_D	V_{GS}=10 V, Chip limitation[1,2)]	310	A
		V_{GS}=10V, DC current[3)]	220	
		T_a=100 °C, V_{GS}=10 V, R_{thJA} on 2s2p[2,4)]	64	
Pulsed drain current[2)]	$I_{D,pulse}$	T_C=25 °C, t_p= 100 µs	1100	
Avalanche energy, single pulse[2)]	E_{AS}	I_D=110 A	617	mJ
Avalanche current, single pulse	I_{AS}	–	220	A
Gate source voltage	V_{GS}	–	±20	V
Power dissipation	P_{tot}	T_C=25 °C	325	W
Operating and storage temperature	T_j, T_{stg}	–	-55 ... +175	°C

Thermal characteristics[2)]

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Thermal resistance, junction - case	R_{thJC}	–	–	–	0.46	K/W
Thermal resistance, junction - ambient[3)]	R_{thJA}	–	–	7.8	–	

Electrical characteristics

at T_j=25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Static characteristics						
Drain-source breakdown voltage	$V_{(Br)DSS}$	V_{GS}=0 V, I_D=1 mA	100	–	–	V
Gate threshold voltage	$V_{GS(th)}$	V_{DS}=V_{GS}, I_D=230 µA	2.2	3	3.8	
Zero gate voltage drain current	I_{DSS}	V_{DS}=100 V, V_{GS}=0 V, T_j=25 °C	–	–	1	µA
		V_{DS}=100 V, V_{GS}=0 V, T_j=100 °C[2)]	–	–	100	
Gate-source leakage current	I_{GSS}	V_{GS}=20 V, V_{DS}=0 V	–	–	100	nA
Drain-source on-state resistance	$R_{DS(on)}$	V_{GS}=6 V, I_D=50 A	–	1.6	2.1	mΩ
		V_{GS}=10 V, I_D=100 A	–	1.2	1.6	
Gate resistance[2)]	R_G	–	–	1.3	–	Ω

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Dynamic characteristics[2]						
Input capacitance	C_{iss}	V_{GS}=0 V, V_{DS}=50 V, f=1 MHz	–	10439	13570	pF
Output capacitance	C_{oss}		–	1674	2180	
Reverse transfer capacitance	C_{rss}		–	71	90	
Turn-on delay time	$t_{d(on)}$	V_{DD}=50 V, V_{GS}=10 V, I_D=100 A, R_G=3.5 Ω	–	25	–	ns
Rise time	t_r		–	13	–	
Turn-off delay time	$t_{d(off)}$		–	55	–	
Fall time	t_f		–	50	–	
Gate Charge Characteristics[2]						
Gate to source charge	Q_{gs}	V_{DD}=50 V, I_D=100 A, V_{GS}=0 to 10 V	–	47	60	nC
Gate to drain charge	Q_{gd}		–	28	42	
Gate charge total	Q_g		–	142	190	
Gate plateau voltage	$V_{plateau}$		–	4.5	–	V
Reverse Diode						
Diode continous forward current[2]	I_S	T_C=25 °C	–	–	220	A
Diode pulse current[2]	$I_{S,pulse}$	T_C=25 °C, t_p= 100 µs	–	–	1100	
Diode forward voltage	V_{SD}	V_{GS}=0 V, I_F=110 A, T_j=25 °C	–	0.9	1.2	V
Reverse recovery time[2]	t_{rr}	V_R=50 V, I_F=50A, di_F/dt =100 A/µs	–	79	119	ns
Reverse recovery charge[2]	Q_{rr}		–	175	350	nC

[1] Practically the current is limited by the overall system design including the customer-specific PCB.

[2] The parameter is not subject to production testing – specified by design.

[3] Current is limited by package.

[4] Device on 2s2p FR4 PCB defined in accordance with JEDEC standards (JESD51-5, -7). PCB is vertical in still air.

Electrical characteristics diagrams

1 Power dissipation

$P_{tot} = f(T_C)$; $V_{GS} \geq 6$ V



2 Drain current

$I_D = f(T_C)$; $V_{GS} \geq 6$ V



3 Safe operating area

$I_D = f(V_{DS})$; $T_C = 25$ °C; $D = 0$; parameter: t_p



4 Max. transient thermal impedance

$Z_{thJC} = f(t_p)$; parameter: $D=t_p/T$



5 Typ. output characteristics

$I_D = f(V_{DS})$; $T_j = 25$ °C; parameter: V_{GS}



6 Typ. drain-source on-state resistance

$R_{DS(on)} = f(I_D)$; $T_j = 25$ °C; parameter: V_{GS}



7 Typ. transfer characteristics

$I_D = f(V_{GS})$; $V_{DS} = 6$V: parameter: T_j



8 Typ. drain-source on-state resistance

$R_{DS(on)} = f(T_j)$; parameter: I_D, V_{GS}



9 Typ. gate threshold voltage

$V_{GS(th)} = f(T_j)$; $V_{GS} = V_{DS}$; parameter: I_D



10 Typ. capacitances

$C = f(V_{DS})$; $V_{GS} = 0$ V; $f = 1$ MHz



11 Typical forward diode characteristics

$I_F = f(V_{SD})$; parameter: T_j



12 Typ. avalanche characteristics

$I_{AS} = f(t_{AV})$; parameter: $T_{j(start)}$



13 Typical avalanche energy

$E_{AS} = f(T_j)$; parameter: ID



14 Drain-source breakdown voltage

$V_{Br(DSS)} = f(T_j)$; $I_D = 1$ mA



15 Typ. gate charge

$V_{GS} = f(Q_{gate})$; $I_D = 100$ A pulsed; parameter: V_{DD}



16 Gate charge waveforms



Package Outline



All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1 [⇿]
Drawing according to ISO 8015, general tolerances ISO 2768-mK

Footprint



All dimensions are in units mm
All pads are non-solder mask defined

Packaging



All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1 [⇿]

Revision History

Revision	Date	Changes
Revision 1.0	2024-04-22	Final Data Sheet

Trademarks
All referenced product or service names and trademarks are the property of their respective owners.

Edition 2024-04-22

Published by

Infineon Technologies AG

81726 Munich, Germany

Do you have any questions about any aspect of this document?

Email: erratum@infineon.com

Document reference
IAUMN10S5N016G-Data-Sheet-01-Infineon