Automotive MOSFET

OptiMOS™ 5 Power-Transistor

RoHS Infineon Automotive Quality AEC Qualified



Features

- OptiMOS™ power MOSFET for automotive applications
- N-channel – enhancement mode – normal level
- Extended qualification beyond AEC-Q101
- Enhanced electrical testing
- Robust design
- MSL1 up to 260°C peak reflow
- 175°C operating temperature
- RoHS compliant
- 100% avalanche tested
- Very low reverse recovery charge (Q_{rr})



Potential applications

General automotive applications.

Product validation

Qualified for automotive applications. Product validation according to AEC-Q101.

Product Summary

V_{DS}	120	V
$R_{DS(on)}$	1.8	mΩ
I_D (chip limited)	310	A

Type	Package	Marking
IAUTN12S5N018G	PG-HSOG-8-1	5N12N018

Table of Contents

Description 1
Maximum ratings 3
Thermal characteristics 4
Electrical characteristics 4
Electrical characteristics diagrams 6
Package outline & footprint 10
Revision history 11
Disclaimer 12

Maximum ratings

at T_j=25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Value	Unit
Continuous drain current	I_D	V_{GS}=10 V, Chip limitation[1,2)]	310	A
		V_{GS}=10V, DC current[3)]	300	
		T_a=100 °C, V_{GS}=10 V, R_{thJA} on 2s2p[2,4)]	37	
Pulsed drain current[2)]	$I_{D,pulse}$	T_C=25 °C, t_p= 100 µs	1160	
Avalanche energy, single pulse[2)]	E_{AS}	I_D=150 A	510	mJ
Avalanche current, single pulse	I_{AS}	–	300	A
Gate source voltage	V_{GS}	–	±20	V
Power dissipation	P_{tot}	T_C=25 °C	358	W
Operating and storage temperature	T_j, T_{stg}	–	-55 ... +175	°C
IEC climatic category; DIN IEC 68-1	–	–	55/175/56	

Thermal characteristics[2)]

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Thermal resistance, junction - case	R_{thJC}	–	–	–	0.42	K/W
Thermal resistance, junction - ambient[4)]	R_{thJA}	–	–	14.8	–	

Electrical characteristics

at T_j=25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Static characteristics						
Drain-source breakdown voltage	$V_{(Br)DSS}$	V_{GS}=0 V, I_D=1 mA	120	–	–	V
Gate threshold voltage	$V_{GS(th)}$	V_{DS}=V_{GS}, I_D=270 µA	2.6	3.1	3.6	
Zero gate voltage drain current	I_{DSS}	V_{DS}=120 V, V_{GS}=0 V, T_j=25 °C	–	0.3	3	µA
		V_{DS}=120 V, V_{GS}=0 V, T_j=100 °C[2)]	–	10	100	
Gate-source leakage current	I_{GSS}	V_{GS}=20 V, V_{DS}=0 V	–	–	100	nA
Drain-source on-state resistance	$R_{DS(on)}$	V_{GS}=7 V, I_D=50 A	–	1.9	2.8	mΩ
		V_{GS}=10 V, I_D=100 A	–	1.5	1.8	
Gate resistance[2)]	R_G	–	–	1.1	–	Ω

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Dynamic characteristics[2]						
Input capacitance	C_{iss}	V_{GS}=0 V, V_{DS}=60 V, f=1 MHz	–	8260	10740	pF
Output capacitance	C_{oss}		–	2369	3080	
Reverse transfer capacitance	C_{rss}		–	45	68	
Turn-on delay time	$t_{d(on)}$	V_{DD}=60 V, V_{GS}=10 V, I_D=100 A, R_G=3.5 Ω	–	27	–	ns
Rise time	t_r		–	47	–	
Turn-off delay time	$t_{d(off)}$		–	43	–	
Fall time	t_f		–	47	–	
Gate Charge Characteristics[2]						
Gate to source charge	Q_{gs}	V_{DD}=60 V, I_D=100 A, V_{GS}=0 to 10 V	–	43	55	nC
Gate to drain charge	Q_{gd}		–	23	35	
Gate charge total	Q_g		–	111	145	
Gate plateau voltage	$V_{plateau}$		–	5.2	–	V
Reverse Diode						
Diode continous forward current[2]	I_S	T_C=25 °C	–	–	310	A
Diode pulse current[2]	$I_{S,pulse}$	T_C=25 °C, t_p= 100 µs	–	–	1160	
Diode forward voltage	V_{SD}	V_{GS}=0 V, I_F=100 A, T_j=25 °C	–	0.85	0.95	V
Reverse recovery time[2]	t_{rr}	V_R=60 V, I_F=50A, di_F/dt =100 A/µs	–	45	67	ns
Reverse recovery charge[2]	Q_{rr}		–	34	68	nC

[1] Practically the current is limited by the overall system design including the customer-specific PCB.

[2] The parameter is not subject to production testing – specified by design.

[3] Current is limited by package.

[4] Device on 2s2p FR4 PCB defined in accordance with JEDEC standards (JESD51-5, -7). PCB is vertical in still air.

Electrical characteristics diagrams

1 Power dissipation

$P_{tot} = f(T_C)$; $V_{GS} \geq 6$ V



2 Drain current

$I_D = f(T_C)$; $V_{GS} \geq 6$ V



3 Safe operating area

$I_D = f(V_{DS})$; $T_C = 25$ °C; $D = 0$; parameter: t_p



4 Max. transient thermal impedance

$Z_{thJC} = f(t_p)$; parameter: $D=t_p/T$



5 Typ. output characteristics

$I_D = f(V_{DS})$; $T_j = 25$ °C; parameter: V_{GS}



6 Typ. drain-source on-state resistance

$R_{DS(on)} = f(I_D)$; $T_j = 25$ °C; parameter: V_{GS}



7 Typ. transfer characteristics

$I_D = f(V_{GS})$; $V_{DS} = 6$V: parameter: T_j



8 Typ. drain-source on-state resistance

$R_{DS(on)} = f(T_j)$; parameter: I_D, V_{GS}



9 Typ. gate threshold voltage



10 Typ. capacitances



11 Typical forward diode characteristics



12 Typ. avalanche characteristics



13 Typical avalanche energy



14 Drain-source breakdown voltage



15 Typ. gate charge



16 Gate charge waveforms



Package Outline



Footprint



Packaging



Revision History

Revision	Date	Changes
Revision 1.0	2022-12-19	Final data sheet
Revision 1.01	2023-08-29	Reduced typical on-state resistance $R_{DS(on)}$
Revision 1.10	2024-11-18	Test conditions in graph 14 updated

Trademarks
All referenced product or service names and trademarks are the property of their respective owners.

Edition 2024-11-18

Published by

Infineon Technologies AG

81726 Munich, Germany

Do you have any questions about any aspect of this document?

Email: erratum@infineon.com

Document reference
IAUTN12S5N018G-Data-Sheet-101-Infineon

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications. The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (**www.infineon.com**).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact the nearest Infineon Technologies Office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.