

Product Qualification Report

ICB2FL01G

Fluorescent Ballast IC

Description

This product qualification report describes the characteristics of the product with respect to quality and reliability.

The qualification sample selection was done on production lots which were manufactured and tested on standard production processes and meet the defined requirements.

The qualification test results of those products as outlined in this document are based on **JEDEC** for target applications and may reference existing qualification results of similar products. Such referencing is justified by the structural similarity of the products.

Qualification Assessment

Qualified according to **JEDEC Standard** and assessed as PASS

For further information about comparable products, please contact the nearest Infineon Technologies office (www.infineon.com).

ICB2FL01G
PG-DSO-19
MSL: 3; 260°C

qualified in 2009

Electrical Stress Test Results:

Test Description	Abbr.	Condition	Duration	Lots/SS	Fail/Qty	Result
High Temperature Operating Life JESD22 A108	HTOL	Ta = 125°C	1000 h	3x77	0/231	PASS
Temperature Humidity Test (biased) JESD22 A101	THB*	Ta = 85 °C RH = 85 %	1000 h	3x25	0/75	PASS
ESD Human Body Model JESD22 A114	ESD HBM	Class 2 2000 V to < 4000 V	-	-	-	PASS
ESD Charged Device Model JESD22 C101	ESD CDM	Class C2 500 V to < 1000 V	-	-	-	PASS
Latch-Up JESD 78	LU	-	-	-	-	PASS

Environmental Stress Test Results:

Test Description	Abbr.	Condition	Duration	Lots/SS	Fail/Qty	Result
Pre-Conditioning J-STD-20/JESD22 A111	PC	MSL and 3 x reflow/wave	-	9x25	0/225	PASS
Temperature Cycling JESD22 A104	TC*	-55°C to +150°C	1000 cyc	3x25	0/75	PASS
Unbiased Highly Accelerated Stress Test JESD22 A102	AC*	Ta = 121°C RH = 100 %	96 h	3x25	0/75	PASS
High Temperature Storage Life JESD22 A103	HTSL	Ta = 150°C	1000 h	3x25	0/75	PASS

Notes:

* For SMD devices reliability stress tests performed after pre-conditioning test (PC)

Further abbreviations: MSL - moisture sensitivity level, Qty – quantity, RH – relative humidity, SS – sample size, Ta – ambient temperature

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2016-01-22

Published by

Infineon Technologies AG

81726 München, Germany

© 2018 Infineon Technologies AG.

All Rights Reserved.

Do you have a question about this document?

Email: erratum@infineon.com

Document reference

n.a.

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.