

### IGBT

TRENCHSTOP<sup>™</sup> IGBT4 Low Power Chip IGC13T120T8L

Data Sheet

### Industrial Power Control



### **Table of Contents**

Features and Applications	Ì
Mechanical Parameters3	
Maximum Ratings4	•
Static and Electrical Characteristics4	•
Further Electrical Characteristics5	
Chip Drawing6	i
Revision History7	
Relevant Application Notes7	
Legal Disclaimer8	




### TRENCHSTOP<sup>™</sup> IGBT4 Low Power Chip

#### Features:

- 1200V trench & field stop technology
- Low switching losses
- Positive temperature coefficient
- Easy paralleling

#### **Recommended for:**

- Low / medium power modules
- Applications:
- Low / medium power drives



Chip Type	V <sub>CE</sub>	I <sub>Cn</sub>	Die Size	Package
IGC13T120T8L	1200V	10A	3.54mm x 3.81mm	Sawn on foil

#### **Mechanical Parameters**

Die size		3.54 x 3.81		
Emitter pad size		See chip drawing	- mm²	
Gate pad size		0.61 x 1.10	mm	
Area total		13.49		
Silicon thickness		115	μm	
Wafer size		200	mm	
Maximum possible ch	ips per wafer	2036		
Passivation frontside		Photoimide		
Pad metal		3200nm AlSiCu		
Backside metal Ni Ag – system To achieve a reliable solder connection recommended not to consume the Ni layer production process				
Die bond		Electrically conductive epoxy glue and soft so	lder	
Wire bond		Al, ≤500µm		
Reject ink dot size		Ø 0.65mm; max. 1.2mm		
Storage environment	for original and sealed MBB bags	Ambient atmosphere air, temperature 17°C – 2	25°C	
(<6 months)	for open MBB bags	Acc. IEC 62258-3; Section 9.4 Storage Environ	ment.	



#### **Maximum Ratings**

In general, from reliability and lifetime point of view, the lower the operation junction temperature and/or the applied voltage, the greater the expected lifetime of any semiconductor device.

Parameter	Symbol	Value	Unit
Collector-emitter voltage, $T_{vj}$ =25°C	V <sub>CE</sub>	1200	V
DC collector current, limited by $T_{vj max}$ <sup>1</sup>	I <sub>C</sub>	-	А
Pulsed collector current, $t_p$ limited by $T_{vj max}^2$	I <sub>C,puls</sub>	30	А
Gate-emitter voltage	V <sub>GE</sub>	±20	V
Junction temperature	T <sub>vj</sub>	-40 +175	°C
Operating junction temperature	T <sub>vj op</sub>	-40 +150	°C
Short circuit data $^{1/2/3}$ V <sub>GE</sub> =15V, V <sub>CC</sub> =800V, $T_{vj}$ =150°C	t <sub>sc</sub>	10	μs

#### Static Characteristics (tested on wafer), Tvi=25°C

Parameter	Symbol	Conditions	Value			Unit
	Symbol	Conditions	min.	typ.	max.	
Collector-emitter breakdown voltage	V <sub>(BR)CES</sub>	V <sub>GE</sub> =0V, <i>I</i> <sub>C</sub> =0.5mA	1200	-	-	
Collector-emitter saturation voltage	V <sub>CEsat</sub>	V <sub>GE</sub> =15V, <i>I</i> <sub>C</sub> =10A	1.58	1.85	2.07	V
Gate-emitter threshold voltage	V <sub>GE(th)</sub>	<i>I</i> <sub>C</sub> =0.35mA, <i>V</i> <sub>GE</sub> = <i>V</i> <sub>CE</sub>	5.3	5.8	6.3	
Zero gate voltage collector current	I <sub>CES</sub>	V <sub>CE</sub> =1200V, V <sub>GE</sub> =0V	-	-	1.2	μA
Gate-emitter leakage current	I <sub>GES</sub>	$V_{CE}$ =0V, $V_{GE}$ =20V	-	-	120	nA
Integrated gate resistor	r <sub>G</sub>			none		Ω

#### **Electrical Characteristics**<sup>2</sup>

Parameter	Symbol Conditions		Value			Unit
Falameter	Symbol	Conditions	min.	typ.	max.	Unit
Collector-emitter saturation voltage	V <sub>CEsat</sub>	V <sub>GE</sub> =15V, <i>I</i> <sub>C</sub> =10A, <i>T</i> <sub>vj</sub> =150°C	-	2.25	-	V
Input capacitance	C <sub>ies</sub>	$V_{CE}=25V$ ,	-	625	-	~F
Reverse transfer capacitance	C <sub>res</sub>	V <sub>GE</sub> =0V, <i>f</i> =1MHz <i>T</i> <sub>vj</sub> =25°C	-	40	-	рF

<sup>&</sup>lt;sup>1</sup> Depending on thermal properties of assembly.

<sup>&</sup>lt;sup>2</sup> Not subject to production test - verified by design/characterization.

<sup>&</sup>lt;sup>3</sup> Allowed number of short circuits: <1000; time between short circuits: >1s.




#### **Further Electrical Characteristics**

Switching characteristics and thermal properties are depending strongly on module design and mounting technology and can therefore not be specified for a bare die.

Application exampleFP10R12W1T4Rev. 2.1	Application example	FP10R12W1T4	Rev. 2.1
--	---------------------	-------------	----------



#### **Chip Drawing**



Die-Size 3540 um x 3810 um

E = Emitter

 $\mathbf{G} = \text{Gate}$ 



#### **Bare Die Product Specifics**

Test coverage at wafer level cannot cover all application conditions. Therefore it is recommended to test all characteristics which are relevant for the application at package level, including RBSOA and SCSOA.

#### Description

AQL 0.65 for visual inspection according to failure catalogue
Electrostatic Discharge Sensitive Device according to MIL-STD 883

#### **Revision History**

Revision	Subjects (major changes since last revision)	Date
2.0	Final data sheet	09.09.2016

#### **Relevant Application Notes**



Published by Infineon Technologies AG 81726 München, Germany © Infineon Technologies AG 2016. All Rights Reserved.

#### **IMPORTANT NOTICE**

The information given in this document shall in <u>no event</u> be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie"). With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

Please note that this product is <u>not</u> qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

#### <u>WARNINGS</u>

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may <u>not</u> be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

www.infineon.com

Published by Infineon Technologies AG