

Final datasheet  
Reverse-Conducting IGBT with monolithic body diode

Features

- $V_{CE} = 1400\text{ V}$
- $I_C = 30\text{ A}$
- Powerful monolithic body diode with low forward voltage designed for soft commutation only
- Very tight parameter distribution
- High ruggedness, temperature stable behavior
- Very low  $V_{CEsat}$
- Easy paralleling capability due to positive temperature coefficient in  $V_{CEsat}$
- Low EMI
- Qualified according to JESD-022 for target applications
- Pb-free lead plating; RoHS compliant
- Halogen free (according to IEC 61249-2-21)
- Complete product spectrum and PSpice Models: <http://www.infineon.com/igbt/>


Potential applications

- Induction cooker
- Microwave ovens

Product validation

- Qualified for industrial applications according to the relevant tests of JEDEC47/20/22

Description



| Type         | Package              | Marking |
|--------------|----------------------|---------|
| IHW30N140R5L | PG-TO247-3-STD-NN2.5 | H30QR5L |



Table of contents

|   |                                |    |
|---|--------------------------------|----|
|   | Description .....              | 1  |
|   | Features .....                 | 1  |
|   | Potential applications .....   | 1  |
|   | Product validation .....       | 1  |
|   | Table of contents .....        | 2  |
| 1 | Package .....                  | 3  |
| 2 | IGBT .....                     | 3  |
| 3 | Diode .....                    | 5  |
| 4 | Characteristics diagrams ..... | 6  |
| 5 | Package outlines .....         | 11 |
| 6 | Testing conditions .....       | 12 |
|   | Revision history .....         | 13 |
|   | Disclaimer .....               | 14 |

## 1 Package

**Table 1** Characteristic values

| Parameter                                                       | Symbol        | Note or test condition                               | Values |      |      | Unit |
|-----------------------------------------------------------------|---------------|------------------------------------------------------|--------|------|------|------|
|                                                                 |               |                                                      | Min.   | Typ. | Max. |      |
| Internal emitter inductance measured 5 mm (0.197 in.) from case | $L_E$         |                                                      |        | 13   |      | nH   |
| Storage temperature                                             | $T_{stg}$     |                                                      | -55    |      | 150  | °C   |
| Soldering temperature                                           | $T_{sold}$    | wave soldering 1.6 mm (0.063 in.) from case for 10 s |        |      | 260  | °C   |
| Mounting torque                                                 | $M$           | M3 screw, Maximum of mounting processes: 3           |        |      | 0.6  | Nm   |
| Thermal resistance, junction-ambient                            | $R_{th(j-a)}$ |                                                      |        |      | 40   | K/W  |
| IGBT thermal resistance, junction-case                          | $R_{th(j-c)}$ |                                                      |        |      | 0.49 | K/W  |
| Diode thermal resistance, junction-case                         | $R_{th(j-c)}$ |                                                      |        |      | 0.49 | K/W  |

## 2 IGBT

**Table 2** Maximum rated values

| Parameter                                              | Symbol       | Note or test condition                                 |                       | Values | Unit |
|--------------------------------------------------------|--------------|--------------------------------------------------------|-----------------------|--------|------|
| Collector-emitter voltage                              | $V_{CE}$     | $T_{vj} \geq 25\text{ °C}$                             |                       | 1400   | V    |
| DC collector current, limited by $T_{vjmax}$           | $I_C$        | limited by bondwire                                    | $T_c = 25\text{ °C}$  | 80     | A    |
|                                                        |              |                                                        | $T_c = 100\text{ °C}$ | 58     |      |
| Pulsed collector current, $t_p$ limited by $T_{vjmax}$ | $I_{Cpulse}$ |                                                        |                       | 90     | A    |
| Non repetitive peak collector current <sup>1)</sup>    | $I_{CSM}$    |                                                        |                       | 200    | A    |
| Turn-off safe operating area <sup>2)</sup>             |              | $V_{CE} \leq 1400\text{ V}, T_{vj} \leq 175\text{ °C}$ |                       | 90     | A    |
| Gate-emitter voltage                                   | $V_{GE}$     |                                                        |                       | ±20    | V    |
| Transient gate-emitter voltage                         | $V_{GE}$     | $t_p \leq 10\text{ }\mu\text{s}, D < 0.01$             |                       | ±25    | V    |
| Power dissipation                                      | $P_{tot}$    |                                                        | $T_c = 25\text{ °C}$  | 306    | W    |
|                                                        |              |                                                        | $T_c = 100\text{ °C}$ | 153    |      |

1) capacitor charging saturation current limited by  $T_{vjmax} < 175\text{ °C}$  and  $t_p < 3\text{ }\mu\text{s}$

2)  $dV/dt < 1\text{ kV}/\mu\text{s}$

**Table 3**                      **Characteristic values**

| Parameter                            | Symbol       | Note or test condition                                                                                                                                |                                                     | Values |       |      | Unit          |
|--------------------------------------|--------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------|--------|-------|------|---------------|
|                                      |              |                                                                                                                                                       |                                                     | Min.   | Typ.  | Max. |               |
| Collector-emitter breakdown voltage  | $V_{BRCES}$  | $I_C = 0.5 \text{ mA}$ , $V_{GE} = 0 \text{ V}$                                                                                                       |                                                     | 1400   |       |      | V             |
| Collector-emitter saturation voltage | $V_{CEsat}$  | $I_C = 30 \text{ A}$ , $V_{GE} = 15 \text{ V}$                                                                                                        | $T_{vj} = 25 \text{ °C}$                            |        | 1.65  | 1.95 | V             |
|                                      |              |                                                                                                                                                       | $T_{vj} = 125 \text{ °C}$                           |        | 1.85  |      |               |
|                                      |              |                                                                                                                                                       | $T_{vj} = 175 \text{ °C}$                           |        | 1.9   |      |               |
| Gate-emitter threshold voltage       | $V_{GEth}$   | $I_C = 0.47 \text{ mA}$ , $V_{CE} = V_{GE}$                                                                                                           |                                                     | 4      | 5.6   | 6.2  | V             |
| Zero gate-voltage collector current  | $I_{CES}$    | $V_{CE} = 1400 \text{ V}$ , $V_{GE} = 0 \text{ V}$                                                                                                    | $T_{vj} = 25 \text{ °C}$                            |        |       | 100  | $\mu\text{A}$ |
|                                      |              |                                                                                                                                                       | $T_{vj} = 175 \text{ °C}$                           |        | 700   |      |               |
| Gate-emitter leakage current         | $I_{GES}$    | $V_{CE} = 0 \text{ V}$ , $V_{GE} = 20 \text{ V}$                                                                                                      |                                                     |        |       | 100  | nA            |
| Transconductance                     | $g_{fs}$     | $I_C = 30 \text{ A}$ , $V_{CE} = 20 \text{ V}$                                                                                                        |                                                     |        | 26.4  |      | S             |
| Input capacitance                    | $C_{ies}$    | $V_{CE} = 25 \text{ V}$ , $V_{GE} = 0 \text{ V}$ , $f = 100 \text{ kHz}$                                                                              |                                                     |        | 1520  |      | pF            |
| Output capacitance                   | $C_{oes}$    | $V_{CE} = 25 \text{ V}$ , $V_{GE} = 0 \text{ V}$ , $f = 100 \text{ kHz}$                                                                              |                                                     |        | 45    |      | pF            |
| Reverse transfer capacitance         | $C_{res}$    | $V_{CE} = 25 \text{ V}$ , $V_{GE} = 0 \text{ V}$ , $f = 100 \text{ kHz}$                                                                              |                                                     |        | 37    |      | pF            |
| Gate charge                          | $Q_G$        | $V_{CC} = 1120 \text{ V}$ , $I_C = 30 \text{ A}$ , $V_{GE} = 15 \text{ V}$                                                                            |                                                     |        | 210   |      | nC            |
| Turn-off delay time                  | $t_{d(off)}$ | $V_{GE} = 0/15 \text{ V}$ ,<br>$R_{G(off)} = 10 \text{ }\Omega$ , $C_r = 270 \text{ nF}$ ,<br>$L = 77 \text{ }\mu\text{H}$ , $R = 2.2 \text{ }\Omega$ | $T_{vj} = 25 \text{ °C}$ ,<br>$I_C = 30 \text{ A}$  |        | 170   |      | ns            |
|                                      |              |                                                                                                                                                       | $T_{vj} = 175 \text{ °C}$ ,<br>$I_C = 30 \text{ A}$ |        | 175   |      |               |
| Fall time (inductive load)           | $t_f$        | $V_{GE} = 0/15 \text{ V}$ ,<br>$R_{G(off)} = 10 \text{ }\Omega$ , $C_r = 270 \text{ nF}$ ,<br>$L = 77 \text{ }\mu\text{H}$ , $R = 2.2 \text{ }\Omega$ | $T_{vj} = 25 \text{ °C}$ ,<br>$I_C = 30 \text{ A}$  |        | 1065  |      | ns            |
|                                      |              |                                                                                                                                                       | $T_{vj} = 175 \text{ °C}$ ,<br>$I_C = 30 \text{ A}$ |        | 1195  |      |               |
| Soft turn-off energy                 | $E_{off}$    | $V_{GE} = 0/15 \text{ V}$ ,<br>$R_{G(off)} = 10 \text{ }\Omega$ , $C_r = 270 \text{ nF}$ ,<br>$L = 77 \text{ }\mu\text{H}$ , $R = 2.2 \text{ }\Omega$ | $T_{vj} = 25 \text{ °C}$ ,<br>$I_C = 30 \text{ A}$  |        | 0.147 |      | mJ            |
|                                      |              |                                                                                                                                                       | $T_{vj} = 175 \text{ °C}$ ,<br>$I_C = 30 \text{ A}$ |        | 0.175 |      |               |
| Operating junction temperature       | $T_{vj}$     |                                                                                                                                                       |                                                     | -40    |       | 175  | °C            |

### 3 Diode

**Table 4** Maximum rated values

| Parameter                                          | Symbol       | Note or test condition |                       | Values | Unit |
|----------------------------------------------------|--------------|------------------------|-----------------------|--------|------|
| Diode forward current, limited by $T_{vjmax}$      | $I_F$        | limited by bondwire    | $T_c = 25\text{ °C}$  | 80     | A    |
|                                                    |              |                        | $T_c = 100\text{ °C}$ | 60     |      |
| Diode pulsed current, $t_p$ limited by $T_{vjmax}$ | $I_{Fpulse}$ |                        |                       | 90     | A    |

**Table 5** Characteristic values

| Parameter                      | Symbol   | Note or test condition |                          | Values |      |      | Unit |
|--------------------------------|----------|------------------------|--------------------------|--------|------|------|------|
|                                |          |                        |                          | Min.   | Typ. | Max. |      |
| Diode forward voltage          | $V_F$    | $I_F = 30\text{ A}$    | $T_{vj} = 25\text{ °C}$  |        | 1.6  | 1.95 | V    |
|                                |          |                        | $T_{vj} = 125\text{ °C}$ |        | 1.8  |      |      |
|                                |          |                        | $T_{vj} = 175\text{ °C}$ |        | 1.9  |      |      |
| Operating junction temperature | $T_{vj}$ |                        |                          | -40    |      | 175  | °C   |

**Note:** For optimum lifetime and reliability, Infineon recommends operating conditions that do not exceed 80% of the maximum ratings stated in this datasheet.


Electrical Characteristic, at  $T_{vj} = 25\text{ °C}$ , unless otherwise specified.

Dynamic test circuit, energy losses include “tail” according to Figure B. (Test circuit Figure E).

4 Characteristics diagrams


Power dissipation as a function of case temperature

$P_{\text{tot}} = f(T_c)$   
 $T_{vj} \leq 175\text{ °C}$




Collector current as a function of case temperature

$I_C = f(T_c)$   
 $T_{vj} \leq 175\text{ °C}, V_{GE} \geq 15\text{ V}$




Typical output characteristic

$I_C = f(V_{CE})$   
 $T_{vj} = 25\text{ °C}$



Typical output characteristic


$I_C = f(V_{CE})$   
 $T_{vj} = 175\text{ °C}$



4 Characteristics diagrams


Typical transfer characteristic

$I_C = f(V_{GE})$   
 $V_{CE} = 20\text{ V}$




Typical collector-emitter saturation voltage as a function of junction temperature

$V_{CEsat} = f(T_{vj})$   
 $V_{GE} = 15\text{ V}$




Gate-emitter threshold voltage as a function of junction temperature

$V_{GEth} = f(T_{vj})$   
 $I_C = 0.47\text{ mA}$



Typical switching times as a function of collector current


$t = f(I_C)$   
 $T_{vj} = 175\text{ }^\circ\text{C}, V_{GE} = 0/15\text{ V}, C_r = 270\text{ nF}, R_G = 10\text{ }\Omega$



4 Characteristics diagrams


Typical switching times as a function of gate resistor

$t = f(R_G)$   
 $I_C = 30\text{ A}$ ,  $T_{vj} = 175\text{ °C}$ ,  $V_{GE} = 0/15\text{ V}$ ,  $C_r = 270\text{ nF}$




Typical switching times as a function of junction temperature

$t = f(T_{vj})$   
 $I_C = 30\text{ A}$ ,  $V_{GE} = 0/15\text{ V}$ ,  $C_r = 270\text{ nF}$ ,  $R_G = 10\ \Omega$




Typical switching energy losses as a function of collector current

$E = f(I_C)$   
 $V_{GE} = 0/15\text{ V}$ ,  $C_r = 270\text{ nF}$ ,  $R_G = 10\ \Omega$



Typical switching energy losses as a function of gate resistor


$E = f(R_G)$   
 $I_C = 30\text{ A}$ ,  $T_{vj} = 175\text{ °C}$ ,  $V_{GE} = 0/15\text{ V}$ ,  $C_r = 270\text{ nF}$



4 Characteristics diagrams


Typical switching energy losses as a function of junction temperature

$E = f(T_{vj})$   
 $V_{GE} = 0/15\text{ V}$ ,  $C_r = 270\text{ nF}$ ,  $R_G = 10\text{ }\Omega$




Typical switching energy losses as a function of resonant capacitance

$E = f(C_r)$   
 $I_C = 30\text{ A}$ ,  $T_{vj} = 175\text{ }^\circ\text{C}$ ,  $V_{GE} = 0/15\text{ V}$ ,  $R_G = 10\text{ }\Omega$




Typical gate charge

$V_{GE} = f(Q_G)$   
 $I_C = 30\text{ A}$



Typical capacitance as a function of collector-emitter voltage


$C = f(V_{CE})$   
 $f = 100\text{ kHz}$ ,  $V_{GE} = 0\text{ V}$



4 Characteristics diagrams


IGBT transient thermal impedance as a function of pulse width

$Z_{th(j-c)} = f(t_p)$   
 $D = t_p/T$




Diode transient thermal impedance as a function of pulse width

$Z_{th(j-c)} = f(t_p)$   
 $D = t_p/T$




Typical diode forward current as a function of forward voltage

$I_F = f(V_F)$



Typical diode forward voltage as a function of junction temperature

$V_F = f(T_{vj})$



5 Package outlines




Figure 1

6 Testing conditions




Figure A. Definition of switching times




Figure B. Definition of switching losses




Figure C. Typical switching behavior in resonant applications




Figure D. Thermal equivalent circuit




Figure E. Dynamic test circuit  
Resonant capacitor,  $C_r$   
Damping resistor,  $R$

Figure 2



Revision history

Revision history

| Document revision | Date of release | Description of changes         |
|-------------------|-----------------|--------------------------------|
| 0.10              | 2022-11-25      | Preliminary datasheet          |
| 1.00              | 2023-05-19      | Final datasheet                |
| 1.10              | 2024-06-07      | Updated switching related data |

## Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

**Edition 2024-06-07**

**Published by**

**Infineon Technologies AG**  
**81726 Munich, Germany**

**© 2024 Infineon Technologies AG**  
**All Rights Reserved.**

**Do you have a question about any aspect of this document?**

**Email:** [erratum@infineon.com](mailto:erratum@infineon.com)

**Document reference**  
**IFX-ABC707-003**

## Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Please note that this product is not qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

## Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.