

Product Qualification Report

IGOT40R070D1 E8220

Cool GaN™

Description

This product qualification report describes the characteristics of the product with respect to quality and reliability.

The qualification sample selection was done on production lots which were manufactured and tested on standard production processes and meet the defined requirements.

The qualification test results of those products as outlined in this document are based on **JEDEC** for target applications and may reference existing qualification results of similar products. Such referencing is justified by the structural similarity of the products.

Qualification Assessment

Fully qualified according to **JEDEC** for **Industrial Applications** and assessed as PASS

For further information about comparable products, please contact the nearest Infineon Technologies office (www.infineon.com).

IGOT40R070D1 E8220
PG-DSO-20
MSL: 3; 260°C

qualified 2018

Electrical Stress Test Results:

Test Description	Abbr.	Condition	Duration	Lots/SS	Fail/Qty	Result
High Temperature Storage Life <i>JESD22-A103</i>	HTSL	T _a = 150 °C	1000 h	3 x 45	0 / 135	PASS
High Temperature Reverse Bias <i>JESD22-A108</i>	HTRB ¹	T _a = 150 °C V _{DS} = 600 V	1000 h	3 x 77	0 / 231	PASS
Positive High Temperature Gate Stress <i>JESD22-A108</i>	HTGF ¹	T _a = 150 °C I _G = 50 mA	1000 h	3 x 77	0 / 231	PASS
Negative High Temperature Gate Stress <i>JESD22-A108</i>	HTGS ¹	T _a = 150 °C V _{GS} = -10 V	1000 h	3 x 77	0 / 231	PASS
Intermittent Operational Life Test <i>MIL-STD 750 / Meth.1037</i>	IOL ¹	ΔT = 100 K	15,000x	3 x 77	0 / 231	PASS
ESD (HBM) <i>JESD22-A114</i>	HBM	Class 2 (2000 V to <4000 V)		1 x 3 (per voltage level)	0 / 3	PASS
ESD (CDM) <i>JESD22-C101</i>	CDM	Class C3 (1000 V or greater)		1 x 3 (per voltage level)	0 / 3	PASS

Environmental Stress Test Results:

Test Description	Abbr.	Condition	Duration	Lots/SS	Fail/Qty	Result
Pre-Conditioning <i>J-STD020 / JESD22 A113</i>	PC	MSL and 3 x reflow		3	0	PASS
High Humidity, High Temperature Reverse Bias <i>JESD22 A101</i>	H ³ TRB ¹	T _a = 85 °C r.h. = 85% V _{DS} = 100 V	1000 h	3 x 77	0 / 231	PASS
Biased Highly Accelerated Stress Test <i>JESD22 A110</i>	HAST ¹	T _a = 130 °C r.h. = 85% V _{DS} = 480 V	192 h	3 x 77	0 / 231	PASS
Temperature Cycling <i>JESD22 A104</i>	TC ¹	-25 °C to +150 °C	1500x	3 x 77	0 / 231	PASS

Mechanical Stress Test Results:

Test Description	Abb	Condition	Duration	Lots	Fail/Qty	Result
Moisture Sensitivity Level <i>IPC / J-STD-020</i>	MSL	MSL 3 @ 260 °C			0 / 22	PASS

¹ For SMD devices, a preconditioning (PC) according to JESD22 was performed prior to selected reliability stress tests.

Additional, Non-Standard Reliability Test Data

Test Description	Abbr.	Condition	Duration	Lots/SS	Fail/Qty	Result
Dynamic High Temperature Reverse Bias	dynHTRB ¹	T _a = 150 °C V _{DS} = 600 V f = 100 kHz	1000 h	3 x 77	0 / 231	PASS
Dynamic Gate Current Bias	dynGCB	T _a = 150 °C f = 100 kHz	1000 h	1 x 14	0 / 14	PASS
High Voltage, High Humidity, High Temperature Reverse Bias	HV-H ³ TRB ¹	T _a = 85 °C r.h. = 85% V _{DS} = 480 V	1000 h	3 x 77	0 / 231	PASS
Unbiased Highly Accelerated Stress Test JESD22 A118	uHAST ¹	T _a = 130 °C r.h. = 85%	192 h	3 x 77	0 / 231	PASS
Low Temperature Reverse Bias	LTRB ¹	T _a = 0 °C V _{DS} = 600 V	1000 h	1 x 77	0 / 77	PASS
Positive Low Temperature Gate Stress	LTGF ¹	T _a = 0 °C I _G = 50 mA	1000 h	1 x 77	0 / 77	PASS
Negative Low Temperature Gate Stress	LTGS ¹	T _a = 0 °C V _{GS} = -10 V	1000 h	1 x 77	0 / 77	PASS
Positive High Humidity, High Temperature Gate Stress	H ³ TGF ¹	T _a = 85 °C r.h. = 85% I _G = 50 mA	1000 h	1 x 77	0 / 77	PASS
Negative High Humidity, High Temperature Gate Stress	H ³ TGS ¹	T _a = 85 °C r.h. = 85% V _{GS} = -10 V	1000 h	1 x 77	0 / 77	PASS
High Load Test		T _a = 25 °C V _{DS} ≤ 600 V I _D = 15 A (mean) f = 100 kHz	1000 h	1 x 10	0 / 10	PASS
Autoclave JESD22 A102	AC ¹	T _a = 121 °C r.h. = 100%	192 h	3 x 77	0 / 231	PASS

¹ For SMD devices, a preconditioning (PC) according to JESD22 was performed prior to selected reliability stress tests.

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2016-01-22

Published by

Infineon Technologies AG

81726 München, Germany

© 2018 Infineon Technologies AG.

All Rights Reserved.

Do you have a question about this document?

Email: erratum@infineon.com

Document reference

n.a.

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.