


# IMBF170R1K0M1

## CoolSiC™ 1700V SiC Trench MOSFET Silicon Carbide MOSFET

### Features

- Revolutionary semiconductor material - Silicon Carbide
- Optimized for fly-back topologies
- 12V/0V gate-source voltage compatible with most fly-back controllers
- Very low switching losses
- Benchmark gate threshold voltage,  $V_{GS(th)} = 4.5V$
- Fully controllable dV/dt for EMI optimization



### Benefits

- Reduction of system complexity
- Directly drive from fly-back controller
- Efficiency improvement and cooling effort reduction
- Enabling higher frequency



### Potential applications

- Energy generation
  - Solar string inverter
  - Solar Central inverter
- Industrial power supplies
  - Industrial UPS
  - Industrial SMPS
- Infrastructure – Charger
  - Charger



### Product validation

Qualified for industrial applications according to the relevant tests of JEDEC 47/20/22

**Note:** *the source and sense pins are not exchangeable, their exchange might lead to malfunction recommended for forward operation mode only*

**Table 1 Key Performance and Package Parameters**

Type	$V_{DS}$	$I_D$ $T_C = 25^\circ C, R_{th(j-c,max)}$	$R_{DS(on)}$ $T_j = 25^\circ C, I_D = 1A, V_{GS} = 12V$	$T_{vj,max}$	Marking	Package
IMBF170R1K0M1	1700V	5.2A	1000mΩ	175°C	170M11K0	PG-T0263-7

---

**Table of contents****Table of contents**

<b>Features .....</b>	<b>1</b>
<b>Benefits .....</b>	<b>1</b>
<b>Potential applications .....</b>	<b>1</b>
<b>Product validation .....</b>	<b>1</b>
<b>Table of contents.....</b>	<b>2</b>
<b>1    Maximum ratings .....</b>	<b>3</b>
<b>2    Thermal resistances .....</b>	<b>4</b>
<b>3    Electrical Characteristics .....</b>	<b>5</b>
3.1        Static characteristics.....	5
3.2        Dynamic characteristics.....	6
3.3        Switching characteristics.....	7
<b>4    Electrical characteristic diagrams .....</b>	<b>8</b>
<b>5    Package drawing.....</b>	<b>12</b>
<b>6    Test conditions .....</b>	<b>13</b>
<b>Revision history.....</b>	<b>14</b>

## Maximum ratings

### 1 Maximum ratings

For optimum lifetime and reliability, Infineon recommends operating conditions that do not exceed 80% of the maximum ratings stated in this datasheet.

**Table 2 Maximum ratings**

Parameter	Symbol	Value	Unit
Drain-source voltage, $T_{vj} \geq 25^\circ\text{C}$	$V_{DSS}$	1700	V
DC drain current for $R_{th(j-c,max)}$ , limited by $T_{vjmax}$ , $V_{GS} = 12\text{V}$ , $T_c = 25^\circ\text{C}$ $T_c = 100^\circ\text{C}$	$I_D$	5.2 3.7	A
Pulsed drain current, $t_p$ limited by $T_{vjmax}$ , $V_{GS} = 12\text{V}$	$I_{D,pulse}^1$	13.3	A
Gate-source voltage <sup>2</sup>			
Max transient voltage, < 1% duty cycle	$V_{GS}$	-10... 20	V
Recommended turn-on gate voltage	$V_{GS,on}$	12... 15	
Recommended turn-off gate voltage	$V_{GS,off}$	0	
Power dissipation, limited by $T_{vjmax}$			
$T_c = 25^\circ\text{C}$	$P_{tot}$	68	W
$T_c = 100^\circ\text{C}$		34	
Virtual junction temperature	$T_{vj}$	-55... 175	°C
Storage temperature	$T_{stg}$	-55... 150	°C
Soldering temperature			
Reflow soldering (MSL1 according to JEDEC J-STD-020)	$T_{sold}$	260	°C

<sup>1</sup> verified by design

<sup>2</sup> **Important note:** The selection of positive and negative gate-source voltages impacts the long-term behavior of the device. The design guidelines described in [Application Note AN2018-09](#) must be considered to ensure sound operation of the device over the planned lifetime.

## Thermal resistances

## 2 Thermal resistances

**Table 3**

Parameter	Symbol	Conditions	Value			Unit
			min.	typ.	max.	
MOSFET thermal resistance, junction – case	$R_{th(j-c)}$		-	1.7	2.2	K/W
Thermal resistance, junction – ambient	$R_{th(j-a)}$	leaded	-	-	62	K/W

### 3 Electrical Characteristics

#### 3.1 Static characteristics

**Table 4 Static characteristics (at  $T_{vj} = 25^\circ\text{C}$ , unless otherwise specified)**

Parameter	Symbol	Conditions	Value			Unit
			min.	typ.	max.	
Drain-source on-state resistance	$R_{DS(on)}$	$V_{GS} = 12\text{V}, I_D = 1\text{A},$ $T_{vj} = 25^\circ\text{C}$ $T_{vj} = 100^\circ\text{C}$ $T_{vj} = 175^\circ\text{C}$ $V_{GS} = 15\text{V}, I_D = 1\text{A},$ $T_{vj} = 25^\circ\text{C}$	-	1000 1416 2037 809	- - - 880	mΩ
Gate-source threshold voltage	$V_{GS(th)}$	(tested after 1 ms pulse at $V_{GS} = 20\text{V}$ ) $I_D = 1.1\text{mA}, V_{DS} = V_{GS}$ $T_{vj} = 25^\circ\text{C}$ $T_{vj} = 175^\circ\text{C}$	3.5 -	4.5 3.6	5.7 -	V
Zero gate voltage drain current	$I_{DSS}$	$V_{GS} = 0\text{V}, V_{DS} = 1700\text{V}$ $T_{vj} = 25^\circ\text{C}$ $T_{vj} = 175^\circ\text{C}$	- -	0.4 6	11 -	μA
Gate-source leakage current	$I_{GSS}$	$V_{GS} = 20\text{V}, V_{DS} = 0\text{V}$ $V_{GS} = -10\text{V}, V_{DS} = 0\text{V}$	- -	- -	100 -100	nA
Transconductance	$g_{fs}$	$V_{DS} = 20\text{V}, I_D = 1\text{A}$	-	0.42	-	S
Internal gate resistance	$R_{G,int}$	$f = 1\text{MHz}, V_{AC} = 25\text{mV}$	-	35	-	Ω

### 3.2 Dynamic characteristics

**Table 5 Dynamic characteristics (at  $T_{vj} = 25^\circ\text{C}$ , unless otherwise specified)**

<b>Parameter</b>	<b>Symbol</b>	<b>Conditions</b>	<b>Value</b>			<b>Unit</b>
			<b>min.</b>	<b>typ.</b>	<b>max.</b>	
Input capacitance	$C_{iss}$	$V_{DD} = 1000\text{V}, V_{GS} = 0\text{V}, f = 1\text{MHz}, V_{AC} = 25\text{mV}$	-	275	-	$\text{pF}$
Output capacitance	$C_{oss}$		-	7.2	-	
Reverse capacitance	$C_{rss}$		-	0.7	-	
$C_{oss}$ stored energy	$E_{oss}$		-	1.3	-	$\mu\text{J}$
Total gate charge	$Q_G$	$V_{DD} = 1000\text{V}, I_D = 1\text{A}, V_{GS} = 0/12\text{V}$ , turn-on pulse	-	5	-	$\text{nC}$
Gate to source charge	$Q_{GS,pl}$		-	1.5	-	
Gate to drain charge	$Q_{GD}$		-	1.6	-	

## Electrical Characteristics

## 3.3 Switching characteristics

Table 6 Switching characteristics, Inductive load<sup>3</sup>

Parameter	Symbol	Conditions	Value			Unit
			min.	typ.	max.	
<b>MOSFET Characteristics, <math>T_{vj} = 25^\circ\text{C}</math></b>						
Turn-on delay time	$t_{d(on)}$	$V_{DD} = 1000\text{V}$ , $I_D = 1\text{A}$ , $V_{GS} = 0/12\text{V}$ , $R_{G,\text{ext}} = 22\Omega$ , $L_\sigma = 40\text{nH}$ , diode: body diode at $V_{GS} = 0\text{V}$ see Fig. E	-	19	-	ns
Rise time	$t_r$		-	14	-	
Turn-off delay time	$t_{d(off)}$		-	20	-	
Fall time	$t_f$		-	22	-	
Turn-on energy	$E_{on}$		-	31	-	
Turn-off energy	$E_{off}$		-	7	-	
Total switching energy	$E_{tot}$		-	37	-	


**MOSFET Characteristics,  $T_{vj} = 175^\circ\text{C}$** 

Turn-on delay time	$t_{d(on)}$	$V_{DD} = 1000\text{V}$ , $I_D = 1\text{A}$ , $V_{GS} = 0/12\text{V}$ , $R_{G,\text{ext}} = 22\Omega$ , $L_\sigma = 40\text{nH}$ , diode: body diode at $V_{GS} = 0\text{V}$ see Fig. E	-	16	-	ns
Rise time	$t_r$		-	11	-	
Turn-off delay time	$t_{d(off)}$		-	23	-	
Fall time	$t_f$		-	23	-	
Turn-on energy	$E_{on}$		-	33	-	
Turn-off energy	$E_{off}$		-	8	-	
Total switching energy	$E_{tot}$		-	41	-	


<sup>3</sup> The chip technology was characterized up to 200 kV/μs. The measured dV/dt was limited by measurement test setup and package. In applications, e.g. fly-back topology, the switching behavior highly depends on the circuitry (transformer, snubber...), the switching loss in the application will be different from the datasheet value.

## 4


## Electrical characteristic diagrams




**Figure 1 Safe operating area (SOA)**  
( $V_{GS} = 0/12\text{V}$ ,  $T_c = 25^\circ\text{C}$ ,  $T_j \leq 175^\circ\text{C}$ )




**Figure 2 Power dissipation as a function of case temperature limited by bond wire**  
( $P_{tot} = f(T_c)$ )




**Figure 3 Maximum DC drain to source current as a function of case temperature limited by bond wire**  
( $I_{DS} = f(T_c)$ )




**Figure 4 Typical transfer characteristic**  
( $I_{DS} = f(V_{GS})$ ,  $V_{DS} = 20\text{V}$ ,  $t_P = 20\mu\text{s}$ )




**Figure 5** Typical gate-source threshold voltage as a function of junction temperature  
( $V_{GS(th)} = f(T_{vj})$ ,  $I_{DS} = 1.1\text{mA}$ ,  $V_{GS} = V_{DS}$ )




**Figure 6** Typical on-resistance as a function of junction temperature  
( $R_{DS(on)} = f(T_{vj})$ ,  $I_{DS} = 1\text{A}$ )




**Figure 7** Typical output characteristic,  $V_{GS}$  as parameter  
( $I_{DS} = f(V_{DS})$ ,  $T_{vj}=25^{\circ}\text{C}$ ,  $t_P = 20\mu\text{s}$ )




**Figure 8** Typical output characteristic,  $V_{GS}$  as parameter  
( $I_{DS} = f(V_{DS})$ ,  $T_{vj}=175^{\circ}\text{C}$ ,  $t_P = 20\mu\text{s}$ )




**Figure 9** Typical capacitance as a function of drain-source voltage  
( $C = f(V_{DS})$ ,  $V_{GS} = 0V$ ,  $f = 1\text{MHz}$ )




**Figure 10** Typical gate charge  
( $V_{GS} = f(Q_G)$ ,  $I_{DS} = 1A$ ,  $V_{DS} = 1000V$ , turn-on pulse)



**Figure 11** Typical switching energy losses as a function of gate resistance  
( $E = f(R_{G,\text{ext}})$ ,  $V_{DD} = 1000V$ ,  $V_{GS} = 0V/12V$ ,  $I_D = 1A$ ,  $T_{vj} = 175^\circ\text{C}$ , ind. load, test circuit in Fig. E, diode: body diode at  $V_{GS} = 0V$ )




**Figure 12** Typical switching energy losses as a function of junction temperature  
( $E = f(T_{vj})$ ,  $V_{DD} = 1000V$ ,  $V_{GS} = 0V/12V$ ,  $R_{G,\text{ext}} = 22\Omega$ ,  $I_D = 1A$ , ind. load, test circuit in Fig. E, diode: body diode at  $V_{GS} = 0V$ )




**Figure 13** Typical switching energy losses as a function of drain-source current

( $E = f(I_{DS})$ ,  $V_{DD} = 1000\text{V}$ ,  $V_{GS} = 0\text{V}/12\text{V}$ ,  $R_{G,\text{ext}} = 22\Omega$ ,  $T_{vj} = 175^\circ\text{C}$ , ind. load, test circuit in Fig. E, diode: body diode at  $V_{GS} = 0\text{V}$ )



**Figure 14** Typical switching times as a function of gate resistor


( $t = f(R_{G,\text{ext}})$ ,  $V_{DD} = 1000\text{V}$ ,  $V_{GS} = 0\text{V}/12\text{V}$ ,  $I_D = 1\text{A}$ ,  $T_{vj} = 175^\circ\text{C}$ , ind. load, test circuit in Fig. E, diode: body diode at  $V_{GS} = 0\text{V}$ )



**Figure 15** Max. transient thermal resistance (MOSFET)

( $Z_{th(j-c,\max)} = f(t_p)$ , parameter  $D = t_p/T$ , thermal equivalent circuit in Fig. D)

## 5 Package drawing



**Figure 16** Package drawing

## Test conditions

## 6 Test conditions




Figure A. Definition of switching times




Figure C. Definition of diode switching characteristics




Figure B. Definition of switching losses




Figure D. Thermal equivalent circuit




Figure E. Dynamic test circuit

Parasitic inductance  $L_\sigma$ ,  
parasitic capacitor  $C_\sigma$ ,

Figure 17 Test conditions

**Revision history**

<b>Document version</b>	<b>Date of release</b>	<b>Description of changes</b>
2.1	2020-04-27	Final Datasheet
2.2	2020-12-11	Correction of circuit symbol on page 1
2.3	2021-04-12	Editorial changes

## **Trademarks**

All referenced product or service names and trademarks are the property of their respective owners.

## **Published by**

**Infineon Technologies AG**

**81726 München, Germany**

**© Infineon Technologies AG 2021.**

**All Rights Reserved.**

## **Important notice**

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics (“Beschaffenheitsgarantie”). With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office ([www.infineon.com](http://www.infineon.com)).

Please note that this product is not qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

## **Warnings**

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.