

# Half-Bridge Driver

#### **Features**

- Floating channel designed for bootstrap operation
- Fully operational to +600V
- Tolerant to negative transient voltage
- dV/dt immune
- Gate drive supply range from 10 to 20V
- · Under voltage lockout for both channels
- 3.3V, 5V and 15V input logic compatible
- Cross-conduction prevention logic
- Internally set dead-time (100ns)
- Output in phase with input
- Matched propagation delay for both channels
- Lower di/dt gate driver for better noise immunity


### **Product Summary**

V <sub>OFFSET</sub>	600V max.
I <sub>O+/-</sub>	60 mA / 130 mA
V <sub>OUT</sub>	10 – 20V
Delay Matching	50ns
Ton/off (typ.)	220 & 220 ns
Internal Dead time	100 ns

### Description

The IR25601 is a high voltage, high speed power MOSFET and IGBT driver with independent high and low side referenced output channels. Proprietary HVIC and latch immune CMOS technologies enable ruggedized monolithic construction. The logic input is compatible with standard CMOS or LSTTL output, down to 3.3V logic. The output driver features a high pulse current buffer stage designed for minimum driver cross-conduction. The floating channel can be used to drive an N-channel power MOSFET or IGBT in the high side configuration which operates up to 600 volts.

### **Package Options**




## **Ordering Information**

Danie Bart Namel au		Standar	d Pack	Orderable Deut Neumber
Base Part Number	Package Type	Form	Quantity	Orderable Part Number
IR25601SPBF	SO8N	Tube	95	IR25601SPBF
IR25601SPBF	SO8N	Tape and Reel	2500	IR25601STRPBF



# **Typical Connection Diagram**





### **Absolute Maximum Ratings**

Absolute maximum ratings indicate sustained limits beyond which damage to the device may occur. All voltage parameters are absolute voltages referenced to COM. The thermal resistance and power dissipation ratings are measured under board mounted and still air conditions.

Symbol	Definition	Min.	Max.	Units
$V_{B}$	High side floating supply absolute voltage	-0.3	625	
Vs	High side floating supply offset voltage	V <sub>B</sub> - 25	V <sub>B</sub> + 0.3	
V <sub>HO</sub>	High side floating output voltage	V <sub>S</sub> - 0.3	V <sub>B</sub> + 0.3	V
V <sub>C</sub> C	Low side and logic fixed supply voltage	-0.3	25	7 ·
$V_{LO}$	Low side output voltage	-0.3	V <sub>CC</sub> + 0.3	
V <sub>IN</sub>	Logic input voltage (HIN & LIN)	-0.3	V <sub>CC</sub> + 0.3	
dVs/dt	Allowable offset supply voltage transient	<del>-</del>	50	V/ns
$P_{D}$	Package power dissipation @ T <sub>A</sub> ≤ +25°C	_	0.625	W
Rth <sub>JA</sub>	Thermal resistance, junction to ambient	_	200	°C/W
TJ	Junction temperature	_	150	
T <sub>S</sub>	Storage temperature	-55	150	°C
TL	Lead temperature (soldering, 10 seconds)	_	300	

### **Recommended Operating Conditions**

For proper operation the device should be used within the recommended conditions. The  $V_S$  offset rating is tested with all supplies biased at 15V differential.

Symbol	Definition	Min.	Max.	Units
V <sub>B</sub>	High side floating supply absolute voltage	V <sub>S</sub> + 10	V <sub>S</sub> + 20	
Vs	High side floating supply offset voltage	+	600	
V <sub>HO</sub>	High side floating output voltage	Vs	V <sub>B</sub>	V
V <sub>CC</sub>	Low side and logic fixed supply voltage	10	20	]
V <sub>LO</sub>	Low side output voltage	0	V <sub>CC</sub>	
V <sub>IN</sub>	Logic input voltage (HIN, LIN)	0	V <sub>CC</sub>	
T <sub>A</sub>	Ambient temperature	-40	125	°C

<sup>+</sup> Logic operational for VS of -5 to +600V. Logic state held for VS of -5V to -VBS. (Please refer to Design Tip DT97-3 for more details).

www.irf.com © 2013 International Rectifier March 26, 2013



### **Dynamic Electrical Characteristics**

 $V_{BIAS}$  ( $V_{CC}$ ,  $V_{BS}$ ) = 15V, CL = 1000 pF and  $T_A$  = 25°C unless otherwise specified.

Symbol	Definition	Min.	Тур.	Max.	Units	Test Conditions
ton	Turn-on propagation delay	120	220	320		$V_S = 0V$
t <sub>off</sub>	Turn-off propagation delay	130	220	330		V <sub>S</sub> = 0Vor 600V
t <sub>r</sub>	Turn-on rise time	60	200	300	ns	
t <sub>f</sub>	Turn-off fall time	20	100	170		
DT	Dead time	80	100	190		
MT	Delay matching, HS & LS turn-on/off	_	_	50		

#### **Static Electrical Characteristics**

www.irf.com


 $V_{BIAS}$  ( $V_{CC}$ ,  $V_{BS}$ ) = 15V and  $T_A$  = 25°C unless otherwise specified. The  $V_{IN}$ ,  $V_{TH}$  and  $I_{IN}$  parameters are referenced to COM. The VO and IO parameters are referenced to COM and are applicable to the respective output leads: HO and LO.

Symbol	Definition	Min.	Тур.	Max.	Units	Test Conditions
V <sub>IH</sub>	Logic "1" input voltage	2.3	_	_		
$V_{IL}$	Logic "0" input voltage		_	0.8	V	
V <sub>OH</sub>	High level output voltage, V <sub>BIAS</sub> - V <sub>O</sub>		_	2.8	v	Io = 20mA
$V_{OL}$	Low level output voltage, VO		—	1.2		10 – 2011IA
I <sub>LK</sub>	Offset supply leakage current		_	50		$V_{B} = V_{S} = 600V$
$I_{QBS}$	Quiescent V <sub>BS</sub> supply current	20	60	150		$V_{IN}$ = 0V or 5V
I <sub>QCC</sub>	Quiescent V <sub>CC</sub> supply current	50	120	240	μA	$V_{IN} = 0V \text{ or } 5V$
I <sub>IN+</sub>	Logic "1" input bias current		5	40		V <sub>IN</sub> = 5V
$I_{IN-}$	Logic "0" input bias current	_	1.0	2.0		$V_{IN} = 0V$
V <sub>CCUV+</sub> V <sub>BSUV+</sub>	V <sub>CC</sub> and V <sub>BS</sub> supply undervoltage positive going threshold	8	8.9	9.8		
V <sub>CCUV</sub> - V <sub>BSUV</sub> -	V <sub>CC</sub> supply undervoltage negative going threshold	7.4	8.2	9	V	
V <sub>CCUVH</sub> V <sub>BSUVH</sub>	V <sub>CC</sub> supply undervoltage lockout hysteresis	0.3	0.7			
I <sub>O+</sub>	Output high short circuit pulsed current	60	_	_	mA	V <sub>O</sub> = 0V PW ≤ 10 μs
I <sub>O-</sub>	Output low short circuit pulsed current	130	_	_		V <sub>O</sub> = 15V PW ≤ 10 μs



# **Functional Block Diagram**

5 www.irf.com






## **Lead Definitions**

Symbol	Description
HIN	Logic input for high side gate driver output
LIN	Logic input for low side gate driver output
V <sub>B</sub>	High side floating supply
НО	High side gate drive output
VS	High side floating supply return
V <sub>C</sub> C	Low side supply voltage
LO	Low side gate drive output
COM	Low side return

# **Lead Assignments**



6 <u>www.irf.com</u> © 2013 International Rectifier March 26, 2013



## **Application Information and Additional Details**




Figure 1. Input/Output Functionality Diagram




Figure 2. Switching Time Waveforms





Figure 3. Internal Deadtime Timing




### **Package Details**

www.irf.com






# **Tape and Reel Details**



#### CARRIER TAPE DIMENSION FOR 8SOICN

	Metric		Imperial	
Code	Min	Max	Min	Max
Α	7.90	8.10	0.311	0.318
В	3.90	4.10	0.153	0.161
С	11.70	12.30	0.46	0.484
D	5.45	5.55	0.214	0.218
E	6.30	6.50	0.248	0.255
F	5.10	5.30	0.200	0.208
G	1.50	n/a	0.059	n/a
Н	1.50	1.60	0.059	0.062




REEL DIMENSIONS FOR 8SOICN

9 www.irf.com

	Me	etric	Imperial		
Code	Min	Max	Min	Max	
Α	329.60	330.25	12.976	13.001	
В	20.95	21.45	0.824	0.844	
С	12.80	13.20	0.503	0.519	
D	1.95	2.45	0.767	0.096	
E	98.00	102.00	3.858	4.015	
F	n/a	18.40	n/a	0.724	
G	14.50	17.10	0.570	0.673	
H	12.40	14.40	0.488	0.566	



## **Part Marking Information**



10 <u>www.irf.com</u> © 2013 International Rectifier March 26, 2013



#### Qualification Information<sup>†</sup>

Qualification Level	Industrial <sup>††</sup> (per JEDEC JESD 47)
	Comments: This family of ICs has passed JEDEC's
	Industrial qualification. IR's Consumer qualification level is
	granted by extension of the higher Industrial level.
Maistura Cansitivity Lavel	MSL2 <sup>†††</sup>
Moisture Sensitivity Level	(per IPC/JEDEC J-STD-020)
RoHS Compliant	Yes

- † Qualification standards can be found at International Rectifier's web site <a href="http://www.irf.com/">http://www.irf.com/</a>
- †† Higher qualification ratings may be available should the user have such requirements. Please contact your International Rectifier sales representative for further information.
- ††† Higher MSL ratings may be available for the specific package types listed here. Please contact your International Rectifier sales representative for further information.

The information provided in this document is believed to be accurate and reliable. However, International Rectifier assumes no responsibility for the consequences of the use of this information. International Rectifier assumes no responsibility for any infringement of patents or of other rights of third parties which may result from the use of this information. No license is granted by implication or otherwise under any patent or patent rights of International Rectifier. The specifications mentioned in this document are subject to change without notice. This document supersedes and replaces all information previously supplied.

For technical support, please contact IR's Technical Assistance Center http://www.irf.com/technical-info/

#### **WORLD HEADQUARTERS:**

233 Kansas St., El Segundo, California 90245 Tel: (310) 252-7105

www.irf.com © 2013 International Rectifier March 26, 2013