

μHVICTM

SOT-23 Single Low-Side Gate Driver IC

Features

- Wide VCC range (5 V to 20 V)
- CMOS Schmitt-triggered inputs
- Under voltage lockout
- 3.3 V logic compatible
- Additional OUT pin
- Output in phase with inputs
- Leadfree, RoHS compliant

Typical Applications

- General purpose gate driver
- Industrial applications
- Switched-mode power supplies


Product Summary

Topology	General Driver
IO+/- (typical)	1.5 A

Package Options



Typical Connection Diagram



Ordering Information

Base Part Number	Packago Typo	Standar	d Pack	Orderable Part Number	
Dase Part Number	Package Type	Form	Quantity	Orderable Part Number	
<u>IR44273L</u>	SOT23-5	Tape and Reel	3000	IR44273LTRPBF	



Table of Contents	Page
Typical Connection Diagram	1
Ordering Information	1
Description	3
Qualification Information	4
Absolute Maximum Ratings	5
Recommended Operating Conditions	5
Static Electrical Characteristics	6
Dynamic Electrical Characteristics	6
Functional Block Diagrams	7
Input/Output Pin Equivalent Circuit Diagram	8
Lead Definitions	9
Lead Assignments	9
Timing Diagrams	10
Package Details: SOT23-5	11
Package Details: SOT23-5, Tape and Reel	12
Part Marking Information	14



Description

The IR44273L is a low-voltage, wide VCC range, power MOSFET and IGBT non-inverting gate driver. Proprietary latch immune CMOS technologies enable ruggedized monolithic construction. The logic input is compatible with standard CMOS or LSTTL output. The output driver features a current buffer stage. The design also includes an additional gate drive OUT pin for flexible PCB layout.



Qualification Information[†]

		Industrial ^{††}				
Qualification Level		Comments: This family of ICs has passed JEDEC's Industrial qualification. IR's Consumer qualification level is				
		granted by extension of the higher Industrial level.				
Moisture Sensitivity Level		MSL1 ^{†††} 260°C				
Wioisture Serisitivi	ity Level	(per IPC/JEDEC J-STD-020)				
	Machine Model	Class B				
ESD	Machine Model	(per JEDEC standard JESD22-A115)				
E3D	Human Bady Madal	Class 2				
	Human Body Model	(per EIA/JEDEC standard EIA/JESD22-A114)				
IC Latch-Up Test		Class 1 Level A				
		(per JESD78)				
RoHS Compliant		Yes				

- Qualification standards can be found at International Rectifier's web site http://www.irf.com/
- Higher qualification ratings may be available should the user have such requirements. Please contact your †† International Rectifier sales representative for further information.
- Higher MSL ratings may be available for the specific package types listed here. Please contact your ††† International Rectifier sales representative for further information.

www.infineon.com/gdlowside



Absolute Maximum Ratings

Absolute maximum ratings indicate sustained limits beyond which damage to the device may occur. The device may not function or not be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. All voltage parameters are absolute voltages referenced to COM. The thermal resistance and power dissipation ratings are measured under board mounted and still air conditions.

Symbol	Definition	Min	Max	Units		
Vcc	Fixed supply voltage	-0.3	20			
Vo	Output voltage	-0.3	V _{CC} + 0.3	V		
Vin	Logic input voltage	-0.3	V _{CC} + 0.3			
Rth _{JA}	Thermal resistance, junction to ambient	_	151	°C/W		
TJ	Junction temperature	_	150			
Ts	Storage temperature	-55	150	°C		
TL	Lead temperature (soldering, 10 seconds)	_	300			

Recommended Operating Conditions

For proper operation, the device should be used within the recommended conditions. All voltage parameters are absolute voltages referenced to COM unless otherwise stated in the table.

Symbol	Definition		Max	Units
Vcc	Fixed supply voltage	5.0	18	
Vo	Output voltage	0	Vcc	V
V _{IN}	Logic input voltage (IN and EN)	0	Vcc	
T _A	Ambient temperature	-40	125	°C



Static Electrical Characteristics

 V_{CC} = 15V, T_A = 25°C unless otherwise specified. The V_{IN} , and I_{IN} parameters are referenced to COM and are applicable to input leads: IN. The Vo and Io parameters are referenced to COM and are applicable to the output leads: OUT.

Symbol	Definition	Min	Тур	Max	Units	Test Conditions
Vccuv+	Vcc supply UVLO positive going threshold	_	_	5.0		
Vccuv-	Vcc supply UVLO negative going threshold	4.15				
Vcc uvh	Vcc supply UVLO hysteresis	_	0.3			
VCLAMP	Vcc Zener clamp voltage	_	21.4	_	V	Icc=5mA
VIL	Logic "0" input voltage (OUT = LO)	_	_	0.6	V	
V _{IH}	Logic "1" input voltage (OUT = HI)	2.7	_	_		
Vон	High level output voltage, V _{BIAS} -V _O		_	2.0		$I_0 = 0.1 \text{mA}$
V _{OL}	Low level output voltage, Vo	_	_	0.12		I _O = 20mA
I _{IN+}	Logic "1" input bias current		5	15		$V_{IN} = 5V$
I _{IN-}	Logic "0" input bias current	-30	-10	_	μΑ	V _{IN} = 0V
Iqcc	Quiescent V _{CC} supply current			400		V _{IN} = 0V or 5V
I _{O+}	Output high short circuit pulsed current		1.7	_	_	V _O = 0V, V _{IN} = 5V
l ₀₋	Output low short circuit pulsed current		1.5	_	Α	V _O = 15V, V _{IN} = 0V


Dynamic Electrical Characteristics

 V_{CC} = 15V, T_A = 25°C, and C_L = 1000pF unless otherwise specified.

Symbol	Definition	Min	Тур	Max	Units	Test Conditions
ton	Turn-on propagation delay	_	50	_		
$t_{ m off}$	Turn-off propagation delay	_	50	_	20	Figure 2
t _r	Turn-on rise time	_	10	_	ns	Figure 2
t _f	Turn-off fall time	_	10	_		




Functional Block Diagram



www.infineon.com/gdlowside



Input/Output Pin Equivalent Circuit Diagrams






Lead Definitions

PIN	Symbol	Description
1	IN	Logic input for gate driver output (OUT), in phase
2	СОМ	Ground
3	OUT	Gate drive output
4	OUT	Gate drive output
5	VCC	Supply Voltage

Lead Assignments



Timing Diagrams




Figure 1: Input/output Timing Diagram






Figure 2: Switching Time Waveform Definitions

Package Details, SOT23-5







SYMBOL	MIN	MAX			
Α	0.90	1.45			
A1	0.00	0.15			
A2	0.90	1.30			
В	0.25	0.50			
С	0.09	0.20			
D	2.80	3.00			
Е	2.60	3.00			
E1	1.50	1.75			
е	0.95	REF			
e1	1.90 REF				
L	0.35	0.55			
α	08	108			

NOTE: ALL MEASUREMENTS ARE IN MILLIMETERS.




Package details: SOT23-5, Tape and Reel








Package details: SOT23-5, Tape and Reel









Part Marking Information

Top Marking



Bottom Marking



The information provided in this document is believed to be accurate and reliable. However, International Rectifier assumes no responsibility for the consequences of the use of this information. International Rectifier assumes no responsibility for any infringement of patents or of other rights of third parties which may result from the use of this information. No license is granted by implication or otherwise under any patent or patent rights of International Rectifier. The specifications mentioned in this document are subject to change without notice. This document supersedes and replaces all information previously supplied.

> For technical support, please contact IR's Technical Assistance Center http://www.irf.com/technical-info/

WORLD HEADQUARTERS:

101N Sepulveda Blvd., El Segundo, California 90245 Tel: (310) 252-7105

www.infineon.com/gdlowside