Application

- Half-bridge and full-bridge topologies
- Synchronous rectifier applications
- Resonant mode power supplies
- DC/DC converters
- DC/AC Inverters



V_{DSS}	40V
$R_{DS(on)\ typ.}$	0.95mΩ
$R_{DS(on)\ max}$	1.25mΩ
I_D	265A

Benefits

- Improved Gate, Avalanche and Dynamic dV/dt Ruggedness
- Fully Characterized Capacitance and Avalanche SOA
- Enhanced body diode dV/dt and dI/dt Capability
- Lead-Free, RoHS Compliant

Base part number	Package Type	Standard Pack		Orderable Part Number
		Form	Quantity	
IRFH7084PbF	PQFN 5mm x 6mm	Tape and Reel	4000	IRFH7084TRPbF



Fig 1. Typical On-Resistance vs. Gate Voltage



Fig 2. Maximum Drain Current vs. Case Temperature

Absolute Maximium Rating

Symbol	Parameter	Max.	Units
I_D @ T_A = 25°C	Continuous Drain Current, V_{GS} @ 10V	40	A
I_D @ $T_{C(Bottom)}$ = 25°C	Continuous Drain Current, V_{GS} @ 10V①	265	
I_D @ $T_{C(Bottom)}$ = 100°C	Continuous Drain Current, V_{GS} @ 10V①	170	
I_{DM}	Pulsed Drain Current ②	1060	A
	Linear Derating Factor	1.25	W/°C
P_D @T_C = 25°C	Max Power Dissipation	156	
V_{GS}	Gate-to-Source Voltage	± 20	V
T_J T_{STG}	Operating Junction and Storage Temperature Range	-55 to + 150	°C

Avalanche Characteristics

$E_{AS\ (Thermally\ limited)}$	Single Pulse Avalanche Energy ③	185	mJ
$E_{AS\ (Thermally\ limited)}$	Single Pulse Avalanche Energy ⑨	431	
I_{AR}	Avalanche Current ②	See Fig 14, 15, 23a, 23b	A
E_{AR}	Repetitive Avalanche Energy ②		mJ

Thermal Resistance

	Parameter	Typ.	Max.	Units
$R_{\theta JC}$ (Bottom)	Junction-to-Case ⑧	0.5	0.8	°C/W
$R_{\theta JC}$ (Top)	Junction-to-Case ⑧	–––	21	
$R_{\theta JA}$	Junction-to-Ambient ⑩	–––	35	
$R_{\theta JA}$ (<10s)	Junction-to-Ambient	–––	20	

Static @ T_J = 25°C (unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Units	Conditions
$V_{(BR)DSS}$	Drain-to-Source Breakdown Voltage	40	–––	–––	V	V_{GS} = 0V, I_D = 250µA
$\Delta V_{(BR)DSS}/\Delta T_J$	Breakdown Voltage Temp. Coefficient	–––	0.034	–––	V/°C	Reference to 25°C, I_D = 1mA
$R_{DS(on)}$	Static Drain-to-Source On-Resistance	–––	0.95	1.25	mΩ	V_{GS} = 10V, I_D = 100A
$V_{GS(th)}$	Gate Threshold Voltage	2.2	–––	3.9	V	V_{DS} = V_{GS}, I_D = 150µA
I_{DSS}	Drain-to-Source Leakage Current	–––	–––	1.0	µA	V_{DS} =40 V, V_{GS} = 0V
		–––	–––	150		V_{DS} =40V,V_{GS} = 0V,T_J =125°C
I_{GSS}	Gate-to-Source Forward Leakage	–––	–––	100	nA	V_{GS} = 20V
	Gate-to-Source Reverse Leakage	–––	–––	-100		V_{GS} = -20V
R_G	Gate Resistance	–––	1.4	–––	Ω	

Notes:

① Rating refers to the product only with datasheet specified absolute maximum values, maintaining case temperature at 25°C. For higher case temperature please refer to Diagram 2. De-rating will be required based on the actual environmental conditions.

② Repetitive rating; pulse width limited by max. junction temperature.

③ Limited by T_{Jmax}, starting T_J = 25°C, L = 0.037mH, R_G = 50Ω, I_{AS} = 100A, V_{GS} =10V.

④ $I_{SD} \leq$ 100A, di/dt ≤ 994A/µs, $V_{DD} \leq V_{(BR)DSS}$, $T_J \leq$ 150°C.

⑤ Pulse width ≤ 400µs; duty cycle ≤ 2%.

⑥ C_{oss} eff. (TR) is a fixed capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS}.

⑦ C_{oss} eff. (ER) is a fixed capacitance that gives the same energy as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS}.

⑧ R_θ is measured at T_J approximately 90°C.

⑨ Limited by T_{Jmax}, starting T_J = 25°C, L = 1mH, R_G = 50Ω, I_{AS} = 29A, V_{GS} =10V.

⑩ When mounted on 1 inch square PCB (FR-4). Please refer to AN-994 for more details:
http://www.infineon.com/technical-info/appnotes/an-994.pdf

Dynamic Electrical Characteristics @ T_J = 25°C (unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Units	Conditions
gfs	Forward Transconductance	120	—	—	S	V_{DS} = 10V, I_D =100A
Q_g	Total Gate Charge	—	127	190	nC	I_D = 100A
Q_{gs}	Gate-to-Source Charge	—	35	—		V_{DS} = 20V
Q_{gd}	Gate-to-Drain Charge	—	41	—		V_{GS} = 10V
Q_{sync}	Total Gate Charge Sync. (Qg– Qgd)	—	195	—		
$t_{d(on)}$	Turn-On Delay Time	—	16	—	ns	V_{DD} = 20V
t_r	Rise Time	—	31	—		I_D = 30A
$t_{d(off)}$	Turn-Off Delay Time	—	64	—		R_G= 2.7Ω
t_f	Fall Time	—	34	—		V_{GS} = 10V⑤
C_{iss}	Input Capacitance	—	6560	—	pF	V_{GS} = 0V
C_{oss}	Output Capacitance	—	940	—		V_{DS} = 25V
C_{rss}	Reverse Transfer Capacitance	—	650	—		f = 1.0MHz, See Fig.5
$C_{oss\ eff.(ER)}$	Effective Output Capacitance (Energy Related)	—	1120	—		V_{GS} = 0V, VDS = 0V to 32V⑦ See Fig.11
$C_{oss\ eff.(TR)}$	Output Capacitance (Time Related)	—	1300	—		V_{GS} = 0V, VDS = 0V to 32V⑥

Diode Characteristics

Symbol	Parameter	Min.	Typ.	Max.	Units	Conditions
I_S	Continuous Source Current (Body Diode)	—	—	120	A	MOSFET symbol showing the integral reverse p-n junction diode. 
I_{SM}	Pulsed Source Current (Body Diode) ②	—	—	1060		
V_{SD}	Diode Forward Voltage⑤	—	—	1.3	V	T_J = 25°C,I_S = 100A,V_{GS} = 0V
dv/dt	Peak Diode Recovery dv/dt ④	—	4.5	—	V/ns	T_J = 150°C,I_S =100A,V_{DS} = 40V
t_{rr}	Reverse Recovery Time	—	36	—	ns	T_J = 25°C V_{DD} = 34V
		—	37	—		T_J = 125°C I_F = 100A,
Q_{rr}	Reverse Recovery Charge	—	38	—	nC	T_J = 25°C di/dt = 100A/µs ⑤
		—	40	—		T_J = 125°C
I_{RRM}	Reverse Recovery Current	—	1.7	—	A	T_J = 25°C



Fig 3. Typical Output Characteristics



Fig 4. Typical Output Characteristics



Fig 5. Typical Transfer Characteristics



Fig 6. Normalized On-Resistance vs. Temperature



Fig 7. Typical Capacitance vs. Drain-to-Source Voltage



Fig 8. Typical Gate Charge vs. Gate-to-Source Voltage



Fig 9. Typical Source-Drain Diode Forward Voltage



Fig 10. Maximum Safe Operating Area



Fig 11. Drain-to–Source Breakdown Voltage



Fig 12. Typical C_{oss} Stored Energy



Fig 13. Typical On-Resistance vs. Drain Current



Fig 14. Maximum Effective Transient Thermal Impedance, Junction-to-Case



Fig 15. Typical Avalanche Current vs. Pulse width



Fig 16. Maximum Avalanche Energy vs. Temperature

Notes on Repetitive Avalanche Curves , Figures 14, 15:
(For further info, see AN-1005 at www.infineon.com)

1. Avalanche failures assumption:
   Purely a thermal phenomenon and failure occurs at a temperature far in excess of T_{jmax}. This is validated for every part type.
2. Safe operation in Avalanche is allowed as long asT_{jmax} is not exceeded.
3. Equation below based on circuit and waveforms shown in Figures 22a, 22b.
4. $P_{D\ (ave)}$ = Average power dissipation per single avalanche pulse.
5. BV = Rated breakdown voltage (1.3 factor accounts for voltage increase during avalanche).
6. I_{av} = Allowable avalanche current.
7. ΔT = Allowable rise in junction temperature, not to exceed T_{jmax} (assumed as 25°C in Figure 14, 15).
   t_{av} = Average time in avalanche.
   D = Duty cycle in avalanche = tav ·f
   $Z_{thJC}(D, t_{av})$ = Transient thermal resistance, see Figures 13)
   PD (ave) = 1/2 (1.3·BV·I_{av}) = ΔT/ Z_{thJC}
   I_{av} = 2ΔT/ [1.3·BV·Z_{th}]
   $E_{AS\ (AR)}$ = $P_{D\ (ave)}$·t_{av}



Fig 17. Threshold Voltage vs. Temperature



Fig 18. Typical Recovery Current vs. dif/dt



Fig 19. Typical Recovery Current vs. dif/dt



Fig 20. Typical Stored Charge vs. dif/dt



Fig 21. Typical Stored Charge vs. dif/dt



Fig 22. Peak Diode Recovery dv/dt Test Circuit for N-Channel HEXFET® Power MOSFETs



Fig 23a. Unclamped Inductive Test Circuit



Fig 23b. Unclamped Inductive Waveforms



Fig 24a. Switching Time Test Circuit



Fig 24b. Switching Time Waveforms



Fig 25a. Gate Charge Test Circuit



Fig 25b. Gate Charge Waveform

PQFN 5x6 Outline "B" Package Details



DIM / SYMBOL	MILLIMITERS		INCH	
	MIN	MAX	MIN	MAX
A	0.800	0.900	0.0315	0.0543
A1	0.000	0.050	0.0000	0.0020
A3	0.200 REF		0.0079 REF	
b	0.350	0.470	0.0138	0.0185
b1	0.025	0.125	0.0010	0.0049
b2	0.210	0.410	0.0083	0.0161
b3	0.150	0.450	0.0059	0.0177
D	5.000 BSC		0.1969 BSC	
D1	4.750 BSC		0.1870 BSC	
D2	4.100	4.300	0.1614	0.1693
E	6.000 BSC		0.2362 BSC	
E1	5.750 BSC		0.2264 BSC	
E2	3.380	3.780	0.1331	0.1488
e	1.270 REF		0.0500 REF	
e1	2.800 REF		0.1102 REF	
K	1.200	1.420	0.0472	0.0559
L	0.710	0.900	0.0280	0.0354
P	0°	12°	0°	12°
R	0.200 REF		0.0079 REF	
R2	0.150	0.200	0.0059	0.0079

Note:

1. Dimensions and toleranceing confirm to ASME Y14.5M–1994
2. Dimension L represents terminal full back from package edge up to 0.1mm is acceptable
3. Coplanarity applies to the expose Heat Slug as well as the terminal
4. Radius on terminal is Optional

PQFN 5x6 Outline "G" Package Details



DIM / SYMBOL	MILLIMETERS		INCH	
	MIN.	MAX.	MIN.	MAX.
A	0.950	1.050	0.0374	0.0413
A1	0.000	0.050	0.0000	0.0020
A3	0.254 REF		0.0100 REF	
b	0.310	0.510	0.0122	0.0201
b1	0.025	0.125	0.0010	0.0049
b2	0.210	0.410	0.0083	0.0161
b3	0.180	0.450	0.0071	0.0177
D	5.150 BSC		0.2028 BSC	
D1	5.000 BSC		0.1969 BSC	
D2	3.700	3.900	0.1457	0.1535
E	6.150 BSC		0.2421 BSC	
E1	6.000 BSC		0.2362 BSC	
E2	3.560	3.760	0.1402	0.1488
E3	2.270	2.470	0.0894	0.0972
e	1.27 REF		0.050 REF	
K	0.830	1.400	0.0327	0.0551
L	0.510	0.710	0.0201	0.0280
L1	0.510	0.710	0.0201	0.0280
P	10 deg	12 deg	0 deg	12 deg

Note:

1. Dimensions and toleranceing confirm to ASME Y14.5M–1994
2. Dimension L represents terminal full back from package edge up to 0.1mm is acceptable
3. Coplanarity applies to the expose Heat Slug as well as the terminal
4. Radius on terminal is Optional

For more information on board mounting, including footprint and stencil recommendation, please refer to application note AN-1136: http://www.infineon.com/technical-info/appnotes/an-1136.pdf
For more information on package inspection techniques, please refer to application note AN-1154: http://www.infineon.com/technical-info/appnotes/an-1154.pdf

Note: For the most current drawing please refer to IR website at http://www.infineon.com/package/

PQFN 5x6 Part Marking



PQFN 5x6 Tape and Reel



CODE	DESCRIPTION
Ao	Dimension design to accommodate the component width
Bo	Dimension design to accommodate the component lenght
Ko	Dimension design to accommodate the component thickness
W	Overall width of the carrier tape
P_1	Pitch between successive cavity centers



Note: All dimension are nominal

Package Type	Reel Diameter (Inch)	QTY	Reel Width W1 (mm)	Ao (mm)	Bo (mm)	Ko (mm)	P1 (mm)	W (mm)	Pin 1 Quadrant
5 X 6 PQFN	13	4000	12.4	6.300	5.300	1.20	8.00	12	Q1

Note: For the most current drawing please refer to IR website at http://www.infineon.com/package/

Qualification information†

Qualification level	Industrial†† (per JEDEC JESD47F †† guidelines)	
Moisture Sensitivity Level	PQFN 5mmx 6mm	MSL1 (per JEDEC J-STD-020D††)
RoHS compliant	Yes	

† Qualification standards can be found at International Rectifier's web site: http://www.infineon.com/product-info/reliability/

†† Applicable version of JEDEC standard at the time of product release.

Revision History

Date	Rev.	Comments
10/16/2014	2.1	• Add Pd at tc=25C on Absolute Max Rating table on page 2
03/05/2015	2.2	• Updated $E_{AS\ (L=1mH)}$ = 431mJ on page 2 • Updated note 8 "Limited by T_{Jmax}, starting T_J = 25°C, L = 1mH, R_G = 50Ω, I_{AS} = 29A, V_{GS} =10V" on page 2
03/19/2015	2.3	• Updated package outline on page 9.
01/24/2017	2.4	• Changed datasheet with Infineon logo - all pages • Added package outline for "option G" on page 9. • Added disclaimer on last page
4/14/2020	2.5	• Updated datasheet based on IFX template. • Updated Datasheet based on new current rating and application note :App-AN_1912_PL51_2001_180356

Trademarks
All referenced product or service names and trademarks are the property of their respective owners.

We Listen to Your Comments
Any information within this document that you feel is wrong, unclear or missing at all? Your feedback will help us to continuously improve the quality of this document. Please send your proposal (including a reference to this document) to:
erratum@infineon.com

Published by
Infineon Technologies AG
81726 München, Germany
© 2020 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer
The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics (“Beschaffenheitsgarantie”) .

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.
In addition, any information given in this document is subject to customer’s compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer’s products and any use of the product of Infineon Technologies in customer’s applications.
The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer’s technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Information
For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (www.infineon.com).

Warnings
Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.
The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.