PD - 94909A

International
IOR Rectifier


IRG4BC20UDPbF

INSULATED GATE BIPOLAR TRANSISTOR WITH ULTRAFAST SOFT RECOVERY DIODE

UltraFast CoPack IGBT

Features

- UltraFast: optimized for high operating frequencies 8-40 kHz in hard switching, >200 kHz in resonant mode
- Generation 4 IGBT design provides tighter parameter distribution and higher efficiency than Generation 3
- IGBT co-packaged with HEXFRED® ultrafast, ultra-soft-recovery anti-parallel diodes for use in bridge configurations
- Industry standard TO-220AB package
- Lead-Free



n-channel

V_{CES} = 600V

$V_{CE(on)\ typ.}$ = 1.85V

@V_{GE} = 15V, I_C = 6.5A

Benefits

- Generation -4 IGBTs offer highest efficiencies available
- IGBTs optimized for specific application conditions
- HEXFRED diodes optimized for performance with IGBTs. Minimized recovery characteristics require less/no snubbing
- Designed to be a "drop-in" replacement for equivalent industry-standard Generation 3 IR IGBTs


TO-220AB

Absolute Maximum Ratings

	Parameter	Max.	Units
V_{CES}	Collector-to-Emitter Voltage	600	V
I_C @ T_C = 25°C	Continuous Collector Current	13	A
I_C @ T_C = 100°C	Continuous Collector Current	6.5	
I_{CM}	Pulsed Collector Current ①	52	
I_{LM}	Clamped Inductive Load Current ②	52	
I_F @ T_C = 100°C	Diode Continuous Forward Current	7.0	
I_{FM}	Diode Maximum Forward Current	52	
V_{GE}	Gate-to-Emitter Voltage	± 20	V
P_D @ T_C = 25°C	Maximum Power Dissipation	60	W
P_D @ T_C = 100°C	Maximum Power Dissipation	24	
T_J	Operating Junction and	-55 to +150	°C
T_{STG}	Storage Temperature Range		
	Soldering Temperature, for 10 sec.	300 (0.063 in. (1.6mm) from case)	
	Mounting Torque, 6-32 or M3 Screw.	10 lbf•in (1.1 N•m)	

Thermal Resistance

	Parameter	Min.	Typ.	Max.	Units
$R_{\theta JC}$	Junction-to-Case - IGBT	------	------	2.1	°C/W
$R_{\theta JC}$	Junction-to-Case - Diode	------	------	3.5	
$R_{\theta CS}$	Case-to-Sink, flat, greased surface	------	0.50	------	
$R_{\theta JA}$	Junction-to-Ambient, typical socket mount	-----	-----	80	
Wt	Weight	------	2 (0.07)	------	g (oz)

01/22/10

Electrical Characteristics @ T_J = 25°C (unless otherwise specified)

	Parameter	Min.	Typ.	Max.	Units	Conditions
$V_{(BR)CES}$	Collector-to-Emitter Breakdown Voltage③	600	----	----	V	V_{GE} = 0V, I_C = 250µA
$\Delta V_{(BR)CES}/\Delta T_J$	Temperature Coeff. of Breakdown Voltage	----	0.69	----	V/°C	V_{GE} = 0V, I_C = 1.0mA
$V_{CE(on)}$	Collector-to-Emitter Saturation Voltage	----	1.85	2.1	V	I_C = 6.5A V_{GE} = 15V
		----	2.27	----		I_C = 13A See Fig. 2, 5
		----	1.87	----		I_C = 6.5A, T_J = 150°C
$V_{GE(th)}$	Gate Threshold Voltage	3.0	----	6.0		V_{CE} = V_{GE}, I_C = 250µA
$\Delta V_{GE(th)}/\Delta T_J$	Temperature Coeff. of Threshold Voltage	----	-11	----	mV/°C	V_{CE} = V_{GE}, I_C = 250µA
g_{fe}	Forward Transconductance ④	1.4	4.3	----	S	V_{CE} = 100V, I_C = 6.5A
I_{CES}	Zero Gate Voltage Collector Current	----	----	250	µA	V_{GE} = 0V, V_{CE} = 600V
		----	----	1700		V_{GE} = 0V, V_{CE} = 600V, T_J = 150°C
V_{FM}	Diode Forward Voltage Drop	----	1.4	1.7	V	I_C = 8.0A See Fig. 13
		----	1.3	1.6		I_C = 8.0A, T_J = 150°C
I_{GES}	Gate-to-Emitter Leakage Current	----	----	±100	nA	V_{GE} = ±20V

Switching Characteristics @ T_J = 25°C (unless otherwise specified)

	Parameter	Min.	Typ.	Max.	Units	Conditions
Q_g	Total Gate Charge (turn-on)	----	27	41	nC	I_C = 6.5A
Qge	Gate - Emitter Charge (turn-on)	----	4.5	6.8		V_{CC} = 400V See Fig. 8
Q_{gc}	Gate - Collector Charge (turn-on)	----	10	16		V_{GE} = 15V
$t_{d(on)}$	Turn-On Delay Time	----	39	----	ns	T_J = 25°C
t_r	Rise Time	----	15	----		I_C = 6.5A, V_{CC} = 480V
$t_{d(off)}$	Turn-Off Delay Time	----	93	140		V_{GE} = 15V, R_G = 50Ω
t_f	Fall Time	----	110	170		Energy losses include "tail" and
E_{on}	Turn-On Switching Loss	----	0.16	----	mJ	diode reverse recovery.
E_{off}	Turn-Off Switching Loss	----	0.13	----		See Fig. 9, 10, 11, 18
E_{ts}	Total Switching Loss	----	0.29	0.3		
$t_{d(on)}$	Turn-On Delay Time	----	38	----	ns	T_J = 150°C, See Fig. 9, 10, 11, 18
t_r	Rise Time	----	17	----		I_C = 6.5A, V_{CC} = 480V
$t_{d(off)}$	Turn-Off Delay Time	----	100	----		V_{GE} = 15V, R_G = 50Ω
t_f	Fall Time	----	220	----		Energy losses include "tail" and
E_{ts}	Total Switching Loss	----	0.49	----	mJ	diode reverse recovery.
L_E	Internal Emitter Inductance	----	7.5	----	nH	Measured 5mm from package
C_{ies}	Input Capacitance	----	530	----	pF	V_{GE} = 0V
C_{oes}	Output Capacitance	----	39	----		V_{CC} = 30V See Fig. 7
C_{res}	Reverse Transfer Capacitance	----	7.4	----		f = 1.0MHz
t_{rr}	Diode Reverse Recovery Time	----	37	55	ns	T_J = 25°C See Fig.
		----	55	90		T_J = 125°C 14 I_F = 8.0A
I_{rr}	Diode Peak Reverse Recovery Current	----	3.5	5.0	A	T_J = 25°C See Fig.
		----	4.5	8.0		T_J = 125°C 15 V_R = 200V
Q_{rr}	Diode Reverse Recovery Charge	----	65	138	nC	T_J = 25°C See Fig.
		----	124	360		T_J = 125°C 16 di/dt 200A/µs
$di_{(rec)M}/dt$	Diode Peak Rate of Fall of Recovery	----	240	----	A/µs	T_J = 25°C See Fig.
	During t_b	----	210	----		T_J = 125°C 17




Fig. 1 - Typical Load Current vs. Frequency
(Load Current = I_{RMS} of fundamental)




Fig. 2 - Typical Output Characteristics




Fig. 3 - Typical Transfer Characteristics




Fig. 4 - Maximum Collector Current vs. Case Temperature




Fig. 5 - Typical Collector-to-Emitter Voltage vs. Junction Temperature




Fig. 6 - Maximum IGBT Effective Transient Thermal Impedance, Junction-to-Case




Fig. 7 - Typical Capacitance vs. Collector-to-Emitter Voltage




Fig. 8 - Typical Gate Charge vs. Gate-to-Emitter Voltage




Fig. 9 - Typical Switching Losses vs. Gate Resistance




Fig. 10 - Typical Switching Losses vs. Junction Temperature




Fig. 11 - Typical Switching Losses vs. Collector-to-Emitter Current




Fig. 12 - Turn-Off SOA




Fig. 13 - Maximum Forward Voltage Drop vs. Instantaneous Forward Current




Fig. 14 - Typical Reverse Recovery vs. di_f/dt




Fig. 15 - Typical Recovery Current vs. di_f/dt




Fig. 16 - Typical Stored Charge vs. di_f/dt




Fig. 17 - Typical $di_{(rec)M}/dt$ vs. di_f/dt




Fig. 18a - Test Circuit for Measurement of I_{LM}, E_{on}, $E_{off(diode)}$, t_{rr}, Q_{rr}, I_{rr}, $t_{d(on)}$, t_r, $t_{d(off)}$, t_f




Fig. 18b - Test Waveforms for Circuit of Fig. 18a, Defining E_{off}, $t_{d(off)}$, t_f




Fig. 18c - Test Waveforms for Circuit of Fig. 18a, Defining E_{on}, $t_{d(on)}$, t_r




Fig. 18d - Test Waveforms for Circuit of Fig. 18a, Defining E_{rec}, t_{rr}, Q_{rr}, I_{rr}




Figure 18e. Macro Waveforms for Figure 18a's Test Circuit





Figure 19. Clamped Inductive Load Test Circuit



Pulsed Collector Current
Test Circuit

Figure 20. Pulsed Collector Current
Test Circuit

Notes:


① Repetitive rating: V_{GE}=20V; pulse width limited by maximum junction temperature (figure 20)


② V_{CC}=80%(V_{CES}), V_{GE}=20V, L=10µH, R_G = 50Ω (figure 19)

③ Pulse width ≤ 80µs; duty factor ≤ 0.1%.

④ Pulse width 5.0µs, single shot.

TO-220AB Package Outline (Dimensions are shown in millimeters (inches))






SYMBOL	DIMENSIONS				
	MILLIMETERS		INCHES		NOTES
	MIN.	MAX.	MIN.	MAX.	
A	3.56	4.83	.140	.190	
A1	0.51	1.40	.020	.055	
A2	2.03	2.92	.080	.115	
b	0.38	1.01	.015	.040	
b1	0.38	0.97	.015	.038	5
b2	1.14	1.78	.045	.070	
b3	1.14	1.73	.045	.068	5
c	0.36	0.61	.014	.024	
c1	0.36	0.56	.014	.022	5
D	14.22	16.51	.560	.650	4
D1	8.38	9.02	.330	.355	
D2	11.68	12.88	.460	.507	7
E	9.65	10.67	.380	.420	4,7
E1	6.86	8.89	.270	.350	7
E2	-	0.76	-	.030	8
e	2.54 BSC		.100 BSC		
e1	5.08 BSC		.200 BSC		
H1	5.84	6.86	.230	.270	7,8
L	12.70	14.73	.500	.580	
L1	3.56	4.06	.140	.160	3
øP	3.54	4.08	1.39	.161	
Q	2.54	3.42	.100	.135	

TO-220AB Part Marking Information

EXAMPLE: THIS IS AN IRF1010
LOT CODE 1789
ASSEMBLED ON WW 19, 1997
IN THE ASSEMBLY LINE 'C'

Note: "P" in assembly line position indicates "Lead-Free"



Note: For the most current drawing please refer to IR website at http://www.irf.com/package/

Data and specifications subject to change without notice.

International
IOR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7903
Visit us at www.irf.com for sales contact information.01/2010