

RADIATION HARDENED POWER MOSFET SURFACE MOUNT (SupIR-SMD)

Product Summary

Part Number	Number Radiation Level		ID	QPL Part Number		
IRHNS597160	100 kRads(Si)	0.049Ω	-47A	JANSR2N7550U2A		
IRHNS593160	300 kRads(Si)	0.049Ω	-47A	JANSF2N7550U2A		

Description

IR HiRel R5 technology provides high performance power MOSFETs for space applications. These devices have been characterized for Single Event Effects (SEE) with useful performance up to an LET of 80 (MeV/(mg/cm²)). The combination of low RDS(on) and low gate charge reduces the power losses in switching applications such as DC to DC converters and motor control. These devices retain all of the well established advantages of MOSFETs such as voltage control, fast switching, and temperature stability of electrical parameters.

Features

- Single Event Effect (SEE) Hardened
- Ultra Low RDS(on) •
- Low Total Gate Charge
- Simple Drive Requirements
- Hermetically Sealed
- Ceramic Package
- Light Weight
- Surface Mount
- ESD Rating: Class 3A per MIL-STD-750, Method 1020

Absolute	e Maximum	Ratings

Absolute maximum Ratings Pre-in					
Symbol	Parameter	Value	Units		
I _{D1} @ V _{GS} = -12V, T _C = 25°C	Continuous Drain Current	-47			
I _{D2} @ V _{GS} = -12V, T _C = 100°C	Continuous Drain Current	-30	А		
I _{DM} @T _C = 25°C	Pulsed Drain Current ①	-188			
P _D @T _C = 25°C	Maximum Power Dissipation	250	W		
	Linear Derating Factor	2.0	W/°C		
V _{GS}	Gate-to-Source Voltage	±20	V		
E _{AS}	Single Pulse Avalanche Energy ②	400	mJ		
I _{AR}	Avalanche Current ①	-47	А		
E _{AR}	Repetitive Avalanche Energy ${\mathbb O}$	25	mJ		
dv/dt	Peak Diode Recovery dv/dt 3	-10	V/ns		
TJ	Operating Junction and	-55 to + 150			
T _{STG}	Storage Temperature Range	-55 10 + 150	°C		
	Lead Temperature	300 (for 5s)			
	Weight	3.3 (Typical)	g		

For Footnotes, refer to the page 2.

IRHNS597160 JANSR2N7550U2A

PD-97905C

100V, P-CHANNEL REF: MIL-PRF-19500/713 ZTECHNOLOGY



Pro-Irradiation





Pre-Irradiation

Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions
BV _{DSS}	Drain-to-Source Breakdown Voltage	-100			V	$V_{GS} = 0V, I_{D} = -1.0mA$
$\Delta BV_{DSS}/\Delta T_{J}$	Breakdown Voltage Temp. Coefficient		-0.1		V/°C	Reference to 25° C, I_{D} = -1.0mA
R _{DS(on)}	Static Drain-to-Source On- Resistance			0.049	Ω	V _{GS} = -12V, I _{D2} = -30A ④
V _{GS(th)}	Gate Threshold Voltage	-2.0		-4.0	V	$V_{DS} = V_{GS}, I_{D} = -1.0 \text{mA}$
gfs	Forward Transconductance	24			S	V _{DS} = -15V, I _{D2} = -30A ④
I _{DSS}	Zara Cata Valtaga Drain Current			-10		V_{DS} = -80V, V_{GS} = 0V
	Zero Gate Voltage Drain Current			-25	μA	V _{DS} = -80V,V _{GS} = 0V,T _J =125°C
I _{GSS}	Gate-to-Source Leakage Forward			-100	nA	V _{GS} = -20V
	Gate-to-Source Leakage Reverse			100	ПА	V _{GS} = 20V
Q _G	Total Gate Charge			170		I _{D1} = -47A
Q _{GS}	Gate-to-Source Charge			65	nC	V _{DS} = -50V
Q _{GD}	Gate-to-Drain ('Miller') Charge			35		V _{GS} = -12V
t _{d(on)}	Turn-On Delay Time			30		V _{DD} = -50V
t _r	Rise Time			100		I _{D1} = -47A
t _{d(off)}	Turn-Off Delay Time			100	ns	R _G = 2.35Ω
t _f	Fall Time			120		V _{GS} = -12V
Ls +L _D	Total Inductance		4.0		nH	Measured from center of Drain pad to center of Source pad
C _{iss}	Input Capacitance		6240			V _{GS} = 0V
C _{oss}	Output Capacitance		1570		pF	V _{DS} = -25V
C _{rss}	Reverse Transfer Capacitance		115			f = 1.0MHz

Electrical Characteristics @ Tj = 25°C (Unless Otherwise Specified)

Source-Drain Diode Ratings and Characteristics

Symbol	Parameter		Тур.	Max.	Units	Test Conditions
Is	Continuous Source Current (Body Diode)			-47	۸	
I _{SM}	Pulsed Source Current (Body Diode) ①			-188	A	
V _{SD}	Diode Forward Voltage			-5.0	V	$T_J=25^{\circ}C, I_S = -47A, V_{GS}=0V$
t _{rr}	Reverse Recovery Time			230	ns	T _J =25°C, I _F = -47A,V _{DD} ≤ -50V
Q _{rr}	Reverse Recovery Charge			1.6	μC	di/dt = -100A/µs ④
t _{on}	Forward Turn-On Time	Intrinsic turn-on time is negligible (turn-on is dominated by $L_{\text{S}}+L_{\text{D}}$				

Thermal Resistance

Symbol	Parameter	Min.	Тур.	Max.	Units
$R_{ ext{ heta}JC}$	Junction-to-Case			0.5	°C/W
$R_{\theta J-PCB}$	Junction-to-PC Board (Soldered to 2" sq copper clad board)		1.6		C/W

Footnotes:

- ① Repetitive Rating; Pulse width limited by maximum junction temperature.
- $@~V_{\text{DD}}$ = -50V, starting T_{J} = 25°C, L = 0.36mH, Peak I_L = -47A, V_{GS} = -12V
- 3 $I_{SD} \leq \mbox{ -47A, di/dt } \leq \mbox{ -450A/} \mu s, \, V_{DD} \ \leq \mbox{ -100V, } T_J \leq \mbox{ 150°C}$
- $\textcircled{\ } \textbf{Pulse width} \leq 300 \ \mu \text{s; Duty Cycle} \leq 2\%$

 \odot Total Dose Irradiation with V_{GS} Bias. -12 volt V_{GS} applied and V_{DS} = 0 during irradiation per MIL-STD-750, Method 1019, condition A.

 \odot Total Dose Irradiation with V_{DS} Bias. -80 volt V_{DS} applied and V_{GS} = 0 during irradiation per MIL-STD-750, Method 1019, condition A.



Radiation Characteristics

IR HiRel radiation hardened MOSFETs are tested to verify their radiation hardness capability. The hardness assurance program at IR Hirel is comprised of two radiation environments. Every manufacturing lot is tested for total ionizing dose (per notes 5 and 6) using the TO-3 package. Both pre- and post-irradiation performance are tested and specified using the same drive circuitry and test conditions in order to provide a direct comparison.

Table1. Electrical Characteristics @ Tj = 25°C, Post Total Dose Irradiation \$6

Symbol	Parameter	100 kRads (Si) ¹		300 kRads (Si) ²		Units	Test Conditions	
	i arameter	Min.	Max.	Min.	Max.	Units		
BV_{DSS}	Drain-to-Source Breakdown Voltage	-100		-100		V	$V_{GS} = 0V, I_{D} = -1.0mA$	
V _{GS(th)}	Gate Threshold Voltage	-2.0	-4.0	-2.0	-5.0	V	$V_{DS} = V_{GS}, I_D = -1.0 \text{mA}$	
I _{GSS}	Gate-to-Source Leakage Forward		-100		-100	nA	V _{GS} = -20V	
I _{GSS}	Gate-to-Source Leakage Reverse		100		100	nA	V _{GS} = 20V	
I _{DSS}	Zero Gate Voltage Drain Current		-10		-10	μA	V_{DS} = -80V, V_{GS} = 0V	
R _{DS(on)}	Static Drain-to-Source ④ On-State Resistance (TO-3)		0.05		0.05	Ω	V _{GS} = -12V, I _{D2} = -30A	
R _{DS(on)}	Static Drain-to-Source ④ On-State Resistance (SupIR-SMD)		0.049		0.049	Ω	V _{GS} = -12V, I _{D2} = -30A	
V_{SD}	Diode Forward Voltage ④		-5.0		-5.0	V	V _{GS} = 0V, I _S = -47A	

1. Part number IRHNS597160 (JANSR2N7550U2A)

2. Part number IRHNS593160 (JANSF2N7550U2A)

IR HiRel radiation hardened MOSFETs have been characterized in heavy ion environment for Single Event Effects (SEE). Single Event Effects characterization is illustrated in Fig. a and Table 2.

Table 2. Typical Single Event Effect Safe Operating Area

		F in e rent	Denve	V _{DS} (V)					
lon	LET (MeV/(mg/cm²))	Energy (MeV)	Range (µm)	@ VGS= 0V	@ VGS= 5V	@ VGS= 10V	@ VGS= 15V	@ VGS= 17.5V	@ VGS= 20V
Br	37.9	252.6	33.1	-100	-100	-100	-100	-100	-100
I	59.7	314	30.5	-100	-100	-100	-100	-75	-25
Au	82.3	350	28.4	-100	-100	-100	-30		





Fig a. Typical Single Event Effect, Safe Operating Area

For Footnotes, refer to the page 2.



IRHNS597160 JANSR2N7550U2A

Pre-Irradiation









Fig 3. Typical Transfer Characteristics







Fig 2. Typical Output Characteristics





IRHNS597160 JANSR2N7550U2A

Pre-Irradiation




Fig 7. Typical Source -Drain Diode Forward Voltage




Fig 9. Maximum Drain Current Vs.Case Temperature




Fig 8. Maximum Safe Operating Area





Fig 10. Maximum Avalanche Energy Vs. Drain Current





IRHNS597160 JANSR2N7550U2A

Pre-Irradiation




Fig 11a. Unclamped Inductive Test Circuit




Fig 12a. Switching Time Test Circuit




Fig 13a. Gate Charge Waveform






Fig 11b. Unclamped Inductive Wave-









Fig 13b. Gate Charge Test Circuit



Note: For the most updated package outline, please see the website: SupIR-SMD







Infineon Technologies Service Center: USA Tel: +1 (866) 951-9519 and International Tel: +49 89 234 65555 Leominster, Massachusetts 01453, USA Tel: +1 (978) 534-5776 San Jose, California 95134, USA Tel: +1 (408) 434-5000 Data and specifications subject to change without notice.



IMPORTANT NOTICE

The information given in this document shall be in no event regarded as guarantee of conditions or characteristic. The data contained herein is a characterization of the component based on internal standards and is intended to demonstrate and provide guidance for typical part performance. It will require further evaluation, qualification and analysis to determine suitability in the application environment to confirm compliance to your system requirements.

With respect to any example hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind including without limitation warranties on non- infringement of intellectual property rights and any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's product and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of any customer's technical departments to evaluate the suitability of the product for the intended applications and the completeness of the product information given in this document with respect to applications.

For further information on the product, technology, delivery terms and conditions and prices, please contact your local sales representative or go to (www.infineon.com/irhirel)

WARNING

Due to technical requirements products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.