

IRHNS9A7064 JANSR2N7652U2A

RADIATION HARDENED POWER MOSFET SURFACE MOUNT (SupIR-SMD)

60V, N-CHANNEL REF: MIL-PRF-19500/777

REF: TECHNOLOGY

Product Summary

Part Number	Radiation Level	RDS(on)	I _D	QPL Part Number
IRHNS9A7064	100 kRads (Si)	$4.0 m\Omega$	100A*	JANSR2N7652U2A
IRHNS9A3064	300 kRads (Si)	4.0m $Ω$	100A*	JANSF2N7652U2A



Description

IR HiRel R9 technology provides superior power MOSFETs for space applications. These devices have improved immunity to Single Event Effect (SEE) and have been characterized for useful performance with Linear Energy Transfer (LET) up to 90MeV/(mg/cm²). Their combination of low RDS(on) and faster switching times reduces the power losses and increases power density in today's high speed switching applications such as DC-DC converters and motor controllers. These devices retain all of the well established advantages of MOSFETs such as voltage control, fast switching temperature stability of electrical parameters.

Features

- Low Rds(on)
- Fast Switching
- Single Event Effect (SEE) Hardened
- Low Total Gate Charge
- Simple Drive Requirements
- Hermetically Sealed
- · Ceramic Package
- Light Weight
- Surface Mount
- ESD Rating: Class 3B per MIL-STD-750, Method 1020

Absolute Maximum Ratings

Pre-Irradiation

Symbol	Parameter	Value	Units
I _{D1} @ V _{GS} = 12V, T _C = 25°C	Continuous Drain Current	100*	
I _{D2} @ V _{GS} = 12V, T _C = 100°C	Continuous Drain Current	100*	A
I _{DM} @ T _C = 25°C	Pulsed Drain Current ①	400	
P _D @ T _C = 25°C	Maximum Power Dissipation	250	W
	Linear Derating Factor	2.0	W/°C
V_{GS}	Gate-to-Source Voltage	± 20	V
E _{AS}	Single Pulse Avalanche Energy ②	4000	mJ
I _{AR}	Avalanche Current ①	100	А
E _{AR}	Repetitive Avalanche Energy ①	25	mJ
dv/dt	Peak Diode Recovery dv/dt ③	4.8	V/ns
T _J	Operating Junction and	-55 to + 150	
T _{STG}	Storage Temperature Range		°C
	Lead Temperature	300 (for 5s)	
	Weight	3.3 (Typical)	g

^{*} Current is limited by package

For Footnotes, refer to the page 2.



Electrical Characteristics @ Tj = 25°C (Unless Otherwise Specified)

Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions		
BV _{DSS}	Drain-to-Source Breakdown Voltage	60			V	$V_{GS} = 0V, I_D = 1.0mA$		
$\Delta BV_{DSS}/\Delta T_{J}$	Breakdown Voltage Temp. Coefficient		0.06		V/°C	Reference to 25°C, I _D = 1.0mA		
R _{DS(on)}	Static Drain-to-Source On-Resistance			4.0	mΩ	V _{GS} = 12V, I _{D2} = 100A* ④		
$V_{GS(th)}$	Gate Threshold Voltage	2.0		4.0	V	\\ -\\ \ \ \ - \\ \ \ \ \ \ \ \ \ \ \ \		
$\Delta V_{GS(th)} / \Delta T_J$	Gate Threshold Voltage Coefficient		-7.2		mV/°C	$V_{DS} = V_{GS}$, $I_D = 6.0 \text{mA}$		
Gfs	Forward Transconductance	50			S	V _{DS} = 15V, I _{D2} = 100A* ④		
I _{DSS}	Zero Gate Voltage Drain Current			1.0		$V_{DS} = 48V$, $V_{GS} = 0V$		
	Zero Gate Voltage Drain Current			25	μA	$V_{DS} = 48V, V_{GS} = 0V, T_{J} = 125^{\circ}C$		
I_{GSS}	Gate-to-Source Leakage Forward			100	nA	$V_{GS} = 20V$		
	Gate-to-Source Leakage Reverse			-100	ш	$V_{GS} = -20V$		
Q_G	Total Gate Charge			194		I _{D1} = 100A*		
Q_{GS}	Gate-to-Source Charge			50	nC	V _{DS} = 30V		
Q_{GD}	Gate-to-Drain ('Miller') Charge			69		V _{GS} = 12V		
$t_{d(on)}$	Turn-On Delay Time			30		$V_{DD} = 30V$		
tr	Rise Time			180		I _{D1} = 100A		
$t_{d(off)}$	Turn-Off Delay Time			113	ns	$R_G = 2.35\Omega$		
t _f	Fall Time			66		V _{GS} = 12V		
Ls +L _D	Total Inductance		12		nH	Measured from center of Drain pad to center of Source pad		
C _{iss}	Input Capacitance		9100			V _{GS} = 0V		
Coss	Output Capacitance		3700		pF	V _{DS} = 25V		
C _{rss}	Reverse Transfer Capacitance		30			f = 1.0MHz		
R_G	Gate Resistance		1.5		Ω	f = 1.0MHz, open drain		

Source-Drain Diode Ratings and Characteristics

Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions	
Is	Continuous Source Current (Body Diode)			100*	۸		
I _{SM}	Pulsed Source Current (Body Diode) ①			400	Α		
V _{SD}	Diode Forward Voltage			1.2	V	$T_J = 25^{\circ}C, I_S = 100A^*, V_{GS} = 0V$	
t _{rr}	Reverse Recovery Time		130	165	ns	$T_J = 25^{\circ}C, I_F = 100A^*$	
Q _{rr}	Reverse Recovery Charge		775		nC	V _{DD} ≤ 25V, di/dt = 100A/μs ④	
t _{on}	Forward Turn-On Time	Intrinsic turn-on time is negligible (turn-on is dominated by L _S +L _D)					

^{*} Current is limited by package

Thermal Resistance

Symbol	Parameter	Min.	Тур.	Max.	Units
$R_{ heta JC}$	Junction-to-Case			0.50	°C/W
$R_{ heta J ext{-PCB}}$	Junction-to-PC Board (Soldered to 2" sq.inch copper clad board)		1.6		C/VV

Footnotes:

- ① Repetitive Rating; Pulse width limited by maximum junction temperature.
- $^{\circ}$ V_{DD} = 60V, starting T_J = 25°C, L = 0.8mH, Peak I_L = 100A, V_{GS} = 20V
- $\label{eq:local_local_local_local} \ensuremath{ \Im } \quad I_{SD} \leq 100A, \; di/dt \leq \; 1155A/\mu s, \; V_{DD} \leq 60V, \; T_J \leq 150 ^{\circ} C$
- ⑤ Total Dose Irradiation with V_{GS} Bias. 12 volt V_{GS} applied and V_{DS} = 0 during irradiation per MIL-STD-750, Method 1019, condition A.
- ⑥ Total Dose Irradiation with V_{DS} Bias. 48 volt V_{DS} applied and V_{GS} = 0 during irradiation per MIL-STD-750, Method 1019, condition A.



Radiation Characteristics

IR HiRel Radiation Hardened MOSFETs are tested to verify their radiation hardness capability. The hardness assurance program at IR HiRel is comprised of two radiation environments. Every manufacturing lot is tested for total ionizing dose (per notes 5 and 6) using the TO-3 package. Both pre- and post-irradiation performance are tested and specified using the same drive circuitry and test conditions in order to provide a direct comparison.

Table1. Electrical Characteristics @ Tj = 25°C, Post Total Dose Irradiation \$6

Symbol	Parameter	Up to 300	kRads (Si) 1	Units	Test Conditions	
	Faiailletei	Min.	Max.	Units		
BV_{DSS}	Drain-to-Source Breakdown Voltage	60		V	$V_{GS} = 0V, I_{D} = 1.0mA$	
$V_{GS(th)}$	Gate Threshold Voltage	2.0	4.0	V	$V_{DS} = V_{GS}$, $I_D = 6.0 \text{mA}$	
I _{GSS}	Gate-to-Source Leakage Forward		100	nA	V _{GS} = 20V	
I _{GSS}	Gate-to-Source Leakage Reverse		-100	nA	V _{GS} = -20V	
I _{DSS}	Zero Gate Voltage Drain Current		1.0	μA	$V_{DS} = 48V, V_{GS} = 0V$	
R _{DS(on)}	Static Drain-to-Source ④ On-State Resistance (TO-3)		6.0	mΩ	V _{GS} = 12V, I _{D2} = 75A	
R _{DS(on)}	Static Drain-to-Source ④ On-State Resistance (SupIR-SMD)		4.0	mΩ	V _{GS} = 12V, I _{D2} = 100A	
V _{SD}	Diode Forward Voltage		1.2	V	V _{GS} = 0V, I _S = 75A	

^{1.} Part numbers IRHNS9A7064 (JANSR2N7652U2A) and IRHNS9A3064 (JANSF2N7652U2A)

IR HiRel radiation hardened MOSFETs have been characterized in heavy ion environment for Single Event Effects (SEE). Single Event Effects characterization is illustrated in Fig. a and Table 2.

Table 2. Typical Single Event Effect Safe Operating Area

		D		VDS	S (V)	
LET (MeV/(mg/cm²))	Energy (MeV)	Range (µm)	@ VGS = 0V	@ VGS = -1V	@ VGS = -5V	@ VGS = -10V
38 ± 5%	355 ± 7.5%	43 ± 7.5%	60	60	60	60
60 ± 5%	753 ± 7.5%	60 ± 10%	60	60	60	60
90 ± 5%	1515 ± 7.5%	82 ± 7.5%	60	60		




Fig a. Typical Single Event Effect, Safe Operating Area

For Footnotes, refer to the page 2.




Fig 1. Typical Output Characteristics




Fig 3. Typical Transfer Characteristics




Fig 5. Typical On-Resistance Vs Gate Voltage




Fig 2. Typical Output Characteristics




Fig 4. Normalized On-Resistance Vs. Temperature




Fig 6. Typical On-Resistance Vs Drain Current




Fig 7. Typical Drain-to-Source Breakdown Voltage Vs Temperature




Fig 9. Typical Capacitance Vs. Drain-to-Source Voltage




Fig 11. Typical Source-Drain Diode Forward Voltage




Fig 8. Typical Threshold Voltage Vs Temperature




Fig 10. Typical Gate Charge Vs. Gate-to-Source Voltage




Fig 12. Maximum Drain Current Vs.Case Temperature






Fig 13. Maximum Safe Operating Area




Fig 14. Maximum Avalanche Energy Vs. Drain Current




Fig 15. Maximum Effective Transient Thermal Impedance, Junction-to-Case




Fig 16a. Unclamped Inductive Test Circuit




Fig 17a. Gate Charge Waveform




Fig 18a. Switching Time Test Circuit




Fig 16b. Unclamped Inductive Waveforms




Fig 17b. Gate Charge Test Circuit





Fig 18b. Switching Time Waveforms



Note: For the most updated package outline, please see the website: SupIR-SMD

Case Outline and Dimensions — SupIR-SMD





www.infineon.com/irhirel

Infineon Technologies Service Center: USA Tel: +1 (866) 951-9519 and International Tel: +49 89 234 65555

Leominster, Massachusetts 01453, USA Tel: +1 (978) 534-5776

San Jose, California 95134, USA Tel: +1 (408) 434-5000

Data and specifications subject to change without notice.



IMPORTANT NOTICE

The information given in this document shall be in no event regarded as guarantee of conditions or characteristic. The data contained herein is a characterization of the component based on internal standards and is intended to demonstrate and provide guidance for typical part performance. It will require further evaluation, qualification and analysis to determine suitability in the application environment to confirm compliance to your system requirements.

With respect to any example hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind including without limitation warranties on non- infringement of intellectual property rights and any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's product and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of any customer's technical departments to evaluate the suitability of the product for the intended applications and the completeness of the product information given in this document with respect to applications.

For further information on the product, technology, delivery terms and conditions and prices, please contact your local sales representative or go to (www.infineon.com/irhirel).

WARNING

Due to technical requirements products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.