

Market News

Infineon manufactures industry's first true 1000 A voltage regulator solution for next generation AI and 5G networking

Munich, Germany – 22 March 2019 – Infineon Technologies AG (FSE: IFX / OTCQX: IFNNY) extends its portfolio of high current system chipset solutions with the industry's first 16-phase digital PWM multiphase controller, the [XDPE132G5C](#). The portfolio enables currents of 500 to 1000 A and higher for next generation CPUs, GPUs, FPGA and ASICs used in high-end [artificial intelligence](#) (AI) servers and [5G](#) datacom applications.

As CPU current requirements increase to enable next generation AI and networking workloads, DC-DC voltage regulators (VR) need to deliver more than 500 A to the load. With a true 16-phase digital PWM engine and an improved advanced transient algorithm, the XDPE132G5C controller addresses these high phase count requirements. The true active current sharing between phases enables a reliable, compact and cost-saving design. Furthermore, there is no need for extra logic doubler ICs commonly utilized in today's high phase count markets.

Leading edge ASIC's and FPGA's in communication systems are requesting V_{out} control of less than 1 mV steps. This is inherent in the XDPE132G5C, offering fine V_{out} setting in 0.625 mV increments. In addition, it supports communication market auto-restart requirements with options to reduce remote site maintenance following power or system glitches.

The XDPE132G5C is packaged in a 7 mm x 7 mm 56-pin QFN to accommodate 16 phases. It employs a full digital and programmable load line and is PMBus 1.3/AVS compliant delivering a comprehensive suite of telemetry features. Paired with TDA21475, the industry's most thermally efficient integrated current sense power stage, the XDPE132G5C controller can efficiently deliver over 1000 A.

The 70 A-rated TDA21475 power stage, housed in a 5 mm x 6 mm package, provides industry-leading efficiency of more than 95 percent. The exposed top significantly reduces the $R_{th(j-top)}$ from 19°C/W in the over-molded package to

For the Trade Press: INFPM201903.052e

Fabian Schiffer (Headquarters)
Sian Cummings (Americas)
Chi Kang David Ong (Asia-Pacific)
Jonathan Liu (Greater China)
Yoko Sasaki (Japan)

Tel.: +49 89 234 25869
Tel.: +1 310 252 7148
Tel.: +65 6876 3070
Tel.: +86 21 6101 9182
Tel.: +81 3 5745 7340

fabian.schiffer@infineon.com
sian.cummings@infineon.com
david.ong@infineon.com
jonathan.liu@infineon.com
yoko.sasaki@infineon.com

Investor Relations:
Tel: +49 89 234 26655
investor.relations@infineon.com

1.6°C/W. This efficiently removes heat from the top of the package, resulting in excellent VR power density and optimal VR phase count and footprint. To further maximize the capability of the CPU/ASIC, the TDA21475 also offers smart overcurrent and overvoltage protection and delivers accurate temperature and current information to the XDPE132G5C controller.

Rounding out Infineon's portfolio of high current chipset solutions is the IR35223 true 10-phase PWM digital controller. It provides a cost-effective option for VR solution requirements of up to 500 A. The IR35223 is housed in a 6 mm x 6 mm, 48-pin QFN package and provides advanced transient performance and telemetry features including PMBus 1.3/AVS bus compliance.

More information is available at www.infineon.com/next-gen-processors.

For the Trade Press: INFPM201903.052e

Fabian Schiffer (Headquarters)
Sian Cummings (Americas)
Chi Kang David Ong (Asia-Pacific)
Jonathan Liu (Greater China)
Yoko Sasaki (Japan)

Tel.: +49 89 234 25869
Tel.: +1 310 252 7148
Tel.: +65 6876 3070
Tel.: +86 21 6101 9182
Tel.: +81 3 5745 7340

fabian.schiffer@infineon.com
sian.cummings@infineon.com
david.ong@infineon.com
jonathan.liu@infineon.com
yoko.sasaki@infineon.com

Investor Relations:
Tel: +49 89 234 26655
investor.relations@infineon.com