


SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	4.5	4.7	5.4
L	3	3.3	3.5
D	27.7	28	28.2
E	10.16 BSC		
E1	8.64	8.89	9.14
θ	0°	-	15°
c	0.2	0.27	0.3
b	0.36	0.48	0.56
b1	0.82	1.02	1.32
e	1.778 BSC		
S1	-	-	1.27
Q	0.51	-	-

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []