


1) Does not include plastic or metal protrusion of  $0.15$  max. per side

2) Does not include dambar protrusion of  $0.05$  max. per side

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]

Drawing according to ISO 8015, general tolerances ISO 2768-mK