


1) Does not include plastic or metal protrusion of 0.25 max. per side  
 All dimensions are in units mm  
 The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]  
 Drawing according to ISO 8015, general tolerances ISO 2768-mK