


SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.7
A1	0.05	-	0.15
b	0.13	0.18	0.23
c	0.09	-	0.2
D	26 BSC		
D1	24 BSC		
e	0.4 BSC		
E	26 BSC		
E1	24 BSC		
L	0.45	0.6	0.75
θ	0°	-	8°

1) Dimensions D1 and E1 do not include mold protrusion. allowable protrusion is 0.25mm per side.
 2) Dimension b does not include dambar protrusion. the dambar protrusion(s) shall not cause the lead width to exceed b maximum by more than 0.08mm.
 All dimensions are in units mm
 The drawing is in compliance with ISO 128-30, Projection Method 1 []