





SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	3.35
A1	0.25	-	-
A2	2.7	2.8	2.9
b	0.3	-	0.45
c	0.15	-	0.23
D	17	17.2	17.4
D1	13.9	14	14.1
e	0.8 BSC		
E	23	23.2	23.4
E1	19.9	20	20.1
L	0.73	0.88	1.03
P	24		
Q	40		
R	64		
S	80		

1) Dimensions "D1" and "E1" do not include mold protrusion. allowable protrusion is 0.25mm.

2) Dimension "b" does not include dambar protrusion.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []