


1) Exclude mold flash

2) Removal on mold gate: intrusion 0.1mm, protusion 0.1mm

All metal surfaces are plated except area of cut

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Drawings according to ISO 8015, general tolerances $\pm 0.1 / 1^\circ 30'$