


2×
 $\text{0.1} \text{C} \text{A}$

2×
 $\text{0.1} \text{C} \text{B}$

Pin1 marking



32×
 $\text{0.08} \text{C}$
 Coplanarity


Seating plane

0.05 Max.
 Stand off

(0.2)

1.1 Max.

Bottom view



0.6
 (32×)

2.9

$\text{0.1} \text{C} \text{A}$

2.9

2.98

$\text{0.1} \text{C} \text{B}$

$\text{0.1} \text{C} \text{B}$

2.93

(2.275)

$\text{0.1} \text{C} \text{B}$

0.65

4.2


$\text{0.1} \text{C} \text{A}$

0.3±0.1

32×
 $\text{0.1} \text{M} \text{C} \text{A} \text{B}$

$\text{0.05} \text{M} \text{C}$

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Drawing according to ISO 8015, general tolerances ISO 2768-mK