


1) Typical metal surface min. $x=7.25, y=12.3$

All metal surfaces: tin plated, except area of cut

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Drawing according to ISO 8015, general tolerances $\pm 0,1; \pm 1^\circ 30$