



SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.7
A1	0.05	-	0.15
A2	1.35	1.4	1.45
D	30 BSC		
D1	28 BSC		
D2	9.9 REF		
D3	8.71 REF		
E	30 BSC		
E1	28 BSC		
E2	9.9 REF		
E3	8.71 REF		
θ	0°	4°	8°
c	0.12	-	0.2
b	0.17	0.22	0.27
L	0.45	0.6	0.75
e	0.5 BSC		

1) Dimensions D1 and E1 do not include mold protrusion. allowable protrusion is 0.25mm pre side.

2) Dimension b does not include damber protrusion. the dambar protrusion(S) shall not cause the lead width to exceed b maximum by more than 0.08mm.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [cone symbol]