



SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.2
A1	0.05	-	0.15
D	3.1 BSC		
E	6.4 BSC		
E1	4.4 BSC		
θ	0°	-	8°
c	0.047	-	0.207
b	0.12	0.22	0.32
L	0.5	0.6	0.7
e	0.65 BSC		

1) Dimensioning D include mold flash, dimensioning E1 does not include interlead flash or protrusion. interlead flash or protrusions shall not exceed 0.025 mm per side.

2) Dimension b does not include dambar protrusion. allowable dambar protrusion shall be 0.10mm

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Dimensioning and tolerancing per ASME Y14.5M-1994.