






All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1
A1	0.16	-	-
D	6 BSC		
E	6 BSC		
Øb	0.25	0.3	0.35
eD1	0.5 BSC		
eE1	0.5 BSC		
eD2	0.65 BSC		
eE2	0.65 BSC		
eD3	0.7 BSC		
eE3	0.7 BSC		