








SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	0.9
A1	0	-	0.05
A2	-	0.65	0.7
A3	0.203 REF		
b	0.18	0.25	0.3
D	7 BSC		
E	7 BSC		
D2	5.2	5.3	5.4
E2	5.2	5.3	5.4
e	0.5 BSC		
L	0.3	0.4	0.5

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []