



Product Brief

OptiMOS™ 100V, 120V, 150V

Highest Power Density and System Efficiency

Infineon's OptiMOS™ 100V, 120V and 150V families combine very low on-state resistance ($R_{DS(on)}$) and fastest switching behavior, providing outstanding performance to a wide range of industrial and consumer applications. From high current Motor Control applications to fast switching DC/DC converters or Class D Audio Amplifiers, Infineon's products offer excellent performance and the highest efficiency and minimal space requirements.

OptiMOS™ 100V-150V are available in high performance packages such as CanPAK™, S308, SuperSO8 and TO-Leadless, enabling designs with highest efficiency and power density. Additionally, the devices facilitate the change from leaded packages to small and high-efficient SMD packages such as SuperSO8.

For high-current applications requiring low ohmic parts the OptiMOS™ 100V and 150V products based in the new and exclusive TO-Leadless package sets new benchmarks in the market. In comparison to devices in the Best-in-Class D²PAK and D²PAK 7pin, products in TO-Leadless offer up to 40% higher current capability, up to 13% lower $R_{DS(on)}$, up to 27% lower Figure of Merit (FOM) and 60% space reduction.

Features


- Outstanding switching performance
- Excellent $R_{DS(on)}$ and FOM
- Very low Q_g and Q_{gd}
- RoHS compliant – halogen free

Benefits

- Increased efficiency
- Highest power density
- Less paralleling required
- Smallest board-space consumption
- Easy-to-design products
- Environmentally friendly

Application

- Motor Control for 48V–80V systems (i.e. domestic vehicles, forklift, trucks)
- Synchronous Rectification for AC/DC SMPS
- Isolated DC/DC converters (Telecom and datacom systems)
- OR-ing switches and circuit breakers in 48V systems
- Notebook Adapter
- Class D Audio Amplifiers
- Uninterruptible power supplies (UPS)




OptiMOS™ 100V, 120V, 150V

Highest Power Density and System Efficiency

OptiMOS™ 120V technology opens up new possibilities for performance and cost optimized solutions. Where 150V part is not required but a 100V MOSFET is not enough, the OptiMOS™ 120V family is the perfect solution, providing a significant increase in performance over 150V technologies. Moreover, to optimize and simplify the design process, Infineon offers a broad range of $R_{DS(on)}$ in different packages.

Infineon offers the right MOSFET for each system



OptiMOS™ 100V, 120V and 150V Product Portfolio for best in class products per package

Voltage Class	CanPAK™ M CanPAK™ S	D ² PAK D ² PAK 7pin	TO-220 TO-220 FullPAK	SuperS08	S308	TO-Leadless	Bare Die ($R_{DS(on)}$ typ.)
100V	BSB056N10NN3 G $R_{DS(on)} = 5.6m\Omega$	IPB027N10N3 G $R_{DS(on)} = 2.7m\Omega$	IPPO30N10N3 G $R_{DS(on)} = 3.0m\Omega$	BSC046N10NS3 G $R_{DS(on)} = 4.6m\Omega$	BSZ150N10LS3 G $R_{DS(on)} = 15m\Omega$	IPT020N10N3 $R_{DS(on)} = 2.0m\Omega$	IPC302N10N3 $R_{DS(on)} < 3m\Omega$
	BSF134N10NJ3 G* $R_{DS(on)} = 13.4m\Omega$	IPB025N10N3 G** $R_{DS(on)} = 2.5m\Omega$	IPA030N10N3 G*** $R_{DS(on)} = 3.0m\Omega$				
120V		IPB038N12N3 G $R_{DS(on)} = 3.8m\Omega$	IPPO41N12N3 G $R_{DS(on)} = 4.1m\Omega$	BSC077N12NS3 G $R_{DS(on)} = 7.7m\Omega$	BSZ240N12NS3 G $R_{DS(on)} = 24m\Omega$		IPC302N12N3 $R_{DS(on)} < 4m\Omega$
		IPB036N12N3 G** $R_{DS(on)} = 3.6m\Omega$					
150V	BSB165N15NZ3 G $R_{DS(on)} = 16.5m\Omega$	IPB072N15N3 G $R_{DS(on)} = 7.2m\Omega$	IPPO75N15N3 G $R_{DS(on)} = 7.5m\Omega$	BSC190N15NS3 G $R_{DS(on)} = 19m\Omega$	BSZ520N15NS3 G $R_{DS(on)} = 52m\Omega$	IPT059N15N3 $R_{DS(on)} = 5.9m\Omega$	IPC302N15N3 $4m\Omega < R_{DS(on)} < 7m\Omega$
		IPB065N15N3 G** $R_{DS(on)} = 6.5m\Omega$	IPA075N15N3 G*** $R_{DS(on)} = 7.5m\Omega$				

* CanPAK™ S
 ** D²PAK 7pin
 *** TO-220 FullPAK

Published by
 Infineon Technologies Austria AG
 9500 Villach, Austria

© 2013 Infineon Technologies AG.
 All Rights Reserved.

Visit us:
www.infineon.com

Order Number: B152-H9388-G3-X-7600-DB2013-009
 Date: 09 / 2013

Attention please!

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie"). With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies Office. Infineon Technologies Components may only be used in life-support devices or systems with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.