

# Recommended performance evaluation methodology for XENSIV™ PAS CO2 sensor

## About this document

This application note presents a possible gas measurement setup to potential customers who would like to evaluate the performance of the XENSIV™ PAS CO2.

## Scope and purpose

There is a wide range of gas sensor products available on the market, but very few offer high-performance solutions like XENSIV™ PAS CO2. Therefore, extra care is necessary to ensure the measurement data reproduce the datasheet performance.

## Intended audience

Application engineers, test engineers, verification engineers, system engineers


## Table of contents

<b>About this document</b> .....	<b>1</b>
<b>Table of contents</b> .....	<b>1</b>
<b>1 Introduction to XENSIV™ PAS CO2</b> .....	<b>2</b>
<b>2 Recommended gas measurement setup</b> .....	<b>3</b>
2.1 Gas mixing system.....	3
2.2 A typical test chamber.....	4
2.3 Recommended reference sensors .....	4
2.3.1 CO <sub>2</sub> reference sensor.....	4
2.3.2 Pressure and temperature reference sensor .....	4
2.3.3 Reference relative humidity sensor.....	4
<b>3 Typical performance evaluation of XENSIV™ PAS CO2</b> .....	<b>5</b>
<b>Revision history</b> .....	<b>6</b>

# 1 Introduction to XENSIV™ PAS CO2

The XENSIV™ PAS CO2 is a real CO<sub>2</sub> sensor that overcomes the size, performance and assembly challenges of existing CO<sub>2</sub> sensor solutions. The sensor has been designed based on the unique photo acoustic spectroscopy (PAS) principle. XENSIV™ PAS CO2 comes in an exceptionally miniaturized module that is four times smaller and three times lighter than the existing commercial real CO<sub>2</sub> sensors that operate based on the NDIR principle. In addition to the unprecedented compact design, XENSIV™ PAS CO2 delivers superior-quality data thanks to its high-accuracy performance beating state-of-the-art CO<sub>2</sub> gas sensors. The sensor's high accuracy level makes it the right choice for indoor air-quality monitoring stations, HVAC systems and IoT applications.

All major components of XENSIV™ PAS CO2 are developed and designed in-house according to Infineon's high quality standards (e.g., component traceability, internal and external audits, state-of-the-art qualification standards and tools). As shown in Figure 1(a), outside of the cavity there is an XMCT™ microcontroller to support data processing and a MOSFET to drive the light source. Within the cavity, there is a high-SNR silicon microphone as the detector and an in-house built MEMS-based infrared emitter as the light source.



**Figure 1 All the key components of XENSIV™ PAS CO2 are developed in-house to ensure best-in-class quality of the sensor**

**Recommended gas measurement setup**

## 2 Recommended gas measurement setup


A gas measurement setup should have three main components:

- Gas mixing system
- Test chamber
- Reference sensors

In the following section, a brief description of each component is provided.

### 2.1 Gas mixing system

To deliver the target CO<sub>2</sub> concentration to the gas chamber, a gas mixing system should be used. The schematic of a typical setup is presented in Figure 1. To control the gas and humidity concentration at least three mass flow controllers (MFCs) are needed. For the example setup, MFC 1 is being used for the CO<sub>2</sub> bottle. A synthetic air gas bottle is connected to MFCs 2 and 3, which are used to dilute the gas concentration within the gas bottle to achieve an ideal target gas concentration. MFC 2 is maintaining the dry airflow, whereas MFC 3 is maintaining the wet airflow via a water column. By varying the flow ratio between dry air and wet air, the relative humidity can be controlled. Alternatively, a humidity generator can also be used to maintain a stable relative humidity point.



**Figure 2 Gas mixing system to transfer exact CO<sub>2</sub> concentration to the gas chamber**

To achieve a target gas concentration at specific relative humidity, the following equation (i) needs to be used:

$$T_c = \frac{B_c \times G_f}{D_f + W_f} \tag{i}$$

Where,

T<sub>c</sub> = Target gas concentration (ppm)

B<sub>c</sub> = Bottle concentration (ppm)

G<sub>f</sub> = CO<sub>2</sub> gas flow (SCCM)

D<sub>f</sub> = Dry air flow (SCCM)

W<sub>f</sub> = Wet air flow (SCCM)

**PAS CO2 sensor**

**Recommended gas measurement setup**

Target relative humidity can be achieved by varying the ratio between  $D_f$  and  $W_f$ .

For example, if a sensor needs to be characterized at a room temperature and atmospheric pressure with a 50000 ppm (5 percent) gas bottle concentration at 1000 SCCM flow, then a typical gas measurement protocol can be as follows:

**Table 1 Experimental conditions**

Target CO <sub>2</sub> concentration [ppm]	Time [min]	MFC 1 [SCCM]	MFC 2 [SCCM]	MFC 3 [SCCM]
Air 50 percent RH	30	0	250	250
Air 50 percent RH + 400 ppm CO <sub>2</sub>	15	4	246	250
Air 50 percent RH	30	0	250	250
Air 50 percent RH + 1000 ppm CO <sub>2</sub>	15	10	240	250
Air 50 percent RH	30	0	250	250
Air 50 percent RH + 5000 ppm CO <sub>2</sub>	15	50	200	250
Air 50 percent RH	30	0	250	250

**2.2 A typical test chamber**

A test chamber needs to be designed in such a way that there is no leakage, and it can maintain laminar flow while exposing the sensor to the target gas concentration. Inside the test chamber, it is recommended to accommodate a reference CO<sub>2</sub> sensor. Additionally, to get an overview of the complete test conditions, pressure sensor, humidity sensor and temperature sensor should also be considered.

**2.3 Recommended reference sensors**

**2.3.1 CO<sub>2</sub> reference sensor**

Vaisala GMP343 is recommended as the reference CO<sub>2</sub> sensor. Further details of this product can be found on the product [page](#).

**2.3.2 Pressure and temperature reference sensor**

Infineon’s XENSIV™ DPS368 is recommended as the reference pressure and temperature sensor. The pressure sensor’s pressure output comes with excellent precision of ± 0.002 hPa and relative accuracy of ± 0.06 hPa. The built-in temperature sensor offers an accuracy of ±0.5°C with 0.01°C data resolution. Further details of the product can be found [here](#).

**2.3.3 Reference relative humidity sensor**

A highly accurate low-powered relative humidity sensor should be considered as the reference relative humidity sensor.


### 3 Typical performance evaluation of XENSIV™ PAS CO2

Example test condition:


- Relative humidity 0%, 23%, 50% and 85%
- Ambient pressure 960 hPa
- CO2 concentration steps: 1000 ppm, 1800 ppm, 3100 ppm, 4000 ppm and 5000 ppm

#### Gas ramp for sensor accuracy evaluation

T = 25°C, p = 960 hPa, flow = 500 sccm



#### Typical CO2 response





Revision history

Revision history

Document version	Date of release	Description of changes
V1.0	02.06.2021	Creation

**Trademarks**

All referenced product or service names and trademarks are the property of their respective owners.

**Edition 2021-06-02**

**Published by**

**Infineon Technologies AG**

**81726 Munich, Germany**

**© 2021 Infineon Technologies AG.**

**All Rights Reserved.**

**Do you have a question about this document?**

**Email: [erratum@infineon.com](mailto:erratum@infineon.com)**

**AN\_2106\_PL38\_2107\_132434**

**AppNote Number**

**IMPORTANT NOTICE**

The information contained in this application note is given as a hint for the implementation of the product only and shall in no event be regarded as a description or warranty of a certain functionality, condition or quality of the product. Before implementation of the product, the recipient of this application note must verify any function and other technical information given herein in the real application. Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind (including without limitation warranties of non-infringement of intellectual property rights of any third party) with respect to any and all information given in this application note.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office ([www.infineon.com](http://www.infineon.com)).

**WARNINGS**

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.