

Please note that Cypress is an Infineon Technologies Company.

The document following this cover page is marked as “Cypress” document as this is the company that originally developed the product. Please note that Infineon will continue to offer the product to new and existing customers as part of the Infineon product portfolio.

Continuity of document content

The fact that Infineon offers the following product as part of the Infineon product portfolio does not lead to any changes to this document. Future revisions will occur when appropriate, and any changes will be set out on the document history page.

Continuity of ordering part numbers

Infineon continues to support existing part numbers. Please continue to use the ordering part numbers listed in the datasheet for ordering.

Cypress Semiconductor Automotive Package Qualification Report

QTP# 105211 VERSION *B
April 2014

**Automotive 32L STSOP (8x13.4mm)
NiPdAu, MSL3, 260°C Reflow
JCET-China (JT)**

**FOR ANY QUESTIONS ON THIS REPORT, PLEASE CONTACT
reliability@cypress.com or via a CYLINK CRM CASE**

Prepared By:
Lorena R. Zapanta (ILZ)
Reliability Engineer

Reviewed By:
Rene Rodgers (RT)
Reliability Manager

Approved By:
Richard Oshiro(RGO)
Reliability Director



PRODUCT QUALIFICATION HISTORY

QTP Number	Description of Qualification Purpose	Date
105211	New Assembly Site (JCET) Qual – Automotive STSOP 32ld_8 x 13.4 mm body – Pb-Free (KEG6000, QMI509, 1.0 mil Wire, NiPdAu)	Feb 2011

MAJOR PACKAGE INFORMATION USED IN THIS QUALIFICATION	
Package Designation:	ZB32R
Package Outline, Type, or Name:	32L STSOP (8X13.4mm)
Mold Compound Name/Manufacturer:	KEG6000 / Kyocera
Mold Compound Flammability Rating:	V-O per UL94
Mold Compound Alpha Emission Rate:	0.002 CPH/cm ²
Oxygen Rating Index: >28%	N/A
Lead Frame Designation:	Reduced Metal Pad
Lead Frame Material:	Copper
Substrate Material:	N/A
Lead Finish, Composition / Thickness:	NiPdAu
Die Backside Preparation Method/Metallization:	Backgrind
Die Separation Method:	Wafersaw
Die Attach Supplier:	Henkel
Die Attach Material:	QMI509
Bond Diagram Designation	001-57618, 001-13841, 001-48574
Wire Bond Method:	Thermosonic
Wire Material/Size:	1.0 mil / Au
Thermal Resistance Theta JA °C/W:	11.3 °C/W
Package Cross Section Yes/No:	Yes
Assembly Process Flow:	001-67698
Name/Location of Assembly (prime) facility:	JT-JCET China
MSL LEVEL	3
REFLOW PROFILE	260C

ELECTRICAL TEST / FINISH DESCRIPTION	
Test Location:	CML-R

Note: Please contact a Cypress Representative for other package availability.

RELIABILITY TESTS PERFORMED PER SPECIFICATION REQUIREMENTS

Stress/Test	Test Condition (Temp/Bias)	Result P/F
Electrostatic Discharge Human Body Model (ESD-HBM)	AEC-Q100-002	P
Electrostatic Discharge Charge Device Model (ESD-CDM)	AEC-Q100-011	P
Latch-up Sensitivity	AEC-Q100-004	P
High Temperature Operating Life Early Failure Rate	AEC-Q100-008 and JESD22-A108, 150 C Dynamic Operating Condition, Vcc = 1.85V	P
High Temperature Operating Life Latent Failure Rate	JESD22-A108, 150 C /125C Dynamic Operating Condition, Vcc = 1.85V, 150C	P
High Accelerated Saturation Test (HAST)	JESD22-A110, 130 C, 85%RH, 3.60V Precondition: JESD22-A113 Moisture Sensitivity Level (192 Hrs., 30 C°, 60% RH)	P
High Temperature Storage Life Test	JESD22-A103, 150 C	P
Temperature Cycle	JESD22- A104, -65 C to 150 C Precondition: JESD22-A113 Moisture Sensitivity Level (192 Hrs., 30 C°, 60% RH)	P
Post Temperature Cycle Wire Bond Pull	Mil-Std 883, Method 2011	P
Pressure Cooker Test	JESD22-A102, 121 C, 100%RH, 15 PSIG Precondition: JESD22-A113 Moisture Sensitivity Level (192 Hrs., 30 C°, 60% RH)	P
Wire Bond Shear	AEC Q100-001	P
Wire Bond Pull	Mil-Std 883, Method 2011	P
Solderability	JESD22-B102	P
Physical Dimensions	JESD22B100 and B108	P
Electrical Distributions	AEC Q100-009	P
Lead Integrity	JESD22-B105	P

Reliability Test Data

QTP #: 105211

Device	Fab Lot #	Assy Lot #	Assy Loc	Duration	Samp	Rej	Failure Mechanism
STRESS: ACOUSTIC, MSL3							
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	22	0	
CY62138FV30LL (7A62138GC)	4032933	611058000	JT-CHINA	COMP	22	0	
CY62128ELL (7A62128KC)	4021670	611059133	JT-CHINA	COMP	22	0	
STRESS: BOND SHEAR							
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	30	0	
CY62138FV30LL (7A62138GC)	4032933	611058000	JT-CHINA	COMP	30	0	
CY62128ELL (7A62128KC)	4021670	611059133	JT-CHINA	COMP	30	0	
STRESS: BOND PULL							
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	30	0	
CY62138FV30LL (7A62138GC)	4032933	611058000	JT-CHINA	COMP	30	0	
CY62128ELL (7A62128KC)	4021670	611059133	JT-CHINA	COMP	30	0	
STRESS: CONSTRUCTIONAL ANALYSIS							
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	5	0	
STRESS: DYE PENETRATION TEST							
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	15	0	
CY62138FV30LL (7A62138GC)	4032933	611058000	JT-CHINA	COMP	15	0	
CY62128ELL (7A62128KC)	4021670	611059133	JT-CHINA	COMP	15	0	
STRESS: ESD-CHARGE DEVICE MODEL, 250V							
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	3	0	
STRESS: ESD-CHARGE DEVICE MODEL, 500V							
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	3	0	
STRESS: ESD-CHARGE DEVICE MODEL, 750V							
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	3	0	
STRESS: ESD-HUMAN BODY CIRCUIT PER JESD22, METHOD A114-E, (500V)							
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	3	0	
STRESS: ESD-HUMAN BODY CIRCUIT PER JESD22, METHOD A114-E, (1000V)							
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	3	0	
STRESS: ESD-HUMAN BODY CIRCUIT PER JESD22, METHOD A114-E, (1500V)							
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	3	0	

Reliability Test Data

QTP #: 105211

Device	Fab Lot #	Assy Lot #	Assy Loc	Duration	Samp	Rej	Failure Mechanism
--------	-----------	------------	----------	----------	------	-----	-------------------

STRESS: ESD-HUMAN BODY CIRCUIT PER JESD22, METHOD A114-E, (2000V)

CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	3	0	
-------------------------	---------	-----------	----------	------	---	---	--

STRESS: HIGH TEMP DYNAMIC OPERATING LIFE-EARLY FAILURE RATE, 150C, 1.85V, Vcc Core

CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	48	800	0	
-------------------------	---------	-----------	----------	----	-----	---	--

CY62138FV30LL (7A62138GC)	4032933	611058000	JT-CHINA	48	800	0	
---------------------------	---------	-----------	----------	----	-----	---	--

CY62128ELL (7A62128KC)	4021670	611059133	JT-CHINA	48	797	0	
------------------------	---------	-----------	----------	----	-----	---	--

STRESS: HIGH TEMP DYNAMIC OPERATING LIFE-LATENT FAILURE RATE, 150C, 1.85V, Vcc Core

CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	408	80	0	
-------------------------	---------	-----------	----------	-----	----	---	--

CY62138FV30LL (7A62138GC)	4032933	611058000	JT-CHINA	408	80	0	
---------------------------	---------	-----------	----------	-----	----	---	--

CY62128ELL (7A62128KC)	4021670	611059133	JT-CHINA	408	80	0	
------------------------	---------	-----------	----------	-----	----	---	--

STRESS: STATIC LATCH-UP TESTING, 125C, 5.4V, +/-140Ma

CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	6	0	
-------------------------	---------	-----------	----------	------	---	---	--

STRESS: HI-ACCEL SATURATION TEST, 130C, 3.60V, 85%RH, PRE COND 192 HR 30C/60%RH, MSL3

CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	96	80	0	
-------------------------	---------	-----------	----------	----	----	---	--

CY62138FV30LL (7A62138GC)	4032933	611058000	JT-CHINA	96	80	0	
---------------------------	---------	-----------	----------	----	----	---	--

CY62128ELL (7A62128KC)	4021670	611059133	JT-CHINA	96	80	0	
------------------------	---------	-----------	----------	----	----	---	--

STRESS: HIGH TEMP STORAGE

CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	1000	80	0	
-------------------------	---------	-----------	----------	------	----	---	--

STRESS: LEAD INTEGRITY

CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	5	0	
-------------------------	---------	-----------	----------	------	---	---	--

STRESS: PRESSURE COOKER TEST (121C, 100%RH), 15 Psig, PRE COND 192 HR 30C/60%RH (MSL3)

CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	96	80	0	
-------------------------	---------	-----------	----------	----	----	---	--

CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	168	80	0	
-------------------------	---------	-----------	----------	-----	----	---	--

CY62138FV30LL (7A62138GC)	4032933	611058000	JT-CHINA	96	80	0	
---------------------------	---------	-----------	----------	----	----	---	--

CY62138FV30LL (7A62138GC)	4032933	611058000	JT-CHINA	168	80	0	
---------------------------	---------	-----------	----------	-----	----	---	--

CY62128ELL (7A62128KC)	4021670	611059133	JT-CHINA	96	80	0	
------------------------	---------	-----------	----------	----	----	---	--

CY62128ELL (7A62128KC)	4021670	611059133	JT-CHINA	168	80	0	
------------------------	---------	-----------	----------	-----	----	---	--



Reliability Test Data

QTP #: 105211

<i>Device</i>	<i>Fab Lot #</i>	<i>Assy Lot #</i>	<i>Assy Loc</i>	<i>Duration</i>	<i>Samp</i>	<i>Rej</i>	<i>Failure Mechanism</i>
STRESS: PHYSICAL DIMENSION							
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	30	0	
CY62138FV30LL (7A62138GC)	4032933	611058000	JT-CHINA	COMP	30	0	
CY62128ELL (7A62128KC)	4021670	611059133	JT-CHINA	COMP	30	0	
STRESS: SOLDERABILITY							
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	15	0	
CY62138FV30LL (7A62138GC)	4032933	611058000	JT-CHINA	COMP	15	0	
CY62128ELL (7A62128KC)	4021670	611059133	JT-CHINA	COMP	15	0	
STRESS: TC COND. C -65C TO 150C, PRE COND 192 HR 30C/60%RH, MSL3							
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	500	89	0	
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	1000	84	0	
CY62138FV30LL (7A62138GC)	4032933	611058000	JT-CHINA	500	80	0	
CY62138FV30LL (7A62138GC)	4032933	611058000	JT-CHINA	1000	80	0	
CY62128ELL (7A62128KC)	4021670	611059133	JT-CHINA	500	80	0	
CY62128ELL (7A62128KC)	4021670	611059133	JT-CHINA	1000	80	0	
STRESS: POST TC BOND PULL							
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	5	0	
STRESS: ELECTRICAL DISTRIBUTION							
CY62148ES L (7A62148FC)	4017686	611057999	JT-CHINA	COMP	30	0	
CY62128ELL (7A62128KC)	4021670	611059133	JT-CHINA	COMP	30	0	

Document History Page

Document Title: QTP 105211: Automotive 32L STSOP (8x13.4mm) NiPdAu, MSL3, 260C Reflow JCET-China
(JT) Qualification Report
Document Number: 001-67628

Rev.	ECN No.	Orig. of Change	Description of Change
**	3178043	NRG	Initial Spec Release
*A	3226327	NRG	Updated the Reject Column to reflect "0" reject on ESD-HBM 1500V results
*B	4365037	ILZ	Sunset spec review Updated front page to reflect new qualification report template per Spec 001-57717 Page 3 – Major package information table – Replaced assembly process flow spec# 001-64159 with 001-67698

Distribution: WEB

Posting: None