




Bottom view



- 1) Does not include plastic or metal protrusion of 0.15 max. per side
- 2) Exposed diepad, excluding moldflash allowance of 0.3mm max. per side.
- 3) Does not include dambar protrusion of 0.05 max. per side.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Drawing according to ISO 8015, general tolerances ISO-2768-mK