



SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.4
A1	0.17	-	-
A2	0.98	-	1.15
D	13 BSC		
E	11 BSC		
Øb	0.35	0.4	0.45
eE	0.8 BSC		
eD	0.8 BSC		
SD / SE	0.4 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Dimensioning and tolerancing methods per ASME Y14.5M-1994.