


All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]

Dimensions and tolerances methods per ASME Y14.5-2009.

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.7
A1	0.3	0.35	0.4
D	16 BSC		
E	16 BSC		
$\varnothing b$	0.4	0.45	0.5
eD	0.8 BSC		
eE	0.8 BSC		
SD / SE	0.4 BSC		